



CorePro Glass LED bulbs

CorePro LEDBulbND 7-60W E27 WW A60 CL G

Featuring a classic heritage design, these filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. A very easy choice for people who are looking for a retrofit LED replacement, these CorePro LED bulbs provide 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light in a vintage style. CorePro LED lighting that offers a lifetime of 15,000 hours to reduce maintenance costs.

Product data

General information	
Lighting Technology	LED
Flux measurement reference	Sphere
Switching Cycle	20,000
Nominal lifetime	15,000 h
Cap base	E27 [E27]


Light technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1

Operating and electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	7 W
Lamp current (nom.)	60 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	45 °C


CorePro Glass LED bulbs

Photometric data




Light Distribution Diagram - CorePro LEDBulbND 7-60W E27 WW A60 CL G

Lifetime



Life Expectancy Diagram - CorePro LEDBulbND 7-60W E27 WW A60 CL G



Lumen Maintenance Diagram - CorePro LEDBulbND 7-60W E27 WW A60 CL G

