

Main switch, P3, 63 A, surface mounting, 3 pole, Emergency switching off function, With red rotary handle and yellow locking ring, Lockable in the 0 (Off) position, with assembly sheet screen



Part no. P3-63/I4/MBS/SVB
182421
EL Number 1400421
(Norway)

General specifications	
Product name	Eaton Moeller® series P3 Main switch
Part no.	P3-63/I4/MBS/SVB
EAN	4015081773473
Product Length/Depth	139 millimetre
Product height	240 millimetre
Product width	160 millimetre
Product weight	1.265 kilogram
Certifications	VDE 0660 IEC/EN 60947 IEC/EN 60947-3 IEC/EN 60204
Product Tradename	P3
Product Type	Main switch
Product Sub Type	None
Catalog Notes	Rated Short-time Withstand Current (Icw) for a time of 1 second
Features & Functions	
Features	Version as main switch Version as emergency stop installation Version as maintenance-/service switch
Fitted with:	Red rotary handle and yellow locking ring Assembly sheet screen
Functions	Emergency switching off function Interlockable
Locking facility	Lockable in the 0 (Off) position
Number of poles	3
General information	
Accessories	Auxiliary contact or neutral conductor fitted by user.
Degree of protection	NEMA 12
Degree of protection (front side)	IP65
Lifespan, mechanical	100,000 Operations
Mounting method	Surface mounting
Mounting position	As required
Operating frequency	1200 Operations/h
Overvoltage category	III
Pollution degree	3
Rated impulse withstand voltage (Uimp)	6000 V AC
Safe isolation	440 V AC, Between the contacts, According to EN 61140
Safety parameter (EN ISO 13849-1)	B10d values as per EN ISO 13849-1, table C.1
Shock resistance	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
Suitable for	Ground mounting
Climatic environmental conditions	
Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	40 °C
Ambient operating temperature (enclosed) - min	-20 °C
Ambient operating temperature (enclosed) - max	40 °C
Climatic proofing	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Terminal capacities	

Terminal capacity	1 x (2.5 - 35) mm ² , solid or stranded 2 x (2.5 - 10) mm ² , solid or stranded 1 x (1.5 - 25) mm ² , flexible with ferrules to DIN 46228 2 x (1.5 - 6) mm ² , flexible with ferrules to DIN 46228
Screw size	M5, Terminal screw
Tightening torque	3 Nm, Screw terminals
Electrical rating	
Rated breaking capacity at 220/230 V (cos phi to IEC 60947-3)	640 A
Rated breaking capacity at 400/415 V (cos phi to IEC 60947-3)	600 A
Rated breaking capacity at 500 V (cos phi to IEC 60947-3)	590 A
Rated breaking capacity at 660/690 V (cos phi to IEC 60947-3)	340 A
Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V	51 A
Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V	55 A
Rated operational current (Ie) at AC-3, 500 V	44 A
Rated operational current (Ie) at AC-3, 660 V, 690 V	22.1 A
Rated operational current (Ie) at AC-21, 440 V	63 A
Rated operational current (Ie) at AC-23A, 230 V	63 A
Rated operational current (Ie) at AC-23A, 400 V, 415 V	63 A
Rated operational current (Ie) at AC-23A, 500 V	63 A
Rated operational current (Ie) at AC-23A, 690 V	63 A
Rated operational current (Ie) at DC-1, load-break switches I/r = 1 ms	63 A
Rated operational current (Ie) at DC-23A, 24 V	50 A
Rated operational current (Ie) at DC-23A, 48 V	50 A
Rated operational current (Ie) at DC-23A, 60 V	50 A
Rated operational current (Ie) at DC-23A, 120 V	25 A
Rated operational power at AC-3, 380/400 V, 50 Hz	30 kW
Rated operational power at AC-3, 415 V, 50 Hz	30 kW
Rated operational power at AC-3, 500 V, 50 Hz	30 kW
Rated operational power at AC-3, 690 V, 50 Hz	30 kW
Rated operational power at AC-23A, 220/230 V, 50 Hz	18.5 kW
Rated operational power at AC-23A, 400 V, 50 Hz	30 kW
Rated operational power at AC-23A, 500 V, 50 Hz	45 kW
Rated operational power at AC-23A, 690 V, 50 Hz	55 kW
Rated operational voltage (Ue) at AC - max	690 V
Rated uninterrupted current (Iu)	63 A
Uninterrupted current	Rated uninterrupted current Iu is specified for max. cross-section.
Short-circuit rating	
Rated conditional short-circuit current (Iq)	4 kA (Load side) 100 kA (Supply side)
Rated short-time withstand current (Icw)	1.26 kA
Short-circuit protection rating	80 A gG/gL, Fuse, Contacts
Switching capacity	
Load rating	2 x I# (with intermittent operation class 12, 25 % duty factor) 1.6 x I# (with intermittent operation class 12, 40 % duty factor) 1.3 x I# (with intermittent operation class 12, 60 % duty factor)
Number of contacts in series at DC-23A, 24 V	1
Number of contacts in series at DC-23A, 48 V	2
Number of contacts in series at DC-23A, 60 V	2
Number of contacts in series at DC-23A, 120 V	3
Rated making capacity up to 690 V (cos phi to IEC/EN 60947-3)	800 A
Voltage per contact pair in series	60 V
Contacts	
Control circuit reliability	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
Number of auxiliary contacts (change-over contacts)	0
Number of auxiliary contacts (normally closed contacts)	0
Number of auxiliary contacts (normally open contacts)	0

Actuator		
Actuator color		Red
Actuator type		Door coupling rotary drive
Design verification		
Equipment heat dissipation, current-dependent Pvid		4.5 W
Heat dissipation capacity Pdis		0 W
Heat dissipation per pole, current-dependent Pvid		4.5 W
Rated operational current for specified heat dissipation (In)		63 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		UV resistance only in connection with protective shield.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Switch disconnecter (EC000216)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Switch disconnecter (ecl@ss10.0.1-27-37-14-03 [AKF060013])		
Version as main switch		Yes
Version as maintenance-/service switch		Yes
Version as safety switch		No
Version as emergency stop installation		Yes
Version as reversing switch		No
Number of switches		1
Max. rated operation voltage Ue AC	V	690
Rated operating voltage	V	690 - 690
Rated permanent current Iu	A	63
Rated permanent current at AC-23, 400 V	A	63
Rated permanent current at AC-21, 400 V	A	63
Rated operation power at AC-3, 400 V	kW	30
Rated short-time withstand current Icw	kA	1.26
Rated operation power at AC-23, 400 V	kW	30
Switching power at 400 V	kW	30
Conditioned rated short-circuit current Iq	kA	100
Number of poles		3
Number of auxiliary contacts as normally closed contact		0

Number of auxiliary contacts as normally open contact			0
Number of auxiliary contacts as change-over contact			0
Motor drive optional			No
Motor drive integrated			No
Voltage release optional			No
Device construction			Complete device in housing
Suitable for floor mounting			Yes
Suitable for front mounting 4-hole			No
Suitable for front mounting centre			No
Suitable for distribution board installation			No
Suitable for intermediate mounting			No
Colour control element			Red
Type of control element			Door coupling rotary drive
Interlockable			Yes
Type of electrical connection of main circuit			Screw connection
Degree of protection (IP), front side			IP65
Degree of protection (NEMA)			12