

Changeoverswitches, T0, 20 A, surface mounting, 1 contact unit(s),
Contacts: 2, 45 °, maintained, With 0 (Off) position, HAND-0-AUTO, Design
number 15431

Part no. T0-1-15431/I1
207070
EL Number 1456295
(Norway)

General specifications	
Product name	Eaton Moeller® series T0 Changeover switch
Part no.	T0-1-15431/I1
EAN	4015082070700
Product Length/Depth	137 millimetre
Product height	102 millimetre
Product width	80 millimetre
Product weight	0.253 kilogram
Certifications	IEC/EN 60204 VDE 0660 IEC/EN 60947-3 IEC/EN 60947
Product Tradename	T0
Product Type	Changeover switch
Product Sub Type	None
Catalog Notes	Rated Short-time Withstand Current (Icw) for a time of 1 second
Features & Functions	
Features	Complete device in housing
Fitted with:	0 (off) position Black thumb grip and front plate
Inscription	" HAND-0-AUTO "
Number of poles	Single-pole
General information	
Degree of protection	IP65
Degree of protection (front side)	IP65 NEMA 12
Lifespan, mechanical	400,000 Operations
Mounting method	Surface mounting
Mounting position	As required
Number of contact units	1
Operating frequency	1200 Operations/h
Overvoltage category	III
Pollution degree	3
Product category	Control switches
Rated impulse withstand voltage (Uimp)	6000 V AC
Safe isolation	440 V AC, Between the contacts, According to EN 61140
Safety parameter (EN ISO 13849-1)	B10d values as per EN ISO 13849-1, table C.1
Shock resistance	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
Suitable for	Ground mounting
Switching angle	45 °
Type	Changeover switch
Climatic environmental conditions	
Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	40 °C
Ambient operating temperature (enclosed) - min	-25 °C
Ambient operating temperature (enclosed) - max	40 °C
Climatic proofing	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78

Terminal capacities	
Terminal capacity (flexible with ferrule)	1 x (0.75 - 2.5) mm ² , ferrules to DIN 46228 2 x (0.75 - 2.5) mm ² , ferrules to DIN 46228
Terminal capacity (solid/stranded)	1 x (1 - 2.5) mm ² 2 x (1 - 2.5) mm ²
Screw size	M3.5, Terminal screw
Tightening torque	8.8 lb-in, Screw terminals 1 Nm, Screw terminals
Electrical rating	
Rated breaking capacity at 220/230 V (cos phi to IEC 60947-3)	100 A
Rated breaking capacity at 400/415 V (cos phi to IEC 60947-3)	110 A
Rated breaking capacity at 500 V (cos phi to IEC 60947-3)	80 A
Rated breaking capacity at 660/690 V (cos phi to IEC 60947-3)	60 A
Rated operating voltage (Ue) at AC - max	690 V
Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V	11.5 A
Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V	11.5 A
Rated operational current (Ie) at AC-3, 500 V	9 A
Rated operational current (Ie) at AC-3, 660 V, 690 V	4.9 A
Rated operational current (Ie) at AC-21, 440 V	20 A
Rated operational current (Ie) at AC-23A, 230 V	13.3 A
Rated operational current (Ie) at AC-23A, 400 V, 415 V	13.3 A
Rated operational current (Ie) at AC-23A, 500 V	13.3 A
Rated operational current (Ie) at AC-23A, 690 V	7.6 A
Rated operational current (Ie) at DC-1, load-break switches I/r = 1 ms	10 A
Rated operational current (Ie) at DC-13, control switches L/R = 50 ms	10 A
Rated operational current (Ie) at DC-21, 240 V	1 A
Rated operational current (Ie) at DC-23A, 24 V	10 A
Rated operational current (Ie) at DC-23A, 48 V	10 A
Rated operational current (Ie) at DC-23A, 60 V	10 A
Rated operational current (Ie) at DC-23A, 120 V	5 A
Rated operational current (Ie) at DC-23A, 240 V	5 A
Rated operational current (Ie) star-delta at AC-3, 230 V	20 A
Rated operational current (Ie) star-delta at AC-3, 400 V	20 A
Rated operational current (Ie) star-delta at AC-3, 500 V	15.6 A
Rated operational current (Ie) star-delta at AC-3, 690 V	8.5 A
Rated operational power at AC-3, 415 V, 50 Hz	5.5 kW
Rated operational power at AC-3, 500 V, 50 Hz	5.5 kW
Rated operational power at AC-3, 690 V, 50 Hz	4 kW
Rated operational power at AC-23A, 220/230 V, 50 Hz	3 kW
Rated operational power at AC-23A, 400 V, 50 Hz	5.5 kW
Rated operational power at AC-23A, 500 V, 50 Hz	7.5 kW
Rated operational power at AC-23A, 690 V, 50 Hz	5.5 kW
Rated operational power star-delta at 220/230 V, 50 Hz	5.5 kW
Rated operational power star-delta at 380/400 V, 50 Hz	7.5 kW
Rated operational power star-delta at 500 V, 50 Hz	7.5 kW
Rated operational power star-delta at 690 V, 50 Hz	5.5 kW
Rated uninterrupted current (Iu)	20 A
Uninterrupted current	Rated uninterrupted current Iu is specified for max. cross-section.
Short-circuit rating	
Rated conditional short-circuit current (Iq)	6 kA
Rated short-time withstand current (Icw)	320 A, Contacts, 1 second
Short-circuit protection rating	20 A gG/gL, Fuse, Contacts
Switching capacity	
Load rating	1.6 x I# (with intermittent operation class 12, 40 % duty factor) 2 x I# (with intermittent operation class 12, 25 % duty factor) 1.3 x I# (with intermittent operation class 12, 60 % duty factor)
Number of contacts in series at DC-21A, 240 V	1

Number of contacts in series at DC-23A, 24 V			1
Number of contacts in series at DC-23A, 48 V			2
Number of contacts in series at DC-23A, 60 V			3
Number of contacts in series at DC-23A, 120 V			3
Number of contacts in series at DC-23A, 240 V			5
Rated making capacity up to 690 V (cos phi to IEC/EN 60947-3)			130 A
Voltage per contact pair in series			60 V
Contacts			
Control circuit reliability			1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
Number of contacts			2
Actuator			
Actuator function			Maintained With 0 (Off) position
Actuator type			Toggle
Number of switch positions			3
Design verification			
Equipment heat dissipation, current-dependent Pvid			0 W
Heat dissipation capacity Pdis			0 W
Heat dissipation per pole, current-dependent Pvid			0.6 W
Rated operational current for specified heat dissipation (In)			20 A
Static heat dissipation, non-current-dependent Pvs			0 W
10.2.2 Corrosion resistance			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			UV resistance only in connection with protective shield.
10.2.5 Lifting			Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of assemblies			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Control switch (EC002611)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Control switch (ecl@ss10.0.1-27-37-14-14 [ACN998011])			
Type of switch			Reverser
Number of poles			1
Max. rated operation voltage Ue AC		V	690
Rated permanent current Iu		A	20
Number of switch positions			3
With zero (off) position			Yes

With retraction in 0-position		No
Device construction		Surface mounted device
Width in number of modular spacings		0
Suitable for floor mounting		Yes
Suitable for front mounting		No
Suitable for distribution board installation		No
Suitable for intermediate mounting		No
Complete device in housing		Yes
Type of control element		Toggle
Front shield size		48x48 mm
Degree of protection (IP), front side		IP65
Degree of protection (NEMA), front side		12