



Molded, 50 Mil Pitch, Dual-In-Line Resistor Network



Vishay Thin Film ORN series Dividers provide optimum ratio precision, small size and exceptional stability for most applications. They offer a wide ratio range that is listed in the selection guide and are available for immediate delivery. The tight ratio tolerance offered on the standard ratios will provide exceptional performance throughout life.

SCHEMATIC



FEATURES

- Lead (Pb)-free available
- 0.068" (1.73 mm) maximum seated height
- Rugged molded case construction with no internal solder (JEDEC MS-012 standard)
- Thin film passivity Microbe element
- Low temperature coefficient (± 25 ppm/ $^{\circ}$ C)


RoHS*
COMPLIANT

TYPICAL PERFORMANCE

	ABS	TRACKING
TCR	25	5
	ABS	RATIO
TOL	0.1	0.05

STANDARD RESISTANCE OFFERING (R_1/R_2)

RATIO	R_1	R_2
100:1	100K	1K
50:1	50K	1K
25:1	25K	1K
20:1	20K	1K
10:1	10K	1K
5:1	10K	2K
2:1	10K	5K

STANDARD ELECTRICAL SPECIFICATIONS

TEST	SPECIFICATIONS	CONDITIONS
Material	Passivated Nichrome	
TCR:	Tracking	± 5 ppm/ $^{\circ}$ C
	Absolute	± 25 ppm/ $^{\circ}$ C
Tolerance:	Ratio	± 0.05 %
	Absolute	± 0.1 %
Power Rating:	Resistor	100 mW
	Package	400 mW
Stability:	ΔR Absolute	500 ppm
	ΔR Ratio	150 ppm
Voltage Coefficient	< 0.1 ppm/V	
Working Voltage	50 V (Max.)	
Operating Temperature Range	- 55 $^{\circ}$ C to + 125 $^{\circ}$ C	
Storage Temperature Range	- 55 $^{\circ}$ C to + 150 $^{\circ}$ C	
Noise	$< - 30$ dB	
Thermal EMF	0.08 μ V/ $^{\circ}$ C	
Shelf Life Stability:	Absolute	100 ppm
	Ratio	20 ppm
		1 year at + 25 $^{\circ}$ C
		1 year at + 25 $^{\circ}$ C

Note: Tantalum Nitride film is custom, consult factory


* Pb containing terminations are not RoHS compliant, exemptions may apply

ORN (Divider)

Vishay Thin Film Molded, 50 Mil Pitch, Dual-In-Line Resistor Network



DIMENSIONS AND IMPRINTING in inches and millimeters




DIMENSION	INCHES	MM
A	0.157	3.99
B	0.0165 ± 0.005	0.4 ± 0.06
C	0.050	1.27
D	0.195 Max.	4.93
E	0.008 ± 0.001	0.20 ± 0.03
F	0.028 ± 0.001	0.71 ± 0.02
G	0.239 ± 0.005	6.07 ± 0.13
H	0.068 Max.	1.73
I	0.008 ± 0.002	0.22 ± 0.06
Ø	2° to 6°	

Notes

1. Leads are within 0.005" (0.13 mm) of true position
2. Leads coplanar to ± 0.004" (± 0.50 mm)
3. Marking - VISHAY Symbol, Part Number from Ordering Information


MECHANICAL SPECIFICATIONS	
Resistive Element	Passivated Nichrome
Body	Molded epoxy
Package Format	JEDEC MS-012
Terminals	Copper alloy
Solderability	Per MIL-PRF-83401
Marking Resistance to Solvents	Permanency testing per MIL-PRF-83401
Lead (Pb)-free Option	100 % Matte Tin
Lead (Pb)-free Finish	Plated

DERATING CURVE



GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: ORNA5-1UF (preferred part number format)




GLOBAL MODEL (4 or 5 digits)
ORNA (Tin/Lead)
ORNTA (Lead (Pb)-free) (e3)

RESISTANCE (3, 4 or 5 digits)
2-1
5-1
10-1
20-1
25-1
50-1
100-1

PACKAGING
TAPE AND REEL
T0 = 100 Min 100 Mult
T1 = 1000 Min 1000 Mult
T3 = 300 Min 300 Mult
T5 = 500 Min 500 Mult
TF = Full Reel 3000
TS = 100 Min 1 Mult
UF = TUBED

Historical Part Number example: ORNA2-1 (will continue to be accepted)





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.