



Terminals & Splices > Automotive Terminals > MULTILOCK, RECEPTACLE AND TAB



Terminal Type: **Receptacle**  
Mating Tab Width: **1 mm [ .039 in ]**  
Mating Tab Thickness: **.64 mm [ .025 in ]**  
Terminal Transmits: **0 – 24 A (Low Power)**  
Wire Size: **22 – 20 AWG**

[All MULTILOCK, RECEPTACLE AND TAB \(136\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body

Contact Features

Contact Size	1mm
Contact Fabrication	Stamped & Formed
Typical Current Rating	5 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	1 mm[.039 in]
Mating Tab Thickness	.64 mm[.025 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions



Compatible Insulation Diameter Range	1.4 – 2 mm[.055 – .079 in]
Wire Size	.3 – .5 mm²
Wire Size Search	20 AWG, 21 AWG, 22 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C[176 °F][185 °F][194 °F][212 °F][221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides











on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-M9194-CH8172 MULTILOCK, CONNECTOR HOUSING</p>	 <p>TE Part # 755430-1 EXT TOOL FOR DOUBLE LOOK</p>	 <p>TE Part # 58522-1 PRO-CRMPR II TOOL &amp; DIE</p>	 <p>TE Part # 58522-2 PRO-CRMPR II DIE</p>
 <p>TE Part # 91577-1 CCII 040 SERIES REC TAB 22-20 ASSY</p>	 <p>TE Part # 175567-6 HYBRID I/O PLUG HSG 26P GRAY</p>	 <p>TE Part # 174515-5 040/070 HYBRID PLUG 22P BLUE</p>	

Also in the Series | Multilock Connector System

 <p>Automotive Connector Caps &amp; Covers (17)</p>	 <p>Automotive Connector EMC Shielding (1)</p>	 <p>Automotive Connector Locks &amp; Position Assurance(2)</p>	 <p>Automotive Housings(603)</p>
 <p>Automotive Terminals(141)</p>	 <p>Connector Seals &amp; Cavity Plugs(2)</p>	 <p>Insertion &amp; Extraction Tools(6)</p>	 <p>Other Automotive Connector Accessories(14)</p>



PCB Headers & Receptacles(142)

Customers Also Bought



TE Part #174045-2  
MULTILOCK, CONNECTOR HOUSING



TE Part #T4171020008-001  
M12,REAR MOUNT,MALE, A, 8P, 0.2M WIRE




TE Part #DT4S-BT  
BOOT, 4P, PLG, ST, GRY



TE Part #DRC14-24PA  
REC, 24P, BLK, N, A



TE Part #175027-1  
MULTILOCK, RECEPTACLE AND TAB



TE Part #179679-6  
04/07-2 HD HYBRID PLUG ASY 25P

Documents

Product Drawings

040 HDIO REC CONTACT TIN L/P

English

CAD Files

Customer View Model

ENG\_CVM\_175061-1\_O1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_175061-1\_O1.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_175061-1\_O1.2d\_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



**Datasheets & Catalog Pages**  
**MULTILOCK Connector System**

English

**Product Specifications**  
**Application Specification**

English

**Crimping .040 Series Receptacle Contact**

English