## multicomp PRO

RoHS

**Compliant** 

10W, AC-DC converter



#### Features

- Ultra-wide 85 305VAC and 100 430VDC input voltage range
- Operating ambient temperature range: -40°C to +85°C
- Up to 85% efficiency
- No-load power consumption < 0.1W
- 5000m altitude application
- EMI performance meets CISPR32/EN55032 CLASS B, EN55014
- · IEC/EN/UL62368/EN60335/EN61558 safety approval

### 

### Description

MP-LD10-23BxxR2 series AC-DC converters is one of new generation compact size power converter. It features ultra-wide AC input and at the same time accepts DC input voltage, low power consumption, low ripple & noise, high efficiency, high reliability, reinforced isolation. It offers good EMC performance compliant to IEC/EN61000-4 and CISPR32/EN55032 and meets IEC/EN/UL62368/EN60335/EN61558 standards. The converters are widely used in industrial, power, home appliances, instrumentation, communication and civil applications. For extremely harsh EMC environment, we recommend using the application circuit show in Design Reference of this datasheet.

Selection Guide				
Part Number	Output Power	Nominal Output Voltage and Current	Efficiency at 230VAC (%) Typ.	Capacitive Load (µF) Max.
MP-LD10-23B03R2	8.6W	3.3V/2600mA	74	6600
MP-LD10-23B05R2		5V/2000mA	79	5000
MP-LD10-23B09R2	4014/	9V/1100mA	81	3600
MP-LD10-23B12R2	10W	12V/830mA	84	2000
MP-LD10-23B15R2		15V/660mA	84	820
MP-LD10-23B24R2		24V/410mA	85	470

Input Specifications						
Item	Operating Conditions	Min.	Тур.	Max.	Unit	
Input Voltago Bango	AC input	85		305	V AC	
Input Voltage Range	DC input	100		430	V DC	
Input Frequency		47	-	63	Hz	
In nut Current	115V AC			0.23		
Input Current	230V AC			0.15	٨	
Inrush Current	115V AC		15		A	
Infush Current	230V AC		25			
Leakage Current	277V AC/50Hz		0.1mA R	MS Max.	-	
Fuse(A2S/A4S package series include fuse)			2A/300V, slow	-blow, required	1	
Hot Plug			Unava	ailable		



# multicomp PRO

ltem	Operat	ing Conditions	Min.	Тур.	Max.	Unit	
Output Voltage Accuracy				±2	-		
Line Regulation	Full load			±0.5	-	%	
Load Regulation	0%-100% load	k		±1	-		
Ripple & Noise*	20MHz bandw value)	vidth (peak-to-peak		50	100	mV	
Otan di hui Davian Ocasa martían	0001/40	3.3/5/9/12V		0.10	-	14/	
Stand-by Power Consumption	230V AC	24V		0.12 W			
Temperature Coefficient		•		±0.02	-	%/°C	
Short-circuit Protection			Hiccup, continuous, self-recovery				
Over-current Protection			≥110%lo, self-recovery				
	3.3/5V		≤7.5VDC (Output voltage clamp or hiccup )				
Over veltere Dretestion	9V		≤15VD0	C (Output volta	age clamp o	hiccup)	
Over-voltage Protection	12V		≤20VD0	C (Output volta	age clamp o	r hiccup)	
	24V		≤30VD0	C (Output volta	age clamp o	r hiccup)	
Minimum Load			0	-	-	%	
Llold un Tinee	115V AC input	t	-	5	-		
Hold-up Time	230V AC input		-	50	-	ms	

#### **General Specifications**

	tem	Operat	ing Conditions	Min.	Тур.	Max.	Unit
Isolation	Input-Output	Electric Strength Te <5mA	est for 1min, leakage current	4000	-	-	V AC
Insulation Resistance	Input-Output	At 500V DC	At 500V DC		-	-	MΩ
Operating Te	emperature			40	-	. 05	°C
Storage Terr	perature			-40	-	+85	
Storage Hun	nidity			-	-	+95	%RH
Coldorin a To		Wave-soldering260 ± 5°C; time:				time: 5 - 10	S
Soldering Te	mperature	Manual-welding	Manual-welding		360 ± 10°C; time: 3 - 5s		
Switching Fr	equency			-	65	-	kHz
		-40°C to -25°C	85V AC to 115V AC	2.2	-	-	
		+50°C to +70°C	3.3/5V	2.5	-	-	%/°C
	in a	+55°C to +70°C	9/12/24V	3.33	-	-	%/°C
Power Derat	ing	+70°C to +85°C		0.66	-	-	
		85V AC - 100V AC		0.83	-	-	%/V AC
		2000m - 5000m		0.67	-		%/Km
Safety Stand	lard			IEC/EN	I/UL62368/E	EN60335/EI	N61558



## multicomp PRO

Item	Оре	erating Conditions	Min.	Тур.	Max.	Unit
Safety Certification			IEC/EN	I/UL62368/E	N60335/EN	V61558
Safety Class				CLA	SS II	
MTBF			MIL-HD	)BK-217F@	25°C > 320	0,000 h
		Ta:25°C 100% load		>130 :	<b>x</b> 10³ h	
Designed Life	230V AC	Ta: 55°C 100% load		>20 ×	: 10³ h	
		Ta: 55°C 80% load		>27 ×	: 10³ h	


Mechanica	I Specifications	
Case Material		Black plastic; flame-retardant and heat-resistant (UL94 V-0)
Dimensions	DIP package	40mm × 25.4mm × 21mm
Weight	DIP mounting	34g (Тур.)
Cooling Method	ł	Free air convection

Electron	nagnetic Compatik	oility (EMC)		
	CE	CISPR32/EN55032	CLASS B	
Emissions	CE	EN55014-1		
EIIIISSIOIIS	RE	CISPR32/EN55032	CLASS B (see Fig. 5-2 for recommended circ	uit)
		EN55014-1		
	ESD	IEC/EN61000-4-2	Contact ± 8KV/Air ±15KV	perf. Criteria B
		EN55014-2		perf. Criteria B
	RS	IEC/EN61000-4-3	10V/m	perf. Criteria A
	10	EN55014-2		perf. Criteria A
		IEC/EN61000-4-4	±2KV	perf. Criteria B
	EFT	IEC/EN61000-4-4	±4KV (See Fig.2 for recommended circuit)	perf. Criteria B
		EN55014-2		perf. Criteria B
Immunity		IEC/EN61000-4-5	line to line ±1KV	
	Surge	IEC/EN61000-4-5	line to line ±2KV (See Fig.2 for recommended circuit)	perf. Criteria B
		EN55014-2		perf. Criteria B
	CS	IEC/EN61000-4-6	10Vr.m.s	perf. Criteria A
	65	EN55014-2		perf. Criteria A
	Voltage dip, short	IEC/EN61000-4-11	0%, 70%	perf. Criteria B
	interruption and voltage variation	EN55014-2		perf. Criteria B





# multicomp PRO

### **Product Characteristic Curve**



Note: ① With an AC input between 85-115VAC and a DC input between 100-165VDC, the output power must be derated as per temperature derating curves; ② This product is suitable for applications using natural air cooling; for applications in closed environment please consult factory or one of our FAE.





### **Design Reference**

1. Typical application




Fig. 1: Typical circuit diagram

Part Number	C1(µF)	C2(µF)	FUSE	TVS	MOV
MP-LD10-23B03R2		220µF/16V		SMBJ7A	
MP-LD10-23B05R2		220µF/10V	2A/300V,	SIVIDJ/A	
MP-LD10-23B09R2	1µF/50V		slow-blow,	SMBJ12A	S14K350
MP-LD10-23B12R2		100µF/25V	required	SMBJ20A	
MP-LD10-23B15R2				SMBJ20A	
MP-LD10-23B24R2				SMBJ30A	


Output Filter Components:

We recommend using an electrolytic capacitor with high frequency, and low ESR rating for C2 (refer to manufacture's datasheet). Choose a Capacitor voltage rating with at least 20% margin, in other words not exceeding 80%. C1 is a ceramic capacitor used for filtering high-frequency noise and TVS is a recommended suppressor diode to protect the application in case of a converter failure.



## multicomp PRO

#### 2. EMC compliance recommended circuit





#### Fig 2: EMC application circuit with higher requirements

Component	Recommended value
MOV	S14K350
R1	6.8Ω/3W
FUSE	2A/300V, slow-blow, required

#### **Dimensions and Recommended Layout**

THIRD ANGLE PROJECTION





Note: Unit: mm[inch] Pin diameter tolerances: ±0.10[±0.004] General tolerances: ±0.50[±0.020] -Ø1.50 [Ø0.059]

Note: Grid 2.54\*2.54mm

Pi	in-Out
Pin	Function
1	AC(L)
2	AC(N)
3	No Pin
4	+Vo
5	No Pin
6	-Vo

**Dimensions : Millimetres** 

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information subject to change accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

