

Z5U (Y5U)
Features

- Extremely high volumetric efficiency
- Non-linear capacitance change
- Y5U characteristic is also fulfilled


Applications

- Blocking
- Coupling
- Decoupling
- Interference suppression

Termination

- Parallel wire leads, iron-nickel, tinned
- Crimped leads
- Non-standard lead lengths on request

Marking

- Rated capacitance, tolerance, manufacturer's logo, ceramic material, voltage

Delivery mode

- Cardboard tape in Ammo packing (standard)
- Cardboard tape on 360-mm reel or bulk on request

Electrical data

Temperature characteristic		Z5U (Y5U) ¹⁾	
Climatic category (IEC 60068-1)		30/85/56	
Standard		EIA	
Dielectric		Class 2	
Rated voltage ²⁾	V_R	50	VDC
Test voltage	V_{test}	$2,5 \cdot V_R/5$ s	VDC
Capacitance range / E series	C_R	10 nF ... 4,7 μ F (E6)	
Max. relative capacitance change	$\Delta C/C$	+22/-56	%
Dissipation factor (limit value)	$\tan \delta$	$< 50 \cdot 10^{-3}$	
Insulation resistance ³⁾ at +25 °C	R_{ins}	$> 10^4$	M Ω
Time constant ³⁾ at +25 °C	τ	> 500	s
Operating temperature range	T_{op}	-30 ... +85	°C
Ageing ⁴⁾		yes	

1) Y5U specification is also fulfilled.

2) Note: No operation on AC line.

3) For $C_R > 10$ nF the time constant $\tau = C \cdot R_{ins}$ is given.


4) Refer to chapter "General Technical Information", page 197.



Capacitance tolerances

Code letter	M
Tolerance	$\pm 20\%$

Dimensional drawing








*) Lead length for bulk packaging

**) Seating plane in acc. with IEC 600717


KKE0456-R-E

Dimensions (mm)

	Lead spacing \boxed{e} = 2,5 +0,6/-0,1 mm	
Type	B37982N	B37988N
		
h_{max}	5,5	6,5
b_{max}	5,0	5,0
s_{max}	2,5	2,5

	Lead spacing \boxed{e} = 5,0 +0,6/-0,1 mm		
Type	B37982G	B37988G	B37985N
			
h_{max}	5,5	6,5	9,0
b_{max}	5,0	5,0	7,5
s_{max}	2,5	2,5	2,5






Termination



KKE0457-Z-E

Multilayer Ceramic Capacitors
Z5U (Y5U)

Product range leaded capacitors

		Z5U (Y5U)									
Lead spacing		2,5 mm					5,0 mm				
											
$h \times b \times s$ (mm)		5,5 × 5,0 × 2,5		6,5 × 5,0 × 2,5		5,5 × 5,0 × 2,5		6,5 × 5,0 × 2,5		9,0 × 7,5 × 2,5	
Type		B37982N		B37988N		B37982G		B37988G		B37985N	
V_R (VDC)		50		50		50		50		50	
C_R		50		50		50		50		50	
10 nF											
15 nF											
22 nF											
33 nF											
47 nF											
68 nF											
100 nF											
150 nF											
220 nF											
330 nF											
470 nF											
680 nF											
1,0 μF											
1,5 μF											
2,2 μF											
3,3 μF											
4,7 μF											


Ordering codes and packing for Z5U (Y5U), 50 VDC, lead spacing 2,5 mm

C _R	Ordering code ¹⁾	Ammo packing	Reel packing	Bulk
		** \triangle 54	** \triangle 51	** \triangle 00
		pcs	pcs/reel	pcs

B37982, 50 VDC, 5,5 × 5,0 × 2,5 mm

10 nF	B37982N5103M0**	2500	2500	2000
15 nF	B37982N5153M0**	2500	2500	2000
22 nF	B37982N5223M0**	2500	2500	2000
33 nF	B37982N5333M0**	2500	2500	2000
47 nF	B37982N5473M0**	2500	2500	2000
68 nF	B37982N5683M0**	2500	2500	2000
100 nF	B37982N5104M0**	2500	2500	2000
150 nF	B37982N5154M0**	2500	2500	2000

B37988, 50 VDC, 6,5 × 5,0 × 2,5 mm

220 nF	B37988N5224M0**	2500	2500	2000
330 nF	B37988N5334M0**	2500	2500	2000
470 nF	B37988N5474M0**	2500	2500	2000
680 nF	B37988N5684M0**	2500	2500	2000
1,0 μ F	B37988N5105M0**	2500	2500	2000

1) The table contains the ordering codes for the standard capacitance tolerance.
For other available capacitance tolerances see page 174.

Multilayer Ceramic Capacitors
Z5U (Y5U)
Ordering codes and packing for Z5U (Y5U), 50 VDC, lead spacing 5,0 mm

C _R	Ordering code ¹⁾	Ammo packing	Reel packing	Bulk
		** \triangle 54	** \triangle 51	** \triangle 00
		pcs	pcs/reel	pcs

B37982, 50 VDC, 5,5 × 5,0 × 2,5 mm

10 nF	B37982G5103M0**	2500	2500	2000
15 nF	B37982G5153M0**	2500	2500	2000
22 nF	B37982G5223M0**	2500	2500	2000
33 nF	B37982G5333M0**	2500	2500	2000
47 nF	B37982G5473M0**	2500	2500	2000
68 nF	B37982G5683M0**	2500	2500	2000
100 nF	B37982G5104M0**	2500	2500	2000
150 nF	B37982G5154M0**	2500	2500	2000

B37988, 50 VDC, 6,5 × 5,0 × 2,5 mm

220 nF	B37988G5224M0**	2500	2500	2000
330 nF	B37988G5334M0**	2500	2500	2000
470 nF	B37988G5474M0**	2500	2500	2000
680 nF	B37988G5684M0**	2500	2500	2000
1,0 μ F	B37988G5105M0**	2500	2500	2000

B37985, 50 VDC, 9,0 × 7,5 × 2,5 mm


1,5 μ F	B37985N5155M0**	2000	2000	1000
2,2 μ F	B37985N5225M0**	2000	2000	1000
3,3 μ F	B37985N5335M0**	2000	2000	1000
4,7 μ F	B37985N5475M0**	2000	2000	1000

1) The table contains the ordering codes for the standard capacitance tolerance.
For other available capacitance tolerances see page 174.




Typical characteristics


Capacitance change $\Delta C/C_{25}$ versus temperature T




Capacitance change $\Delta C/C_0$ versus superimposed DC voltage V



Insulation resistance R_{ins} versus temperature T



Dissipation factor $\tan \delta$ versus temperature T




Multilayer Ceramic Capacitors

Z5U (Y5U)


Typical characteristics

Impedance $|Z|$ versus frequency f



- 1: Chip
- 2: 1,5 mm lead length
- 3: 5,0 mm lead length
- 4: 10,0 mm lead length
- 5: 20,0 mm lead length

Capacitance change $\Delta C/C_1$ versus time t



Herausgegeben von EPCOS AG

Unternehmenskommunikation, Postfach 80 17 09, 81617 München, DEUTSCHLAND

☎ ++49 89 636 09, FAX (0 89) 636-2 26 89

© EPCOS AG 2002. Vervielfältigung, Veröffentlichung, Verbreitung und Verwertung dieser Broschüre und ihres Inhalts ohne ausdrückliche Genehmigung der EPCOS AG nicht gestattet.

Bestellungen unterliegen den vom ZVEI empfohlenen Allgemeinen Lieferbedingungen für Erzeugnisse und Leistungen der Elektroindustrie, soweit nichts anderes vereinbart wird.

Diese Broschüre ersetzt die vorige Ausgabe.

Fragen über Technik, Preise und Liefermöglichkeiten richten Sie bitte an den Ihnen nächstgelegenen Vertrieb der EPCOS AG oder an unsere Vertriebsgesellschaften im Ausland. Bauelemente können aufgrund technischer Erfordernisse Gefahrstoffe enthalten. Auskünfte darüber bitten wir unter Angabe des betreffenden Typs ebenfalls über die zuständige Vertriebsgesellschaft einzuholen.

Published by EPCOS AG

Corporate Communications, P.O. Box 80 17 09, 81617 Munich, GERMANY

☎ ++49 89 636 09, FAX (0 89) 636-2 26 89

© EPCOS AG 2002. Reproduction, publication and dissemination of this brochure and the information contained therein without EPCOS' prior express consent is prohibited.

Purchase orders are subject to the General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry recommended by the ZVEI (German Electrical and Electronic Manufacturers' Association), unless otherwise agreed.

This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.