

Main switch, P1, 40 A, rear mounting, 3 pole + N, 1 N/O, 1 N/C, Emergency switching off function, Lockable in the 0 (Off) position, With metal shaft for a control panel depth of 400 mm

Part no. P1-40/M4/SVB/N/HI11
199939
EL Number 1403738
(Norway)

General specifications		
Product name		Eaton Moeller® series P1 Main switch
Part no.		P1-40/M4/SVB/N/HI11
EAN		4015082953614
Product Length/Depth		340 millimetre
Product height		70 millimetre
Product width		86 millimetre
Product weight		0.385 kilogram
Compliances		UKCA CE
Certifications		IEC/EN 60204 IEC/EN 60947 IEC/EN 60947-3
Product Tradename		P1
Product Type		Main switch
Product Sub Type		None
Catalog Notes		Rated Short-time Withstand Current (Icw) for a time of 1 second
Features & Functions		
Features		Version as main switch Version as maintenance-/service switch Version as emergency stop installation
Fitted with:		Red rotary handle and yellow locking ring Metal shaft for a control panel depth of 400 mm
Functions		Emergency switching off function Interlockable
Locking facility		Lockable in the 0 (Off) position
Number of poles		3+N
General information		
Accessories		Auxiliary contact or neutral conductor fitted by user.
Degree of protection		IP65
Degree of protection (front side)		IP65
Lifespan, mechanical		300,000 Operations
Mounting method		Rear mounting
Mounting position		As required
Operating frequency		50 Operations/h
Overvoltage category		III
Pollution degree		3
Rated impulse withstand voltage (Uimp)		6000 V AC
Safe isolation		440 V AC, Between the contacts, According to EN 61140
Shock resistance		15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
Switching angle		90 °
Climatic environmental conditions		
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		50 °C
Ambient operating temperature (enclosed) - min		-25 °C
Ambient operating temperature (enclosed) - max		40 °C
Climatic proofing		Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Terminal capacities		

Terminal capacity		1 x (1 - 4) mm ² , flexible with ferrules to DIN 46228 2 x (1 - 4) mm ² , flexible with ferrules to DIN 46228 1 x 10 mm ² with fork terminal 2 x 10 mm ² with fork terminal
Screw size		M4, Terminal screw
Tightening torque		1.6 Nm, Screw terminals
Electrical rating		
Rated breaking capacity at 400/415 V (cos phi to IEC 60947-3)		290 kA
Rated breaking capacity at 660/690 V (cos phi to IEC 60947-3)		130 kA
Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V		30 A
Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V		30 A
Rated operational current (Ie) at AC-3, 660 V, 690 V		17 A
Rated operational current (Ie) at AC-21, 440 V		40 A
Rated operational current (Ie) at AC-23A, 230 V		40 A
Rated operational current (Ie) at AC-23A, 400 V, 415 V		40 A
Rated operational current (Ie) at AC-23A, 690 V		20 A
Rated operational power at AC-3, 380/400 V, 50 Hz		15 kW
Rated operational power at AC-3, 415 V, 50 Hz		15 kW
Rated operational power at AC-3, 690 V, 50 Hz		15 kW
Rated operational power at AC-23A, 220/230 V, 50 Hz		11 kW
Rated operational power at AC-23A, 400 V, 50 Hz		22 kW
Rated operational power at AC-23A, 690 V, 50 Hz		18.5 kW
Rated operational voltage (Ue) at AC - min		690 V
Rated operational voltage (Ue) at AC - max		690 V
Rated uninterrupted current (Iu)		40 A
Uninterrupted current		Rated uninterrupted current Iu is specified for max. cross-section.
Short-circuit rating		
Rated conditional short-circuit current (Iq)		80 kA
Rated short-time withstand current (Icw)		0.64 kA 640 A, Contacts, 1 second
Short-circuit protection rating		50 A gG/gL, Fuse, Contacts
Switching capacity		
Load rating		1.3 x I# (with intermittent operation class 12, 60 % duty factor) 1.6 x I# (with intermittent operation class 12, 40 % duty factor) 2 x I# (with intermittent operation class 12, 25 % duty factor)
Contacts		
Control circuit reliability		1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
Number of auxiliary contacts (change-over contacts)		0
Number of auxiliary contacts (normally closed contacts)		1
Number of auxiliary contacts (normally open contacts)		1
Actuator		
Actuator color		Red
Actuator type		Door coupling rotary drive
Design verification		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdiss		0 W
Heat dissipation per pole, current-dependent Pvid		1.9 W
Rated operational current for specified heat dissipation (In)		40 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		UV resistance only in connection with protective shield.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of assemblies			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Switch disconnecter (EC000216)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Switch disconnecter (ecl@ss10.0.1-27-37-14-03 [AKF060013])			
Version as main switch			Yes
Version as maintenance-/service switch			Yes
Version as safety switch			No
Version as emergency stop installation			Yes
Version as reversing switch			No
Number of switches			1
Max. rated operation voltage Ue AC		V	690
Rated operating voltage		V	690 - 690
Rated permanent current Iu		A	40
Rated permanent current at AC-23, 400 V		A	40
Rated permanent current at AC-21, 400 V		A	40
Rated operation power at AC-3, 400 V		kW	15
Rated short-time withstand current Icw		kA	0.64
Rated operation power at AC-23, 400 V		kW	22
Switching power at 400 V		kW	22
Conditioned rated short-circuit current Iq		kA	80
Number of poles			4
Number of auxiliary contacts as normally closed contact			1
Number of auxiliary contacts as normally open contact			1
Number of auxiliary contacts as change-over contact			0
Motor drive optional			No
Motor drive integrated			No
Voltage release optional			No
Device construction			Built-in device fixed built-in technique
Suitable for floor mounting			No
Suitable for front mounting 4-hole			No
Suitable for front mounting centre			No
Suitable for distribution board installation			No
Suitable for intermediate mounting			No
Colour control element			Red
Type of control element			Door coupling rotary drive
Interlockable			Yes
Type of electrical connection of main circuit			Screw connection
Degree of protection (IP), front side			IP65

