

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture HARD SURFACE CLEANER

Registration number -

Synonyms None.

Product code UDS000036BU

Issue date 08-November-2022

Version number 1.0

Revision date 08-November-2022

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaners - Heavy duty

Uses advised against None known.

1.3. Details of the supplier of the safety data sheet

Company name CRC Industries UK Ltd.

Address Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom

Telephone +44 1278 727200

Fax +44 1278 425644

E-mail hse.uk@crcind.com

Website www.crcind.com

Company name CRC Industries Europe bv

Address Touwslagerstraat 1
9240 Zele
Belgium

Telephone +32(0)52/45.60.11

Fax +32(0)52/45.00.34

E-mail hse@crcind.com

Website www.crcind.com

1.4. Emergency telephone number Tel.:(+44)(0)1278 72 7200 (office hours: 9-17h GMT)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

Health hazards

Skin corrosion/irritation	Category 2	H315 - Causes skin irritation.
Serious eye damage/eye irritation	Category 1	H318 - Causes serious eye damage.

2.2. Label elements

Label according to Regulation (EC) No. 1272/2008 as amended

Contains: 2-decoxyethanol, Benzenesulfonic acid, C10-13-alkyl derivatives sodium salt

Hazard pictograms



Signal word	Danger
Hazard statements	
H315	Causes skin irritation.
H318	Causes serious eye damage.
Precautionary statements	
Prevention	
P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P280	Wear protective gloves.
Response	
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310	Immediately call a POISON CENTRE/doctor.
Storage	Not assigned.
Disposal	
P501	Dispose of contents/container in accordance with local/regional/national/international regulations.
Supplemental label information	According to Regulation (EC) No. 648/2004 on Detergents, as amended; Contains: 5-15% Non ionic surfactants.
2.3. Other hazards	This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII. The product does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General information

Chemical name	%	CAS-No. / EC No.	REACH Registration No.	Index No.	Notes
Benzenesulfonic acid, C10-13-alkyl derivatives sodium salt	5 - 10	68411-30-3 270-115-0	2119489428-22	-	Classification: Acute Tox. 4;H302, Skin Irrit. 2;H315, Eye Dam. 1;H318, Aquatic Chronic 3;H412
2-decoxyethanol	1 - 5	26183-52-8 500-046-6	-	-	Classification: Acute Tox. 4;H302, Eye Dam. 1;H318

List of abbreviations and symbols that may be used above

#: This substance has been assigned Union workplace exposure limit(s).
ATE: Acute toxicity estimate.
M: M-factor
PBT: persistent, bioaccumulative and toxic substance.
vPvB: very persistent and very bioaccumulative substance.
All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

Composition comments The full text for all H-statements is displayed in section 16.

SECTION 4: First aid measures

General information Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

4.1. Description of first aid measures

Inhalation Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact Remove contaminated clothing. Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention. Wash contaminated clothing before reuse.
Eye contact Rinse with water. Get medical attention if irritation develops and persists.
Ingestion Rinse mouth. Get medical attention if symptoms occur.

4.2. Most important symptoms and effects, both acute and delayed Skin irritation. May cause redness and pain.

4.3. Indication of any immediate medical attention and special treatment needed Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.

SECTION 5: Firefighting measures

General fire hazards No unusual fire or explosion hazards noted.

5.1. Extinguishing media

Suitable extinguishing media Water fog. Foam. Dry chemical powder. Carbon dioxide (CO₂).

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

During fire, gases hazardous to health may be formed.

5.3. Advice for firefighters

Special protective equipment for firefighters Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Special fire fighting procedures Move containers from fire area if you can do so without risk.

Specific methods

Use standard firefighting procedures and consider the hazards of other involved materials.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Do not touch or walk through spilled material.

For emergency responders Keep unnecessary personnel away. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained.

6.2. Environmental precautions

Avoid discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use.

6.4. Reference to other sections

For personal protection, see section 8 of the SDS. For waste disposal, see section 13 of the SDS.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid contact with eyes, skin, and clothing. Provide adequate ventilation. Wear appropriate personal protective equipment. Observe good industrial hygiene practices.

7.2. Conditions for safe storage, including any incompatibilities

Keep container tightly closed. Store away from incompatible materials (see Section 10 of the SDS). Storage class (TRGS 510): 10 (Combustible liquids that cannot be assigned to any of the above storage classes)

7.3. Specific end use(s)

Not available.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits No exposure limits noted for ingredient(s).

Biological limit values No biological exposure limits noted for the ingredient(s).

Recommended monitoring procedures Not available.

Derived no effect levels (DNELs)

General population

Components	Value	Assessment factor	Notes
2-[bis(2-hydroxyethyl)amino]ethanol (CAS 102-71-6)			
Long-term, Local, Inhalation	0.4 mg/m ³	36	Repeated dose toxicity
Long-term, Systemic, Dermal	2.66 mg/kg	100	Repeated dose toxicity

Workers

Components	Value	Assessment factor	Notes
2-[bis(2-hydroxyethyl)amino]ethanol (CAS 102-71-6)			
Long-term, Local, Inhalation	1 mg/m ³		Repeated dose toxicity
Long-term, Systemic, Dermal	7.5 mg/kg	50	Repeated dose toxicity

Predicted no effect concentrations (PNECs)

Components	Value	Assessment factor	Notes
2-[bis(2-hydroxyethyl)amino]ethanol (CAS 102-71-6)			
Freshwater	0.32 mg/l	50	

Sediment (freshwater)	1.7 mg/kg	
Soil	0.151 mg/kg	
STP	10 mg/l	100

8.2. Exposure controls

Appropriate engineering controls

Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station and safety shower.

Individual protection measures, such as personal protective equipment

General information

Use personal protective equipment as required. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.

Eye/face protection

Wear safety glasses with side shields (or goggles). Use eye protection conforming to EN 166.

Skin protection

- Hand protection

When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through. Neoprene. Suitable gloves can be recommended by the glove supplier.

- Other

Wear appropriate chemical resistant clothing. Use of an impervious apron is recommended.

Respiratory protection

In case of insufficient ventilation, wear suitable respiratory equipment. Chemical respirator with organic vapour cartridge and full facepiece. (Filter type ABEK)

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

Hygiene measures

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

Environmental exposure controls

Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. Fume scrubbers, filters or engineering modifications to the process equipment may be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state Liquid.

Form Not available.

Colour Not available.

Odour Not available.

Odour threshold Not available.

pH 10.3

Melting point/freezing point Not available.

Initial boiling point and boiling range 100 °C (212 °F)

Flash point Not available.

Evaporation rate Not available.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Explosive limit - lower (%) Not available.

Explosive limit – upper (%) Not available.

Vapour pressure Not available.

Vapour density Not available.

Relative density 1.03 g/cm³ 20 °C

Solubility(ies)

Solubility (water) Not available.

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature > 200 °C (> 392 °F)

Decomposition temperature Not available.

Viscosity	Not available.
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.
9.2. Other information	No relevant additional information available.

SECTION 10: Stability and reactivity

10.1. Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
10.4. Conditions to avoid	Not available.
10.5. Incompatible materials	Strong oxidising agents.
10.6. Hazardous decomposition products	Not available.

SECTION 11: Toxicological information

General information	Occupational exposure to the substance or mixture may cause adverse effects.
---------------------	--

Information on likely routes of exposure

Inhalation	May cause allergy or asthma symptoms or breathing difficulties if inhaled.
Skin contact	Causes skin irritation. May cause an allergic skin reaction.
Eye contact	Direct contact with eyes may cause temporary irritation.
Ingestion	May cause discomfort if swallowed. However, ingestion is not likely to be a primary route of occupational exposure.

Symptoms	Skin irritation. May cause redness and pain.
----------	--

11.1. Information on toxicological effects

Acute toxicity	Based on available data, the classification criteria are not met.
----------------	---

Product	Species	Test Results
HARD SURFACE CLEANER		
<u>Acute</u>		
Oral		
ATEmix		6677.8 mg/kg bw

Components	Species	Test Results
Benzenesulfonic acid, C10-13-alkyl derivatives sodium salt (CAS 68411-30-3)		
<u>Acute</u>		
Dermal		
LD50	Rat	> 2000 mg/kg
Oral		
LD50	Rat	1080 mg/kg

Skin corrosion/irritation	Causes skin irritation.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.
Respiratory sensitisation	Based on available data, the classification criteria are not met.
Skin sensitisation	Based on available data, the classification criteria are not met.
Germ cell mutagenicity	Based on available data, the classification criteria are not met.
Carcinogenicity	Based on available data, the classification criteria are not met.
Reproductive toxicity	Based on available data, the classification criteria are not met.
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are not met.
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.
Aspiration hazard	Based on available data, the classification criteria are not met.
Mixture versus substance information	Not available.
Other information	May cause allergic respiratory and skin reactions.

SECTION 12: Ecological information

12.1. Toxicity

The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Components	Species		Test Results
Benzenesulfonic acid, C10-13-alkyl derivatives sodium salt (CAS 68411-30-3)			
Aquatic			
Acute			
Crustacea	EC50	Daphnia magna	2.9 mg/l, 48 hours
Fish	LC50	Bluegill (Lepomis macrochirus)	1.67 mg/l, 96 hours
12.2. Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.		
12.3. Bioaccumulative potential			
Partition coefficient n-octanol/water (log Kow)	Not available.		
Bioconcentration factor (BCF)	Not available.		
12.4. Mobility in soil	No data available.		
12.5. Results of PBT and vPvB assessment	This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.		
12.6. Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.		

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.
EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.
Special precautions	Dispose in accordance with all applicable regulations.

SECTION 14: Transport information

ADR

14.1. - 14.6.: Not regulated as dangerous goods.

RID

14.1. - 14.6.: Not regulated as dangerous goods.

ADN

14.1. - 14.6.: Not regulated as dangerous goods.

IATA

14.1. - 14.6.: Not regulated as dangerous goods.

IMDG

14.1. - 14.6.: Not regulated as dangerous goods.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not established.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Retained direct EU regulations

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended

Not listed.

Regulation (EU) 2019/1021 On persistent organic pollutants (recast), as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended
Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended
Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended
Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended
Not listed.

Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry, as amended
Not listed.

Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA
Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended
Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended
Not listed.

Other EU regulations

Directive 2012/18/EU on major accident hazards involving dangerous substances, as amended
1,2-benzisothiazol-3(2H)-one;1,2-benzisothiazolin-3-one (CAS 2634-33-5)

Other regulations

Not available.

15.2. Chemical safety assessment

No Chemical Safety Assessment has been carried out.

SECTION 16: Other information

List of abbreviations

ADN: European Agreement Concerning the International Carriage of Dangerous Goods by Inland Waterways.
ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.
ADR: European Agreement Concerning the International Carriage of Dangerous Goods by Road.
ATE: Acute Toxicity Estimate according to REGULATION (EC) No 1272/2008 (CLP).
CAS: Chemical Abstract Service.
Ceiling: Short Term Exposure Limit Ceiling value.
CEN: European Committee for Standardization.
CLP: Classification, Labeling and Packaging REGULATION (EC) No 1272/2008 on classification, labeling and packaging of substances and mixtures.
GWP: Global Warming Potential.
IATA: International Air Transport Association.
IBC Code: International Code for the Construction and Equipment of Ships Carrying Dangerous Chemicals in Bulk.
IMDG: International Maritime Dangerous Goods.
MAK: Threshold limit values Germany (Maximale Arbeitsplatzkonzentration - DFG).
MARPOL: International Convention for the Prevention of Pollution from Ships.
PBT: Persistent, bioaccumulative and toxic.
REACH: Registration, Evaluation and Authorization of Chemicals (REGULATION (EC) No 1907/2006 concerning Registration, Evaluation Authorization and Restriction of Chemicals).
RID: Regulations concerning the international carriage of dangerous goods by rail (Règlement International concernant le transport de marchandises dangereuses par chemin de fer).
RID: Regulations concerning the International Carriage of Dangerous Goods by Rail.
STEL: Short term exposure limit.
TLV: Threshold Limit Value.
TWA: Time Weighted Average.
VOC: Volatile organic compounds.
vPvB: Very persistent and very bioaccumulative.
STEL: Short-term Exposure Limit.

References

Not available.

Information on evaluation method leading to the classification of mixture

Not available.

Full text of any statements, which are not written out in full under sections 2 to 15

H302 Harmful if swallowed.

Revision information**Training information****Disclaimer**

H315 Causes skin irritation.
H318 Causes serious eye damage.
H412 Harmful to aquatic life with long lasting effects.

None.

Not available.

CRC Industries Europe UK Limited cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC. The products are governed by Regulation (EC) No 1272/2008 on the classification, labelling and packaging of substances and mixtures (CLP); Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (in each case, as amended and replaced) and other applicable laws. It is an importers or downstream users responsibility to ensure compliance of product they import. An SDS provided in the official language(s) of a country is not a guarantee of compliance in that country.