

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture HYDRAULIC OIL SUPER 46 FG

Registration number -

Synonyms None.

Product code BDS000822BU

Issue date 26-January-2023

Version number 1.0

Revision date 26-January-2023

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Lubricants

Uses advised against None known.

1.3. Details of the supplier of the safety data sheet

Company name CRC Industries UK Ltd.

Address Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom

Telephone +44 1278 727200

Fax +44 1278 425644

E-mail hse.uk@crcind.com

Website www.crcind.com

Company name CRC Industries Europe bv

Address Touwslagerstraat 1
9240 Zele
Belgium

Telephone +32(0)52/45.60.11

Fax +32(0)52/45.00.34

E-mail hse@crcind.com

Website www.crcind.com

1.4. Emergency telephone number Tel.:(+44)(0)1278 72 7200 (office hours: 9-17h GMT)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

This mixture does not meet the criteria for classification according to Regulation (EC) 1272/2008 as amended.

2.2. Label elements

Label according to Regulation (EC) No. 1272/2008 as amended

Hazard pictograms None.

Signal word None.

Hazard statements The mixture does not meet the criteria for classification.

Precautionary statements

Prevention Not assigned.

Response Not assigned.

Storage Not assigned.

Disposal	Not assigned.
Supplemental label information	None.
2.3. Other hazards	This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII. The mixture does not contain any substances included in the list established in accordance with REACH Article 59(1) for having endocrine disrupting properties at a concentration equal to or greater than 0.1% by weight.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

The components are not hazardous or are below required disclosure limits.

List of abbreviations and symbols that may be used above

ATE: Acute toxicity estimate.

M: M-factor

vPvB: very persistent and very bioaccumulative substance.

PBT: persistent, bioaccumulative and toxic substance.

#: This substance has been assigned Union workplace exposure limit(s).

All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

SECTION 4: First aid measures

General information Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

4.1. Description of first aid measures

Inhalation Move to fresh air. Call a physician if symptoms develop or persist.

Skin contact Wash off with soap and water. Get medical attention if irritation develops and persists.

Eye contact Rinse with water. Get medical attention if irritation develops and persists.

Ingestion Rinse mouth. Get medical attention if symptoms occur.

4.2. Most important symptoms and effects, both acute and delayed Exposure may cause temporary irritation, redness, or discomfort.

4.3. Indication of any immediate medical attention and special treatment needed Treat symptomatically.

SECTION 5: Firefighting measures

General fire hazards No unusual fire or explosion hazards noted.

5.1. Extinguishing media

Suitable extinguishing media Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture During fire, gases hazardous to health may be formed.

5.3. Advice for firefighters

Special protective equipment for firefighters Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Special fire fighting procedures Move containers from fire area if you can do so without risk.

Specific methods Use standard firefighting procedures and consider the hazards of other involved materials.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel Wear appropriate personal protective equipment.

For emergency responders Keep unnecessary personnel away. For personal protection, see section 8 of the SDS.

6.2. Environmental precautions Avoid discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

The product is immiscible with water and will spread on the water surface.

Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use.

6.4. Reference to other sections

For personal protection, see section 8 of the SDS. For waste disposal, see section 13 of the SDS.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Observe good industrial hygiene practices.

7.2. Conditions for safe storage, including any incompatibilities

Store in tightly closed container. Store away from incompatible materials (see Section 10 of the SDS).

Storage class (TRGS 510): 10 (Combustible liquids that cannot be assigned to any of the above storage classes)

7.3. Specific end use(s)

Observe industrial sector guidance on best practices.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

No exposure limits noted for ingredient(s).

Biological limit values

No biological exposure limits noted for the ingredient(s).

Recommended monitoring procedures

Follow standard monitoring procedures.

Derived no effect levels (DNELs)

Not available.

Predicted no effect concentrations (PNECs)

Not available.

8.2. Exposure controls

Appropriate engineering controls

Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

General information

Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.

Eye/face protection

Use eye protection conforming to EN 166. Wear safety glasses with side shields (or goggles).

Skin protection

- Hand protection

For accidental contact the use of disposable gloves should be sufficient provided they are changed immediately after a splash or spill may occur. If intentional contact is expected reusable gloves should be used with a breakthrough time greater than the total duration of the product use. Nitrile gloves are recommended.

- Other

Wear suitable protective clothing.

Respiratory protection

Not necessary in normal use. In case of insufficient ventilation, wear suitable respiratory equipment. Chemical respirator with organic vapour cartridge. (Filter type A)

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

Hygiene measures

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

Environmental exposure controls

Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. Fume scrubbers, filters or engineering modifications to the process equipment may be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state

Liquid.

Form

Liquid.

Colour

Colourless.

Odour	Odourless.
Odour threshold	Not available.
pH	Not applicable.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash point	252.0 °C (485.6 °F)
Evaporation rate	Not applicable.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Explosive limit - lower (%)	Not available.
Explosive limit – upper (%)	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	0.83 g/cm3
Solubility(ies)	
Solubility (water)	Insoluble in water
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	> 200 °C (> 392 °F)
Decomposition temperature	Not available.
Viscosity	Not available.
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.
9.2. Other information	
Kinematic viscosity	46 cSt at 40°C
VOC	0 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
10.4. Conditions to avoid	Contact with incompatible materials.
10.5. Incompatible materials	Strong oxidising agents.
10.6. Hazardous decomposition products	Not available.

SECTION 11: Toxicological information

General information	Occupational exposure to the substance or mixture may cause adverse effects.
Information on likely routes of exposure	
Inhalation	Based on available data, the classification criteria are not met.
Skin contact	Based on available data, the classification criteria are not met.
Eye contact	Based on available data, the classification criteria are not met.
Ingestion	May cause discomfort if swallowed. However, ingestion is not likely to be a primary route of occupational exposure.
Symptoms	Exposure may cause temporary irritation, redness, or discomfort.
11.1. Information on toxicological effects	
Acute toxicity	Based on available data, the classification criteria are not met.
Skin corrosion/irritation	Based on available data, the classification criteria are not met.
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met.
Respiratory sensitisation	Based on available data, the classification criteria are not met.
Skin sensitisation	Based on available data, the classification criteria are not met.

Germ cell mutagenicity	Based on available data, the classification criteria are not met.
Carcinogenicity	Based on available data, the classification criteria are not met.
Reproductive toxicity	Based on available data, the classification criteria are not met.
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are not met.
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.
Aspiration hazard	Based on available data, the classification criteria are not met.
Mixture versus substance information	Not available.
Other information	This product has no known adverse effect on human health.

SECTION 12: Ecological information

12.1. Toxicity	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
12.2. Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.
12.3. Bioaccumulative potential	No data available.
Partition coefficient n-octanol/water (log Kow)	Not available.
Bioconcentration factor (BCF)	Not available.
12.4. Mobility in soil	No data available.
12.5. Results of PBT and vPvB assessment	This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.
12.6. Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

SECTION 13: Disposal considerations

13.1. Waste treatment methods	
Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.
EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site.
Special precautions	Dispose in accordance with all applicable regulations.

SECTION 14: Transport information

ADR	14.1. - 14.6.: Not regulated as dangerous goods.
RID	14.1. - 14.6.: Not regulated as dangerous goods.
ADN	14.1. - 14.6.: Not regulated as dangerous goods.
IATA	14.1. - 14.6.: Not regulated as dangerous goods.
IMDG	14.1. - 14.6.: Not regulated as dangerous goods.
14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not established.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture	
Retained direct EU regulations	

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended

Not listed.

Regulation (EU) 2019/1021 On persistent organic pollutants (recast), as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended

Not listed.

Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry, as amended

Not listed.

Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA

Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended

Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended

Not listed.

Other EU regulations

Directive 2012/18/EU on major accident hazards involving dangerous substances, as amended

Not listed.

Other regulations

This product is classified and labelled in accordance with the retained CLP Regulation (EC) No 1272/2008, as amended for Great Britain. This Safety Data Sheet is compiled in accordance with REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758.

Follow national regulation for work with chemical agents in accordance with Directive 98/24/EC, as amended.

15.2. Chemical safety assessment

No Chemical Safety Assessment has been carried out.

SECTION 16: Other information

List of abbreviations

ADN: European Agreement Concerning the International Carriage of Dangerous Goods by Inland Waterways.
ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.
ADR: European Agreement Concerning the International Carriage of Dangerous Goods by Road.
AGW: Occupational threshold limit value (Arbeitsplatzgrenzwert – Germany).
ATE: Acute Toxicity Estimate according to REGULATION (EC) No 1272/2008 (CLP).
CAS: Chemical Abstract Service.
Ceiling: Short Term Exposure Limit Ceiling value.
CEN: European Committee for Standardization.
CLP: Classification, Labeling and Packaging REGULATION (EC) No 1272/2008 on classification, labeling and packaging of substances and mixtures.
GWP: Global Warming Potential.
IATA: International Air Transport Association.
IBC Code: International Code for the Construction and Equipment of Ships Carrying Dangerous Chemicals in Bulk.
IMDG: International Maritime Dangerous Goods.
MAC: Maximum Allowed Concentration.
MAK: Threshold limit values Germany (Maximale Arbeitsplatzkonzentration - DFG).
MARPOL: International Convention for the Prevention of Pollution from Ships.
PBT: Persistent, bioaccumulative and toxic.
REACH: Registration, Evaluation and Authorization of Chemicals (REGULATION (EC) No 1907/2006 concerning Registration, Evaluation Authorization and Restriction of Chemicals).
RID: Regulations concerning the international carriage of dangerous goods by rail (Règlement International concernant le transport de marchandises dangereuses par chemin de fer).
RID: Regulations concerning the International Carriage of Dangerous Goods by Rail.
STEL: Short term exposure limit.
TLV: Threshold Limit Value.
TWA: Time Weighted Average.
VLE: Exposure Limit Value.

VME: Exposure Average Value.
VOC: Volatile organic compounds.
vPvB: Very persistent and very bioaccumulative.
STEL: Short-term Exposure Limit.

References

Not available.

Information on evaluation method leading to the classification of mixture

The classification for health and environmental hazards is derived by a combination of calculation methods and test data, if available.

Full text of any statements, which are not written out in full under sections 2 to 15

None.

Revision information

None.

Training information

Follow training instructions when handling this material.

Disclaimer

CRC Industries Europe UK Limited cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC. The products are governed by Regulation (EC) No 1272/2008 on the classification, labelling and packaging of substances and mixtures (CLP); Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (in each case, as amended and replaced) and other applicable laws. It is an importers or downstream users responsibility to ensure compliance of product they import. An SDS provided in the official language(s) of a country is not a guarantee of compliance in that country.