



**Part Number :** [459854924](#)

**Product Description :** EXTreme LPHPower Header, Right-Angle, 4 Power Contacts, Select Gold (Au) Plating, for 2.36mm Thick PC Board with Guide and Press-fit Plastic Pegs

**Series Number :** 45985

**Status :** Active

**Product Category :** Board-to-Board Connectors



---

## Documents & Resources

### Drawings

[Drawing 459854924\\_sd.pdf](#)

[Packaging Design Drawing PK-45984-001-001.pdf](#)

### 3D Models and Design Files

[3D Model 459854924\\_stp.zip](#)

[3D Model PDF 459854924.pdf](#)

[Symbol Footprint Data SYM-45985-4914-001.zip](#)


### Specifications

[Product Specification PS-45984-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Board-to-Board Connectors
Series	45985
Description	EXTreme LPHPower Header, Right-Angle, 4 Power Contacts, Select Gold (Au) Plating, for 2.36mm Thick PC Board with Guide and Press-fit Plastic Pegs
Application	Board-to-Board, Power
Comments	4 Power Blades
Component Type	PCB Header
Product Family	EXTreme LPHPower Connectors
Product Name	EXTreme LPHPower
UPC	800756692586

#### Agency

CSA	LR19980
UL	E29179

#### Electrical

Current - Maximum per Contact	30.0A
Voltage - Maximum	250V AC (RMS)/DC

#### Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4

Color - Resin	Black
Durability (mating cycles max)	250
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.842/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	3.60mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.36mm
Pitch - Mating Interface	12.00mm
Pitch - Termination Interface	2.00mm, 2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Polarized to PCB	No
(p)ower-(s)ignal Configuration	4p - 0s
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

#### Solder Process Data

Max-Duration	15
Lead-Free Process Capability	SMC&WAVE

Max-Cycle	3
Max-Temp	230

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
EXTreme LPHPower Right-Angle PCB Receptacles	<u>45984</u>

---

---

This document was generated on Aug 24, 2023