




Part Number : [461146160](#)

Product Description : 1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, with BMI Guides

Series Number : 46114

Status : Active

Product Category : Board-to-Board Connectors



Documents & Resources

Drawings

[Drawing 461146160_sd.pdf](#)

[Packaging Design Drawing PK-46114-003-001.pdf](#)

3D Models and Design Files

[3D Model 461146160_stp.zip](#)

[3D Model PDF 461146160.pdf](#)

[Symbol Footprint Data SYM-46114-6160-001.zip](#)


Specifications

[Application Specification AS-46114-001-001.pdf](#)

[Product Specification PS-46114-001-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2023)3788-DC (14 Jun 2023) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|----------------|--|
| Status | Active |
| Category | Board-to-Board Connectors |
| Series | 46114 |
| Description | 1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 6 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, with BMI Guides |
| Application | Board-to-Board, Power |
| Comments | Press Fit Pin |
| Component Type | PCB Receptacle |
| Product Family | EXTreme LPHPower Connectors |
| Product Name | EXTreme LPHPower |
| UPC | 800756886671 |

Agency

| | |
|-----|---------|
| CSA | LR19880 |
| UL | E29179 |

Electrical

| | |
|-------------------------------|------------------|
| Current - Maximum per Contact | 30.0A |
| Grounding to PCB | No |
| Voltage - Maximum | 250V AC (RMS)/DC |

Physical

| | |
|--------------------|----|
| Circuits (Loaded) | 22 |
| Circuits (maximum) | 22 |

| | |
|--------------------------------|--------------------------------|
| Color - Resin | Black |
| Durability (mating cycles max) | 250 |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | Yes |
| Keying to Mating Part | None |
| Lock to Mating Part | None |
| Material - Metal | High Performance Alloy (HPA) |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 8.194/g |
| Number of Rows | 2 |
| Orientation | Vertical |
| Packaging Type | Tube |
| PCB Locator | No |
| PCB Retention | None |
| Pitch - Mating Interface | 1.27mm, 12.00mm |
| Pitch - Termination Interface | 1.27mm, 2.50mm |
| Plating min - Mating | 0.762µm |
| Plating min - Termination | 2.540µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| (p)ower-(s)ignal Configuration | 6p - 16s |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface Style | Through Hole - Compliant Pin |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|------------------------------------|--------------|
| EXTreme LPHPower Right-Angle Plugs | <u>45985</u> |

Application Tooling

Global

| Description | Part Number |
|---|-------------------|
| LPH Vertical Receptacle Power Terminal Removal Tool | <u>0621006300</u> |
| Vertical Receptacle Press-In Tool | <u>0622018672</u> |

This document was generated on Aug 24, 2023