


Electro-Holding Magnet: 25mm

Energise To Hold ElectroMagnet

Technical Data

Mountings	Threaded holes in rear face
Finish	Bright nickel-plated with machined face
Weight	66g
Typical Holding Force	15.0kg
ED Rating	100%
IP Rating	54
Standard Operating Voltage	12VDC M52172/12VDC 24VDC M52172/24VDC
Current	12V - 180mA 24V - 90mA
Typical Power	2.1 -2.2W
Connection Type	12VDC & 24VDC Free Leads (500mm Long)




Recommended Armature Plate


Finish	Bright nickel-plated
Diameter	25mm
Height	3mm
Screw	M3
Part Number	M52171/25ARM
Weight	15g



Leads:
1 Red & 1 Black
0.3mm Square
500mm Long




3 Holes Tapped M3
Coarse x 5mm Deep
on 15mm P.C.D.



Tapped M4 Coarse
x 10mm Deep

Electro-Holding Magnet: 25mm

Air Gap (mm)	Pull Force* (kg)
0.00	15.00
0.09	5.10
0.18	2.20
0.27	1.20
0.36	0.80
0.59	0.40
1.00	0.20



* +/- 10% at room temperature

To achieve the optimum pull force 100% contact area must be achieved using the recommended armature plate. The force will be affected if other material specifications, thicknesses and surfaces are used, or if the armature fails to make positive contact over the full diameter of the face of the magnet.

Where misalignment is likely to be an issue we recommend that an oversized armature plate is used to ensure 100% full contact, this however will reduce the stated pull force by approximately 10%.