



# Aggregate and measure large currents in multi-cable circuits




# Measuring large currents and multi-cable circuits with sum functionality



Once a current sensor has been attached to each branch cable, the CT9557 adds the sensor signals together to create a total signal. Since the device can treat multiple sensors as a single sensor, as illustrated in the figure above, the current can be measured using a single power meter.

## Using a data logger to perform high-precision current measurement



Data logger, high-precision voltmeter, etc.

In this setup, waveform output is monitored on the DC current side, and RMS output is monitored on the AC current side of the circuit. Even a logger that lacks RMS conversion functionality can be used to measure AC current. A wireless logger can also be used. If a high-precision voltmeter is used, both the AC and DC currents can be measured with a high degree of precision.



## Compatible products

AC/DC CURRENT SENSOR (pass-through type) AC/DC CURRENT PROBE (clamp-on type) AC/DC CURRENT BOX (direct-connect type)

For details on supported products, please refer to the following product pages.

CT9555	CT9556	CT9557

The CT9555 series with CT9900 can also be used as a replacement for Hioki's legacy 9555-10.

### **Specifications**

Specifications (Accuracy guaranteed for 1 year, Post-adjustment accuracy guaranteed for 1 year)					
Model	SENSOR UNIT CT9557		SENSOR UNIT CT9556		SENSOR UNIT CT9555
Model No. (Order Code)	CT9557		CT9556		CT9555
	Waveform output ——————————————————————————————————	Total RMS output (BNC terminal)  Total waveform output (BNC terminal)	Waveform output (BNC terminal)	RMS output (BNC terminal)	Waveform output (BNC terminal)
Appearance	Front 9 9 9 9 9 Sensor inputs	Rear Total waveform output	Front Sensor inputs	A Comment	Front Sensor inputs
	(Hioki ME15W female terminal)	(Hioki ME15W female terminal)	(Hioki ME15W female	terminal)	(Hioki ME15W female terminal)
Connectable current sensors	Current sensors with a Hioki ME15W (male) output connector (CT686x-05, CT687x,CT684x-05, etc.)				
Output voltage	Waveform output/ total waveform output: 2 V f.s. Total RMS output: 2 V DC f.s.		Waveform output: 2 V f.s. RMS output: 2 V DC f.s.		Waveform output: 2 V f.s.
Output resistance	50 Ω				
Operating temperature range	-10 °C to 50 °C (14 °F to 122 °F)				
Product warranty period	3 year				
Power supply	AC Adapter Z1002 (100 to 240 v power when used with sensors:     External power supply (10 to 30 V DC; maximum rated)	AC Adapter Z1008 (100 to 240 V AC, 50/60 Hz, maximum rated power when used with sensors: 45 VA)     External power supply (10 to 30 V DC; maximum rated power: 15 VA)			
Response time	0.8 s for both RMS output and total RMS output (when the input value changes as follows: 0% to 90%, 100% to 10%)		Not defined		Not defined
Dimensions	116 mm (4.57 in)W $\times$ 67 mm (2.64 in)H $\times$ 132 mm (5.20 in)D mm (excluding protruding parts)		33 mm (1.30 in)W $\times$ 67 mm (2.64 in)H $\times$ 132 mm (5.20 in)D mm (excluding protruding parts)		
Mass	420 g (14.8 oz)		200 g (7.1 oz)		
Accessories	AC Adapter Z1002, power cord, user manual		AC Adapter Z1008, power cord, user manual		

#### Total waveform output accuracy (CT9557)

Frequency		су	Amplitude accuracy	Phase accuracy	
Ī	DC		±0.06 %rdg. ±0.03 %f.s.	Not defined	
	$DC \le f \le$	1 kHz	±0.06 %rdg. ±0.03 %f.s.	±0.1 deg.	
	1 kHz < f ≤	10 kHz	±0.10 %rdg. ±0.03 %f.s.	±1.0 deg.	
	10 kHz < f ≤	100 kHz	±0.20 %rdg. ±0.10 %f.s.	±(0.1×f kHz) deg.	
	100 kHz < f ≤	300 kHz	±1.0 %rdg. ±0.20 %f.s.		
	300 kHz < f ≤	700 kHz	±5.0 %rdg. ±0.20 %f.s.		
	700 kHz < f ≤	1 MHz	±10.0 %rdg. ±0.50 %f.s.		

#### Total RMS output accuracy (CT9557), RMS output accuracy (CT9556)

Frequency	Accuracy
DC	±0.2 %rdg. ±0.1 %f.s.
5 Hz < f ≤ 10 Hz	±0.3 %rdg. ±0.5 %f.s.
10 Hz < f < 45 Hz	±0.2 %rdg. ±0.2 %f.s.
45 Hz ≤ f ≤ 66 Hz	±0.2 %rdg. ±0.1 %f.s.
66 Hz < f ≤ 10 kHz	±0.2 %rdg. ±0.2 %f.s.
10 kHz < f ≤ 100 kHz	±0.3 %rdg. ±0.5 %f.s.
$100 \text{ kHz} < f \le 300 \text{ kHz}$	±5.0 %rdg. ±0.5 %f.s.
300 kHz < f ≤ 700 kHz	±7.0 %rdg. ±0.5 %f.s.
700 kHz < f < 1 MHz	+10.0 %rda. +1.0 %f.s.

#### **Options**



CONNECTION CABLE CT9904 HIOKI ME15W (12 pin) terminal to ME15W (12 pin) terminal, 1 m (3.28 ft) length (for connecting CT9557 total output to PW6001 or PW3390 only)



## **CONNECTION CORD** L9217 Cord has insulated BNC

connectors at both ends. 1.6 m (5.25 ft) length



# CONNECTION CORD 9165 Cord has metallic BNC

connectors at both ends. use at metallic terminal, 1.5 m (4.92 ft) length



CONVERSION CABLE CT9901 HIOKI ME15W (12 pin) to HIOKI PL23 (10 pin) connector



CONVERSION CABLE CT9900 HIOKI PL23 (10 pin) to HIOKI ME15W (12 pin) connector

Note: Company names and product names appearing in this catalog are trademarks or registered trademarks of various companies



#### **HEADQUARTERS**

81 Koizumi. Ueda, Nagano 386-1192 Japan https://www.hioki.com/



Scan for all regional contact information

DISTRIBUTED BY