

SILICON PLANAR EPITAXIAL TRANSISTOR



N-P-N transistor in a TO-39 metal envelope primarily intended for use as a print hammer drive. It has good high current saturation characteristics.

QUICK REFERENCE DATA


Collector-base voltage (open emitter)	V_{CBO}	max.	100 V
Collector-emitter voltage (open base)	V_{CEO}	max.	60 V
Collector current (peak value)	I_{CM}	max.	5,0 A
Total power dissipation up to $T_{case} = 50^{\circ}\text{C}$	P_{tot}	max.	5,0 W
Junction temperature	T_j	max.	175 $^{\circ}\text{C}$
D.C. current gain $I_C = 2 \text{ A}; V_{CE} = 2 \text{ V}$	h_{FE}	>	40
Transition frequency at $f = 35 \text{ MHz}$ $I_C = 0,5 \text{ A}; V_{CE} = 5 \text{ V}$	f_T	typ.	100 MHz
Turn-off time when switched from $I_{Con} = 5 \text{ A}; I_{Bon} = 0,5 \text{ A}$ to cut-off with $-I_{Boff} = 0,5 \text{ A}$	t_{off}	<	1,2 μs

MECHANICAL DATA

Dimensions in mm

Fig. 1 TO-39.

Collector connected to case



Maximum lead diameter is guaranteed only for 12,7 mm.

Accessories: 56245 (distance disc).

RATINGS

Limiting values in accordance with the Absolute Maximum System (IEC 134)

Collector-base voltage (open emitter)	V_{CBO}	max.	100 V
Collector-emitter voltage ($R_{BE} \leq 50 \Omega$)	V_{CER}	max.	80 V
Collector-emitter voltage (open base)	V_{CEO}	max.	60 V
Emitter-base voltage (open collector)	V_{EBO}	max.	5 V
Collector current (d.c.)	I_C	max.	2,0 A
Collector current (peak value)	I_{CM}	max.	5,0 A
Base current (d.c.)	I_B	max.	1,0 A
Total power dissipation up to $T_{case} = 50^\circ\text{C}$	P_{tot}	max.	5,0 W
Storage temperature	T_{stg}		-55 to +175 °C
Junction temperature	T_j	max.	175 °C

THERMAL RESISTANCE

From junction to case	$R_{th j-c}$	=	25 K/W
-----------------------	--------------	---	--------

CHARACTERISTICS

$$T_j = 25^\circ\text{C}$$

Collector cut-off current

$$I_E = 0; V_{CB} = 60 \text{ V} \quad I_{CBO} < 10 \mu\text{A}$$

Emitter cut-off current

$$I_C = 0; V_{EB} = 4 \text{ V} \quad I_{EBO} < 10 \mu\text{A}$$

Saturation voltages

$$I_C = 5 \text{ A}; I_B = 0,5 \text{ A} \quad V_{CEsat} < 1,0 \text{ V}$$

$$V_{BEsat} < 1,8 \text{ V}$$

D.C. current gain

$$I_C = 2 \text{ A}; V_{CE} = 2 \text{ V} \quad h_{FE} > 40$$

Collector capacitance at $f = 1 \text{ MHz}$

$$I_E = I_e = 0; V_{CB} = 10 \text{ V} \quad C_c < 80 \text{ pF}$$

Transition frequency at $f = 35 \text{ MHz}$

$$I_C = 0,5 \text{ A}; V_{CE} = 5 \text{ V} \quad f_T \text{ typ. } 100 \text{ MHz}$$

Switching times

$$I_{Con} = 5 \text{ A}; I_{Bon} = -I_{Boff} = 0,5 \text{ A}$$

$$-V_{BEoff} = 2 \text{ V}$$

turn-on time

$$t_{on} < 0,6 \mu\text{s}$$

turn-off time

$$t_{off} < 1,2 \mu\text{s}$$




Fig. 2.

Safe Operating Area

- I Region of permissible d.c. operation
- II Permissible extension for repetitive pulsed operation
- III D.C. operation in this region is allowable, provided $R_{BE} \leq 50 \Omega$.

BSV64




Fig. 3.




Fig. 4.




Fig. 5.




Fig. 6.




Fig. 7.