

## Leiterplatten Adapter Han Q7/0 2,4mm




Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 12 000 9908  |
| Specification      | Leiterplatten Adapter Han Q7/0 2,4mm  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09120009908">https://b2b.harting.com/09120009908</a> |

### Identification

|                              |                               |
|------------------------------|-------------------------------|
| Category                     | Accessories                   |
| Type of accessory            | PCB adapter                   |
| Description of the accessory | In the Han <sup>®</sup> Q 7/0 |

### Version

|         |                        |
|---------|------------------------|
| Gender  | Female                 |
| Details | for PCB's up to 2.4 mm |

### Technical characteristics

|                       |                 |
|-----------------------|-----------------|
| Rated current         | 7.5 A           |
| Rated voltage         | 250 V           |
| Rated impulse voltage | 4 kV            |
| Pollution degree      | 3               |
| Limiting temperature  | -40 ... +125 °C |

### Material properties

|                             |  |
|-----------------------------|--|
| Material (insert)           | Polycarbonate (PC)                                     |
| RoHS                        | compliant with exemption                               |
| RoHS exemptions             | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                  | compliant with exemption                               |
| China RoHS                  | 50   |
| REACH Annex XVII substances | Not contained  |
| REACH ANNEX XIV substances  | Not contained  |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                              |
|--------------------------------------|------------------------------|
| REACH SVHC substances                | Yes                          |
| REACH SVHC substances                | Lead                         |
| California Proposition 65 substances | Yes                          |
| California Proposition 65 substances | Lead<br>Nickel               |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08)         |
| Requirement set with Hazard Levels   | R22 (HL 1-3)<br>R23 (HL 1-3) |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 10                                       |
| Net weight                     | 2.8 g                                    |
| Country of origin              | Romania                                  |
| European customs tariff number | 85366990                                 |
| GTIN                           | 5713140016316                            |
| ETIM                           | EC002637                                 |
| eCl@ss                         | 27460201 PCB connector (board connector) |