

## Han PP Power L metal plug var cod 9-13mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 434 0401
Specification	Han PP Power L metal plug var cod 9-13mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09354340401">https://b2b.harting.com/09354340401</a>

### Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	Power L
Element	Connector sets
Specification	AIDA compliant With variable coding
Features	Intuitive locking mechanism field assembly without tools

### Version

Termination method	Spring clamp termination
Shielding	Unshielded
Number of contacts	5
Locking type	PushPull
Details	When installing a PROFINET system, observe the PROFINET installation guideline.
Pack contents	incl. metal housing and female insert

### Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm²
Conductor cross-section	AWG 18 ... AWG 13
Rated current	16 A
Rated voltage	24 V
Rated impulse voltage	1.5 kV



**Pushing Performance**  
Since 1945

## Technical characteristics

Pollution degree	3
Stripping length	10 mm Conductors 44 mm cable jacket
Tightening torque	3 Nm
Limiting temperature	-40 ... +70 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 IP67
Clamping range	9 ... 13 mm
Vibration resistance	10-150 Hz, 5 g, 0.35 mm, 10 sweep cycles acc. to IEC 61373 Category 1 Class B
Shock resistance	30 g / 11 ms, 3 shocks / axis and direction

## Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side Sn over Ni Termination side
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Colour (hood/housing)	Silver
Material (O-ring)	NBR
Material (internal seal)	NBR
Material (cable seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

California Proposition 65 substances	Lead
	Naphthalene

## Specifications and approvals

Specifications	IEC/PAS 61076-3-126
UL / CSA	UL 1059 XCFR2.E314677 CSA-C22.2 No. 158-10 XCFR8.E314677
Approvals	DNV GL
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	116 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140223868
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)