

0.7kg Pull Button Magnet Thermocouple, PTFE Insulated with Miniature or Standard Plug - IEC





Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

General Description	Ideal for ferrous metal surface measurement			
Thermocouple Type	К			
Thermocouple Junction	Grounded at tip			
Magnet	1/2" diameter button type, 0.7kg Pull			
Cable Length	1m, 2m			
Cable Type	PTFE insulated twin-twist wires			
Cable Termination	Miniature or Standard Fitted Plug			
Max. Temperature	+250°C (plug 200°C)			
Standards Met	IEC			
Colour	Positive: Green / Negative: White			

Ordering Information

Туре	Cable Length	Pull	Termination	Manufacturers Code	Farnell Order Code
K	1m	0.7 kg Pull	Miniature Plug	BMS-K-1M-MP (0.7kg Pull)	4073492
K	2m	0.7 kg Pull	Miniature Plug	BMS-K-2M-MP (0.7kg Pull)	4155986
K	1m	0.7 kg Pull	Standard Plug	BMS-K-1M-SP (0.7kg Pull)	4155987
K	2m	0.7 kg Pull	Standard Plug	BMS-K-2M-SP (0.7kg Pull)	4155988

TC-12 Nov-23



Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC &

Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

Best Sellers 📥



ANSI PTFE
Insulated Twin
Twisted
Farnell 2443696
Newark 73AC8304

ANSI PFA Insulated
Twin Twisted
Farnell 2443711
Newark 73AC8297

O

Fabricated and Specialist Thermocouples

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.

Best Sellers



Washer Thermocouple Farnell 8597952 Newark 38K1555

Bayonet Thermocouple Farnell 2785115 Newark 37AC0993

> Magnet Thermocouple Farnell 2081298 Newark 88T2877



Exposed Junction Thermocouples

Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.

 2, 3, 5 & 10m lengths available in IEC or ANSI colours.

Best Sellers





IEC Type K Exposed
Junction
Farnell 4100748
Newark 15J1022



Thermocouple Connectors

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.



PCB Socket Farnell 2347056 Newark 06X5514



IEC Thermocouple Plug

Farnell 7086362 Newark 67C1559





RTD Detectors

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.

Best Sellers



Film Detector Farnell 8598550 Newark 38K0883

PT100 Wire Wound Detector

Farnell 2770776 Newark 25AC2608

PT100 Class A Thin Film Detector Farnell 8598525



Mineral Insulated Thermocouples

Available in various calibration types with a variety of terminations.

These include; Thermocouple plugs, Terminal heads and Thermocouple cable.





ANSI Thermocouple Farnell 2420317 Newark 53X3217

IEC Thermocouple with Mini Plug Farnell 4248338

Newark 19J1166

IEC Melt Bolt Thermocouple Farnell 2816490 Newark 44AC8638







Pt100 Heavy Duty Sensor Probe Farnell 8598096 Newark 38K0974



Pt100 Sensor in Stainless Steel Tube with Teflon Lead Farnell 2420300 Newark 53X3459

St

Pt100 Outdoor/ Cold Store Temperature Sensor Farnell 2816462 Newark 44AC8648



L60 Fine Wire Thermocouple Welder

The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.

Best Sellers







L60+ Thermocouple & Fine Wire Welder and accessories Farnell 2897470 Newark 62AC8741

To suit a wide range of applications and styles, available in class A or B.

Resistance Thermometer

Detectors (RTD) / Platinum

Resistance Thermometers (PRT)

TC-12 Nov-23