

Fabricated Grounded Thermocouple in Stainless Steel Tube, Glassfibre stainless steel Overbraided cable - JIS



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

General Description	316 stainless steel tube in various sizes		
Thermocouple Type	К		
Thermocouple Junction	Grounded at tip for fast response		
Cable Length	2m		
Cable Type	Glassfibre stainless steel overbraided cable		
Cable Termination	Bare Wire Tails		
Max. Temperature	+350°C		
Min. Temperature	-60°C		
Standards Met	JIS (Japanese Industrial Standards)		
Tube Diameter	3.18mm, 4mm, 4.76mm		
Tube Length	13mm, 25mm, 40mm, 75mm*, 100mm*		

*=4.76mm Only

Ordering Information

Туре	Cable Length	Diameter x Length	Termination	Manufacturers Code	Farnell Order Code
К	2m	3.18 x 13mm	Bare Tails	FAE-GSK-3.18-13-NP-2.0-C4-T-J	4155730
K	2m	3.18 x 25mm	Bare Tails	FAA-GSK-3.18-25-NP-2.0-C4-T-J	4155731
K	2m	3.18 x 40mm	Bare Tails	FAA-GSK-3.18-40-NP-2.0-C4-T-J	4155732
K	2m	4 x 13mm	Bare Tails	FAE-GSK-4.0-13-NP-2.0-C4-T-J	4155733
K	2m	4 x 25mm	Bare Tails	FAA-GSK-4.0-25-NP-2.0-C4-T-J	4155734
K	2m	4 x 40mm	Bare Tails	FAA-GSK-4.0-40-NP-2.0-C4-T-J	4155735
K	2m	4.76 x 13mm	Bare Tails	FAE-GSK-4.76-13-NP-2.0-C4-T-J	4155736
K	2m	4.76 x 25mm	Bare Tails	FAA-GSK-4.76-25-NP-2.0-C4-T-J	4155738
K	2m	4.76 x 40mm	Bare Tails	FAA-GSK-4.76-40-NP-2.0-C4-T-J	4155739
K	2m	4.76 x 75mm	Bare Tails	FAA-GSK-4.76-75-NP-2.0-C4-T-J	4155740
К	2m	4.76 x 100mm	Bare Tails	FAA-GSK-4.76-100-NP-2.0-C4-T-J	4155741

