
Photoelectrics Through-beam Type PH18CNT..., DC





- Miniature sensor range
- Range: 20 m
- Sensitivity adjustment by potentiometer
- Modulated, infrared light 850 nm
- Supply voltage: 10 to 30 VDC
- Output: 100 mA, NPN or PNP, N.O + N.C.
- Degree of protection IP67, IP69K
- . LED indication for output, stability and power ON
- Protection: reverse polarity, short circuit and transients
- Cable, plug and pigtail versions
- Excellent EMC performance



Product Description

The PH18CNT... is part of a family of inexpensive general purpose through-beam sensors in industrial standard 18 mm cylindrical and square ABS housing.

The sensors are useful in applications where high-accuracy detection as well as small size is required.

Compact housing and high power LED for excellent performance-size ratio.

The potentiometer used for adjustment of the sensitivity makes the sensors highly flexible. The output type is NPN or PNP and the output switching function is NO and NC.

Ordering Key PHISCN

Ordering Key	PH18CNT20PAM1SA
Type Housing style square Housing size Housing material Housing type neutral Detection principle Sensing distance Output type Output configuration Connection type Sensitive adjustment	
oononite aajaounent	

Type Selection

Housing type	Range S _n	Connection	Ordering no. Emitter	Ordering no. Receiver NPN Make or break switching	Ordering no. Receiver PNP Make or break switching
M18 Square type	20 m	Cable Plug Pigtail M12	PH 18 CNT 20	PH 18 CNT 20 NASA	PH 18 CNT 20 PASA
M18 Square type	20 m		PH 18 CNT 20M1	PH 18 CNT 20 NAM1SA	PH 18 CNT 20 PAM1SA
M18 Square type	20 m		PH 18 CNT 20T1	PH 18 CNT 20 NAT1SA	PH 18 CNT 20 PAT1SA

Specifications Receiver according to EN60947-5-2

Rated operating distance (S _n)	Up to 20 m
Blind zone	0 mm
Sensitivity control	Adjustable by potentiometer
Electrical adjustment	210°
Mecanical adjustment	240°
Adjustable distance to target	1 - 20 m
Temperature drift	≤ 0.2%/°C
Hysteresis (H)	
(differential travel)	≤ 20%
Rated operational volt. (U _B)	10 to 30 VDC
, ,	(ripple included)
Ripple (U _{rpp})	≤ 10%
Output current	
Continuous (I _e)	≤ 100 mA
Short-time (I)	≤ 100 mA
ν,	(max. load capacity 100 nF)
No load supply current (I _o)	≤ 15 mA @ 24 VDC
Minimum operational current (I _m)	0.5 mA

OFF-state current (I _r)	≤ 100 µA
Voltage drop (U _d)	≤ 2.0 VDC @ 100 mA
Protection	Short-circuit, reverse polarity and transients
Sensing angle	± 4°
Ambient light	30.000 lux Incandescent lamp
Operating frequency	500 Hz
Response time OFF-ON (t _{ON}) ON-OFF (t _{OFF})	≤ 1.0 ms ≤ 1.0 ms
Power ON delay (t _v)	≤ 200 ms
Output function Type Switching function	NPN or PNP NO and NC
Indication Output ON Signal stability and power ON	LED, yellow LED, green



Specifications Emitter according to EN60947-5-2

Rated operational volt. $(U_{\scriptscriptstyle B})$	10 to 30 VDC (ripple included)	L F
Ripple (U _{rpp})	≤ 10%	
Supply current (I _o)	≤ 25 mA @ 24 VDC	Ī
Light source	LED, 850 nm	
Light type	Infrared, modulated	٠,
Sensing angle	± 4°	١,

Light spot Diameter	Ø 1500 mm @ 10 m
Protection	Reverse polarity and transients
Indication function Power supply ON Signal stability and power ON	LED, green LED, green
Power on delay	< 200 ms

Specifications Common according to EN60947-5-2


Environment Installation category	III (IEC 60664/60664A; 60947-1)
Pollution degree	3 (IEC 60664/60664A; 60947-1)
Degree of protection	IP 67, IP 69K*
Ambient temperature	
Operating	-25° to +60°C
Storage	-40° to +70°C
Vibration	10 to 150 Hz, 1.0 mm/15 g (IEC 60068-2-6)
Shock	30 g / 11ms, 3 pos, 3 neg per axis (IEC 60068-2-6, 60068-2-32)
Rated insulation voltage	500 VAC (rms) IEC protection class III
Housing material Body Backpart Front material	ABS, grey PC-Transparent PMMA, red

Cable gland Trimmer shaft Locknuts Mounting bracket	POM, Black POM, Dark Grey PP, black PPA, black
Connection Cable Receiver Emitter Plug Pigtail	PVC, grey, 2 m 4 x 0.25 mm ² , Ø = 4.5 mm 2 x 0.25 mm ² , Ø = 4.5 mm M12, 4-pin (CON.14NFW series) PUR, grey, 30 cm 4 x 0.25 mm ² , Ø = 4.5 mm M12, 4-pin (CON.14NFW series)
Weight	With cable: 85 g With Pigtail: 40 g With plug: 25 g
CE-marking	Yes
Approvals	cULus (UL508) supply class 2

 $^{^{\}star}$ The IP69K test according to DIN 40050-9 for high-pressure, high-temperature wash-down applications. The sensor must not only be dust tight (IP6X), but also able to withstand high-pressure and steam cleaning. The sensor is exposed to high pressure water from a spray nozzle that is fed with 80°C water at 8'000–10'000 KPa (80–100bar) and a flow rate of 14–6L/min. The nozzle is held 100 –150 mm from the sensor at angles of 0°, 30°, 60° and 90° for 30s each. The test device sits on a turntable that rotates with a speed of 5 times per minute. The sensor must not suffer any damaging effects from the high pressure water in appearance and function.




Operation Diagram







Wiring Diagrams




Detection Diagram




Excess Gain



Signal Stability Indication



APH18-MB1






Mounting Systems




Dimensions





Installation Hints



Delivery Contents

- Photoelectric switch: PH 18 CNT...
- Installation instruction on plastic bag
- Screwdriver
- Mounting bracket APH18-MB1
- 1 M18 locknuts
- Packaging: Plastic bag
- Emitter and receiver is packed separately

Accessories

• Connector type CON.14NF..W series