

## PRODUCT DATASHEET

# ST PAR 16 RGBW REM 25 120 ° 2.9 W/2700 K GU10 FR

LED Retrofit RGBW lamps with remote control | Consumer LED RGBW lamps with remote control



### Areas of application

- Domestic applications
- Outdoor use in suitable outdoor luminaires only

### Product benefits

- Easy installation
- Up to 80 % less energy consumption compared with ordinary light bulbs
- Individual control
- No app or smartphone required to control the lamp
- Comfortable and intuitive infrared remote control
- Switching, dimming in 4 steps and color control with the push of a button
- Color loops for dynamic color changes

### Product features

- Lifetime: up to 25,000 h
- Allows for control of colors, saturation and dimming levels
- Wide range of controllable light colors including white
- Four dynamic effects: Flash, Strobe, Smooth, Mode



- Dimmable via remote control


## TECHNICAL DATA

### Electrical data

Nominal wattage	2.9 W
Construction wattage	2.90 W
Nominal voltage	220...240 V
Claimed equiv. conventional lamp power	25 W
Nominal current	32 mA
Type of current	AC
Inrush current	3.8 A
Operating frequency	50/60 Hz
Mains frequency	50/60 Hz
Max. lamp no. on circuit break. 10 A (B)	157
Max. lamp no. on circuit break. 16 A (B)	197
Total harmonic distortion	157 %
Power factor $\lambda$	0.40

### Photometrical data

Luminous flux	250 lm
Nominal useful luminous flux 90°	250 lm
Luminous efficacy	86 lm/W
Lumen main.fact.at end of nom.life time	0.96
Light color (designation)	Warm White
Color temperature	2700 K
Color rendering index Ra	80
Light color	827
Standard deviation of color matching	$\leq 6$ sdc <sub>m</sub>
Rated LLMF at 6,000 h	0.80
Flickering metric (Pst LM)	1.0
Stroboscope effect metric (SVM)	0.4



### Light technical data

Beam angle	120 °
Warm-up time (60 %)	0.50 s
Starting time	< 0.5 s

### Dimensions & Weight

Overall length	56.00 mm
Diameter	50.00 mm
Maximum diameter	50 mm
Product weight	26.00 g

### Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
Maximum temperature at tc test point	76.3 °C

### Lifespan

Lifespan	25000 h <sup>1)</sup>
Number of switching cycles	100000
Lumen maintenance at end of service lifetime	0.96
Rated lamp survival factor at 6,000 h	≥ 0.90

<sup>1)</sup> L70/B50

### Additional product data

Base (standard designation)	GU10
Mercury content	0.0 mg
Mercury-free	Yes
Design / version	Frosted
Product remark	All technical parameters apply to the entire lamp / Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value

### Capabilities

Dimmable	Yes <sup>1)</sup>
----------	-------------------

<sup>1)</sup> Check dimmer compatibility at [ledvance.com/compatibility](https://www.ledvance.com/compatibility)

## Certificates & Standards

Energy efficiency class	F 1)
Energy consumption	3.00 kWh/1000h
Type of protection	IP20
Standards	CE / LVD / EMC / SLR / ROHS / REACH
Photobiological safety group acc. to EN62778	RG1

1) Energy efficiency class (EEC) on a scale of A (highest efficiency) to G (lowest efficiency)

## Country-specific categorizations

Order reference	LSPR1625REM 2,9
-----------------	-----------------

## LOGISTICAL DATA

Temperature range at storage	-20...+80 °C
------------------------------	--------------

## Energy labelling regulation data acc EU 2019/2015

Lighting technology used	LED
Non-directional or directional	NDLS
Mains or non-mains	MLS
Light source cap-type (or other electric interface)	GU10
Connected light source (CLS)	No
Color-tuneable light source	Yes
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	SINGLE_VALUE
Standby power	0.50 W
Networked standby power for CLS	0.50 W
Claim of equivalent power	Yes
Length	56.00 mm
Height	50.00 mm
Width	50.00 mm
Chromaticity coordinate x	0.463
Chromaticity coordinate y	0.420
R9 Colour rendering index	0.00
Beam angle correspondence	SPHERE_360
Survival factor	0.90

Displacement factor	N/A
LED light source replaces a fluorescent light source	No
EPREL ID	1403055,523282,1338692
Model number	AC31123,AC45050,AC24783

## DOWNLOAD DATA

### Documents and certificates



Declarations Of Conformity CE

### Photometric and lighting design files



Spectral power distribution

## LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075445970	Folding box 1	61 mm x 56 mm x 119 mm	37.00 g	0.41 dm <sup>3</sup>
4058075445987	Shipping box 4	136 mm x 130 mm x 96 mm	320.00 g	1.70 dm <sup>3</sup>
4058075445994	Shipping box 32	288 mm x 276 mm x 217 mm	2110.00 g	17.25 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.