Surge Protected Extension Lead 4 Gang





Specifications

No. of Outlets : 4 Outlets
Outlet Type : UK
Current Rating : 13A
Supply Voltage : 230V AC
Cable Length : 5m

Standard: BS 1363-2

Construction

Description	Material
Socket Base and Cover	FRPP
Socket Terminals (Bus bar)	Brass
Cover Screw	Mild steel nickel plated
Shutter	Nylon (PA)
Spring	Mild Steel
Neon Lamp	Orange light
Neon Lamp Cover	Polycarbonate (PC)
Surge Component	Metal Oxide Varistor
Plug	13A BS 1363 plug
Cable	PVC, A05VV-F 3X1.25mm2

Surge Protection Data

Voltage : 220V – 240V
Operating Voltage (V AC rms) : 300V Max.
Mains Three Way Protection : LN LE NE
Peak Current (A) : 4.5kA
Max. Energy (Joules) : 3 x 125J
Max. Clamping Voltage : 775 Volts
Response Time (nS) : <50ns

Part Number Table

Description	Part Number
4 Gang Surge Protected Mains Extension Lead, Black, 5m	PELB1707

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

