


SERIES: PEME2-D | **DESCRIPTION:** DC-DC CONVERTER**FEATURES**

- 2 W isolated output
- single/dual unregulated output
- 3,000 Vdc isolation
- continuous short circuit protection
- extended temperature range (-40~105°C)
- no-load input current as low as 8mA
- UL 62368 approved
- designed to meet EN/BS EN 62368

**MODEL**


MODEL	input voltage		output voltage	output current		output power	ripple & noise ¹	efficiency ²
	typ (Vdc)	range (Vdc)	(Vdc)	min (mA)	max (mA)	max (W)	max (mVp-p)	typ (%)
PEME2-5-D3-D ³	5	4.5~5.5	±3.3	±30	±303	2	200	78
PEME2-5-D5-D ³	5	4.5~5.5	±5	±20	±200	2	200	84
PEME2-5-D9-D ³	5	4.5~5.5	±9	±11	±111	2	200	85
PEME2-5-D12-D ³	5	4.5~5.5	±12	±8	±83	2	200	85
PEME2-5-D15-D ³	5	4.5~5.5	±15	±7	±67	2	200	86
PEME2-5-D24-D ³	5	4.5~5.5	±24	±4	±42	2	200	86
PEME2-5-S3-D ³	5	4.5~5.5	3.3	40	400	2	200	78
PEME2-5-S5-D ³	5	4.5~5.5	5	40	400	2	200	84
PEME2-5-S9-D ³	5	4.5~5.5	9	22	222	2	200	85
PEME2-5-S12-D ³	5	4.5~5.5	12	17	167	2	200	85
PEME2-5-S15-D ³	5	4.5~5.5	15	13	133	2	200	86
PEME2-5-S24-D ³	5	4.5~5.5	24	8	83	2	200	86
PEME2-12-D3-D ³	12	10.8~13.2	±3.3	±30	±303	2	180	75
PEME2-12-D5-D	12	10.8~13.2	±5	±20	±200	2	180	80
PEME2-12-D12-D	12	10.8~13.2	±12	±8	±83	2	180	83
PEME2-12-D15-D	12	10.8~13.2	±15	±7	±67	2	180	83
PEME2-12-D24-D	12	10.8~13.2	±24	±4	±42	2	200	85
PEME2-12-S5-D	12	10.8~13.2	5	40	400	2	180	82
PEME2-12-S9-D	12	10.8~13.2	9	23	222	2	180	82
PEME2-12-S12-D	12	10.8~13.2	12	17	167	2	180	84
PEME2-12-S15-D	12	10.8~13.2	15	13	133	2	180	85
PEME2-12-S24-D	12	10.8~13.2	24	8	83	2	200	86
PEME2-15-D9-D ³	15	13.5~16.5	±9	±11	±111	2	180	81
PEME2-15-D12-D ³	15	13.5~16.5	±12	±8	±83	2	180	81
PEME2-15-D15-D ³	15	13.5~16.5	±15	±7	±67	2	180	81
PEME2-15-S5-D ³	15	13.5~16.5	5	40	400	2	180	79
PEME2-15-S9-D ³	15	13.5~16.5	9	23	222	2	180	82
PEME2-15-S15-D ³	15	13.5~16.5	15	13	133	2	180	79

MODEL (CONTINUED)

MODEL (CONTINUED)	input voltage		output voltage	output current		output power	ripple & noise ¹	efficiency ²
	typ (Vdc)	range (Vdc)	(Vdc)	min (mA)	max (mA)	max (W)	max (mVp-p)	typ (%)
PEME2-24-D5-D	24	21.6~26.4	±5	±20	±200	2	180	80
PEME2-24-D12-D	24	21.6~26.4	±12	±8	±83	2	180	83
PEME2-24-D15-D	24	21.6~26.4	±15	±7	±67	2	180	83
PEME2-24-D24-D	24	21.6~26.4	±24	±4	±42	2	200	84
PEME2-24-S5-D	24	21.6~26.4	5	40	400	2	180	80
PEME2-24-S9-D	24	21.6~26.4	9	23	222	2	180	80
PEME2-24-S12-D	24	21.6~26.4	12	17	167	2	180	84
PEME2-24-S15-D	24	21.6~26.4	15	13	133	2	180	86
PEME2-24-S24-D	24	21.6~26.4	24	8	83	2	200	86

- Notes:
1. Measured at nominal input, 20 MHz bandwidth oscilloscope.
 2. Measured at nominal input voltage, full load.
 3. Model is not UL certified.
 4. All specifications are measured at Ta=25°C, humidity < 75%, nominal input voltage, and rated output load unless otherwise specified.

PART NUMBER KEY



INPUT

parameter	conditions/description	min	typ	max	units
operating input voltage	5 Vdc input models	4.5	5	5.5	Vdc
	12 Vdc input models	10.8	12	13.2	Vdc
	15 Vdc input models	13.5	15	16.5	Vdc
	24 Vdc input models	21.6	24	26.4	Vdc
surge voltage	for maximum of 1 second				
	5 Vdc input models	-0.7		9	Vdc
	12 Vdc input models	-0.7		18	Vdc
	15 Vdc input models	-0.7		21	Vdc
current (full load/no load)	3.3 Vdc output models		513/8	541/--	mA
	5 Vdc input models		477/8	500/--	mA
	9, 12 Vdc output models		471/8	494/--	mA
	15, 24 Vdc output models		466/8	488/--	mA
	12 Vdc input models	all output models		208/8	219/--
reflected ripple current ⁵	15 Vdc input models		169/8	178/--	mA
	24 Vdc input models	all output models	104/8	113/--	mA
filter	filter capacitor		15		mA

Note: 5. See the Application Notes for specific operation.

OUTPUT

parameter	conditions/description	min	typ	max	units
maximum capacitive load ⁶	5, 12, 15, 24 Vdc input models	3.3, 5 Vdc output models		2,400	μF
		12, 15 Vdc output models		560	μF
		24, ±12, ±15 Vdc output models		220	μF
		±3.3, ±5 Vdc output models		1,200	μF
		±9 Vdc output models		470	μF
		±24 Vdc output models		100	μF
	5 Vdc input models	9 Vdc output models		1,000	μF
	12, 15, 24 Vdc input models	9 Vdc output models		1,200	μF
voltage accuracy	see tolerance envelope curves				
line regulation	for Vin change of ±1%				
	3.3 Vdc output models			±1.5	%
	all other models			±1.2	%
load regulation ⁷	5 Vdc input models	3.3 Vdc output models	11	20	%
		5 Vdc output models	10	15	%
		9, 12, 15 Vdc output models	8	10	%
		24 Vdc output models	6	10	%
	all other input models	3.3 Vdc output models	15	20	%
		5 Vdc output models	7	15	%
9, 12 Vdc output models		5	10	%	
	15 Vdc output models		4	10	%
	24 Vdc output models		3	10	%
switching frequency	at nominal input, full load				
	5 Vdc input		220		kHz
	all other models		260		kHz
temperature coefficient	at full load		±0.02		%/°C

Note: 6. The specified maximum capacitive load for positive and negative output is identical.

7. From 10% to full load.

PROTECTIONS

parameter	conditions/description	min	typ	max	units
short circuit protection	continuous, self recovery				

SAFETY AND COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output for 1 minute, 1 mA max	3,000			Vdc
isolation resistance	input to output at 500 Vdc	1,000			MΩ
isolation capacitance	input to output, 100 kHz / 0.1 V		20		pF
safety approvals ⁸	certified to 62368-1: UL designed to meet 62368: EN/BS EN				
conducted emissions	CISPR32/EN55032 Class B (see Fig. 4 for recommended circuit)				
radiated emissions	CISPR32/EN55032 Class B (see Fig. 4 for recommended circuit)				
ESD	IEC/EN61000-4-2 Air ±8kV, Contact ±6kV perf. Criteria B				
MTBF	as per MIL-HDBK-217F, 25°C	3,500,000			hours
RoHS	yes				


Note: 8. See the model table for reference regarding UL certification.

ENVIRONMENTAL


parameter	conditions/description	min	typ	max	units
operating temperature	see derating curves	-40		105	°C
storage temperature		-55		125	°C
storage humidity	non-condensing	5		95	%
case temperature rise	5 Vdc output model at 25°C		25		°C
vibration	10-150Hz, 5G, 0.75mm. Along X, Y and Z				

DERATING CURVES


OUTPUT REGULATION CURVE
5 Vdc input models; 3.3 Vdc output model
(nominal input)




OUTPUT REGULATION CURVE
5 Vdc input models; all other output models
(nominal input)



OUTPUT REGULATION CURVE
12, 15 & 24 Vdc input models; 3.3 Vdc output model
(nominal input)




OUTPUT REGULATION CURVE
12, 15 & 24 Vdc input models; 3.3 Vdc output model
(nominal input)




DERATING CURVES (CONTINUED)

OUTPUT REGULATION CURVE


12, 15 & 24 Vdc input models; all other Vdc output model (nominal input)



TEMPERATURE DERATING CURVE 5 Vdc input models




TEMPERATURE DERATING CURVE all other input models




EFFICIENCY CURVES

EFFICIENCY VS INPUT VOLTAGE (full load)



EFFICIENCY VS OUTPUT CURRENT (Vin = 5 Vdc)



SOLDERABILITY




parameter	conditions/description	min	typ	max	units
pin soldering resistance	1.5 mm from case for 10 seconds			300	°C

MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	20.32 x 10.16 x 8.20 [0.800 x 0.400 x 0.323 inch]				mm
case material	black flame-retardant and heat-resistant plastic (UL94V-0)				
weight			2.4		g

MECHANICAL DRAWING

units: mm [inch]
 tolerance: ±0.25[±0.010]
 pin section tolerance: ±0.10[±0.004]



PIN CONNECTIONS		
PIN	Function	
	Single	Dual
1	GND	GND
7	NC	NC
8	+Vo	+Vo
9	No Pin	0V
10	0V	-Vo
14	Vin	Vin

APPLICATION CIRCUIT

Input and/or output ripple can be further reduced, by connecting a filter capacitor from the input and/or output terminals to ground as shown in Fig. 1 & 2.

Choosing suitable filter capacitor values is very important for a smooth operation of the modules, particularly to avoid start-up problems caused by capacitor values that are too high. For recommended input and output capacitor values refer to Table 1 & 2.

Figure 1
Single Output Models




Table 1

Vin (Vdc)	Cin (μF/V)	Vo (Vdc)	Cout (μF/V)
5	4.7 μF/16 V	3.3, 5	10 μF/16 V
		9, 12, 15	2.2 μF/25 V
		24	1 μF/50 V
12	2.2 μF/25 V	5	10 μF/16 V
15	2.2 μF/25 V	15	2.2 μF/25 V
24	1 μF/50 V	9, 12	2.2 μF/25 V
-	-	24	1 μF/50 V

Figure 2
Dual Output Models




Table 2

Vin (Vdc)	Cin (μF)	Vo (Vdc)	Cout (μF)
5	4.7 μF/16 V	±3.3, ±5	4.7 μF/16 V
		±9, ±12, ±15	1 μF/25 V
		±24	0.47 μF/50 V
12	2.2 μF/25 V	±3.3	4.7 μF/16 V
15	2.2 μF/25 V	±5	4.7 μF/16 V
24	1 μF/50 V	±12, ±15	1 μF/25 V
-	-	±24	0.47 μF/50 V

EMC RECOMMENDED CIRCUIT

Figure 3
Single Output Models




Figure 4
Dual Output Models




Table 3

Recommended External Circuit Components		
5	Vin (Vdc)	5, 9, 12, 15, 24
5	CY	270 pF / 4kVdc
	C3	refer to Cout in Tables 1, 2
	C1, C2	4.7 μF / 16 V
	LDM	6.8 μH
12/15/24	Vin (Vdc)	5, 9, 12, 15, 24
12/15/24	C1/C2	4.7 μF / 50 V
	CY	270 pF/3 kVdc
	C3, C4	refer to Cout in Tables 1, 2
	LDM	6.8 μH

REVISION HISTORY

rev.	description	date
1.0	initial release	09/26/2023

The revision history provided is for informational purposes only and is believed to be accurate.



CUI INC

a bel group

Headquarters

20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.