


ANSI Type K PFA Insulated Flat Pair Thermocouple Cable / Wire



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



PFA Teflon® insulated flat pair. PFA Teflon® has a good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam & pressure.

Specifications

General Description	Resistant to oils, acids other adverse agents and fluids.			
	Good mechanical strength and flexibility.			
Cable Length	25, 50, 100m			
Cable Type	Single pair of PFA insulated conductors, laid flat with			
	PFA jacket			
Core / Strands	1/0.2mm, 1/0.3mm, 1/0.5mm,7/0.2mm			
Conductor Cross Section 7/0.2	0.219			
(mm2)				
Outer Colour	Yellow			
+ Colour	Yellow			
- Colour	Red			
Drain Wire	No			
Insulation Material	PFA Insulated			
Loop Resistance 7/0.2 (Ohms per	4.5			
combined metre)				
Max. Temperature	+260°C			
Min. Temperature	-75°C			
+ Conductor	Nickel Chromium			
- Conductor	Nickel Aluminium			
Screen	No			
Standards Met	Colour code (cores & jacket) to ANSI MC96.1			
Thermocouple Type	К			
Tolerance	Class 1			

Datasheet



Ordering Information

Туре	Colour Code	Cable Style	Strand Size	Length	Manufacturers Code	Farnell Order Code
К	ANSI	PFA FLAT PAIR	1/0.2mm	25m (82ft)	WK-609-ANSI	3582347
К	ANSI	PFA FLAT PAIR	1/0.2mm	100m (328.1ft)	WK-609-ANSI	3582348
К	ANSI	PFA FLAT PAIR	1/0.3mm	25m (82ft)	WK-356-ANSI	3582338
К	ANSI	PFA FLAT PAIR	1/0.3mm	100m (328.1ft)	WK-356-ANSI	3582339
К	ANSI	PFA FLAT PAIR	1/0.5mm	25m (82ft)	WK-306-ANSI	3582328
К	ANSI	PFA FLAT PAIR	1/0.5mm	100m (328.1ft)	WK-306-ANSI	3582329
К	ANSI	PFA FLAT PAIR	7/0.2mm	10m (32.8ft)	XS-751-ANSI	4073345
К	ANSI	PFA FLAT PAIR	7/0.2mm	25m (82ft)	XS-751-ANSI	2443715
К	ANSI	PFA FLAT PAIR	7/0.2mm	50m (164.1ft)	XS-751-ANSI	2443716
К	ANSI	PFA FLAT PAIR	7/0.2mm	100m (328.1ft)	XS-751-ANSI	2443717

