

RLS27 Rugged Strip Lights




Superior Environmental Resistance for Challenging Applications

- Shatterproof, UV-stabilized polycarbonate shell offers superior chemical resistance and protection to withstand harsh environments such as car washes
- Sturdy aluminum housing and robust endcaps provide dependable use outside in any weather
- High-intensity focused lens delivers long-range illumination for easy viewing outdoors
- IP67- and IP69K-rated for reliable operation in demanding applications with high temperatures and high pressure washdowns
- Colors, animations, and device status on Pro models can be customized using Banner's Pro Editor software to meet any user needs


BANNER[®]
more sensors, more solutions

RLS27 Rugged Strip Lights


Single and Multicolor Models



Pro Models



Specifications



Height (H)

285 mm	1130 mm
570 mm	1700 mm
850 mm	2270 mm

Supply Voltage

Single color: 12 to 30 V DC
Multicolor: 24 V DC
Pro: 18 to 30 V DC

Construction

Inner housing: clear anodized aluminum
Outer housing: UV-stabilized polycarbonate
Connector: Nickel-plated brass

Operating Conditions

-40 to +70 °C (-40 to +158 °F)

Environmental Rating

IP67, IP69K per DIN 40050-9

Certifications



Accessories



LMBHLS27S

Impact absorbing brackets, set of two (included)



LMBHLS27O

Impact absorbing clamp brackets, set of two



LMBWLS27H

Hanging clamp brackets, set of two



LMBWLS27U

Universal clamp bracket



4-Pin M12 Cordset

Straight connector models listed; for right-angle models, add RA to the end of model number (example, MQDC-406RA)

MQDC-406

2 m (6.5')

MQDC-415

5 m (15')

MQDC-430

9 m (30')



5-Pin M12 Chemical Washdown Cordset

Straight connector models listed

MQDCWD-506

2 m (6.5')

MQDCWD-530

9 m (30')



Banner Engineering Corp.

9714 10th Avenue North • Minneapolis, MN 55441 • 1-888-373-6767 • www.bannerengineering.com