



Connectors > PCB Connectors > PCB Headers & Receptacles



Connector System: **Wire-to-Board**

Number of Positions: **10**

Centerline (Pitch): **1.8 mm [.07 in]**

Sealable: **No**

PCB Mount Orientation: **Vertical**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Header Type	Fully Shrouded
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	10
PCB Mount Orientation	Vertical
Number of Rows	2

Body Features

Primary Product Color	Black
Connector & Keying Code	A

Contact Features



Contact Size	.5mm
Contact Type	Tab
Mating Tab Width	.5 mm[.019 in]
Mating Tab Thickness	.4 mm[.015 in]
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

Mechanical Attachment

Mating Alignment	With
PCB Mount Alignment	With
PCB Mount Retention	With
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	1.8 mm[.07 in]
--------------------	----------------

Dimensions

Connector Length	14.9 mm[.586 in]
Connector Width	9.4 mm[.37 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Other

Interface Number	114-94000-20
------------------	--------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2302475-1
10POS,NANOMQS,REC HSG,COD A

TE Part # 2312108-1
8POS,NANOMQS,REC HSG ASSY, COD A

Customers Also Bought

TE Part #5-963716-1
MQS, RECEPTACLE AND TAB

TE Part #1-66103-9
III+ PIN,24-20,TIN,SMPACK

TE Part #2315405-1
4POS,TAB0.5X0.4,HDR ASSY,90DEG, COD A

TE Part #2317523-1
2X4POS,NANOMQS,HDR ASSY, 180DEG,SMD,COD A



TE Part #2317527-1
2X6POS,NANOMQS,HDR ASSY,
180DEG,SMD,COD A

TE Part #2317531-1
2X8POS,NANOMQS,HDR ASSY,
180DEG,SMD,COD A

TE Part #474817-E
SRCP 1,27 6 M 1-KS SMD 137 E1 094 *
GU-H

TE Part #504285-E
MCBA 8 M * SMD 137 * 176 * GURT *
J 2 50

TE Part #4-874468-5
GROOVED BALL BEARING

Documents

Product Drawings

2X5POS,NANOMQS,HDR ASSY,180DEG,SMD,COD A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2317525-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2317525-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2317525-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English