


Nylon Metric Cable Glands

Range: Cable Glands/Grommets

Part Number: K348-1016-00



DESCRIPTION

Venting Cable Gland, Light Grey Nylon RAL7035, M16 x 1.5, with built-in Venting Element with Polytetrafluorethylene PTFE membrane.

CABLE GLANDS/GROMMETS FEATURES

- Wide sealing and clamping range
- Protection for hermetically sealed electro-technical and electronic enclosures against condensation water from alternating temperature and pressure
- Pressure, continuous ventilation and adaption of the inner pressure
- UV and weather resistance

Subject to technical modification without notice.

Typographical and other errors do not justify claim for damages.

SPECIFICATION

Product Type	Venting Cable Glands
Sealing Ring Material	Polychloroprene-Nitrile rubber CR/NBR
Body Material	Polyamide PA6 V-0
Mounting Nut Material	Polyamide PA6 V-0
Moulded Sealing Ring Material	Chloroprene rubber CR
Min Temperature Rating °C	-20 °C (dynamic) -40 °C (static, short term)
Max Temperature Rating °C	+100 °C
IP Rating	IP66, IP68 0.2 bar (30 min.)
Colour	Light Grey RAL7036
Hole Diameter (mm)	5-9.5
Internal Connecting Thread Type	Metric, as per EN 60427
Comments	The membrane has no function if it is blocked with dust and/or submerged in water.
Width Across Flat 1 (mm)	20
Width Across Flat 2 (mm)	20
Height (mm)	40
Additional Material Detail	Membrane material - Polytetrafluorethylene PTFE