

Date Revised: 01/15/2020 Date Issued: 05/22/2015

Version: 1.3

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186

According to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

SECTION 1: IDENTIFICATION

Product Identifier

Product Form: Mixture

Product Name: Gorilla Super Glue Gel Synonyms: Ethyl Cyanoacrylate Adhesive

Intended Use of the Product

Adhesive for metal, wood, ceramics, leather, paper, most plastics and more

Name, Address, and Telephone of the Responsible Party

Company

The Gorilla Glue Company 2101 E. Kemper Road Cincinnati, Ohio 45241 513-271-3300

www.gorillatough.com

Emergency Telephone Number

Emergency number : 1-800-420-7186 (Prosar)

SECTION 2: HAZARDS IDENTIFICATION

Classification of the Substance or Mixture

Classification (GHS-US)

Flam. Liq. 4 H227 Skin Irrit. 2 H315 Eye Irrit. 2A H319 STOT SE 3 H335

Full text of H-phrases: see section 16

Label Elements GHS-US Labeling

Hazard Pictograms (GHS-US)



Signal Word (GHS-US)

: Warning

Hazard Statements (GHS-US)

: H227 - Combustible liquid.

H315 - Causes skin irritation.

H319 - Causes serious eye irritation.

H335 - May cause respiratory irritation.

Precautionary Statements (GHS-US) : P210 - Keep away from extremely high or low temperatures, ignition sources, and

incompatible materials. - No smoking.

P261 - Avoid breathing vapors, mist, or spray.

P264 - Wash hands, forearms, and other exposed areas thoroughly after handling.

P271 - Use only outdoors or in a well-ventilated area.

P280 - Wear protective gloves, protective clothing, and eye protection.

P302+P352 - If on skin: Wash with plenty of water.

P304+P340 - IF INHALED: Remove person to fresh air and keep at rest in a position

comfortable for breathing.

P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses, if present and easy to do. Continue rinsing. P312 - Call a poison center or doctor if you feel unwell.

Gorilla Super Glue Gel SDS



Date Revised: 01/15/2020 **Date Issued:** 05/22/2015

Version: 1.3

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186

According to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

P332+P313 - If skin irritation occurs: Get medical advice/attention.

P337+P313 - If eye irritation persists: Get medical advice/attention.

P362 - Take off contaminated clothing and wash before reuse.

P370+P378 - In case of fire: Use appropriate media (see section 5) to extinguish.

P233 - Keep container tightly closed.

P403+P235 - Store in a well-ventilated place. Keep cool.

P405 - Store locked up.

P501 - Dispose of contents/container in accordance with local, regional, national, territorial, provincial, and international regulations.

Other Hazards

Other Hazards Not Contributing to the Classification: Rapid polymerization occurs upon contact with water or alkaline substances. As a result, heat is generated. Skin inflammation or burns may occur upon contact during this polymerization. Contains Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

Unknown Acute Toxicity (GHS-US) Not available

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

Mixture

Name	Product Identifier	% (w/w)	Classification (GHS-US)
Ethyl cyanoacrylate	(CAS No) 7085-85-0	86 - 100	Flam. Liq. 4, H227
			Skin Irrit. 2, H315
			Eye Irrit. 2A, H319
			STOT SE 3, H335

Full text of H-phrases: see section 16

SECTION 4: FIRST AID MEASURES

Description of First Aid Measures

General: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label if possible). **Inhalation:** If inhaled, remove to fresh air and keep at rest in a position comfortable for breathing. If you feel unwell, seek medical advice

Skin Contact: Remove contaminated clothing. Gently wash with plenty of soap and water followed by rinsing with water for at least 15 minutes. Call a POISON CENTER or doctor/physician if you feel unwell. Wash contaminated clothing before reuse.

Eye Contact: Rinse cautiously with water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Obtain medical attention.

Ingestion: Rinse mouth. Do not induce vomiting. Immediately call a POISON CENTER or doctor/physician.

Most Important Symptoms and Effects Both Acute and Delayed

General: Irritation to eyes, skin and respiratory tract.

Inhalation: May cause respiratory irritation.

Skin Contact: Causes skin irritation. **Eye Contact:** Causes serious eye irritation.

Ingestion: Ingestion is likely to be harmful or have adverse effects.

Chronic Symptoms: Bonds skin and eyes in seconds.

Indication of Any Immediate Medical Attention and Special Treatment Needed

If medical advice is needed, have product container or label at hand.

SECTION 5: FIRE-FIGHTING MEASURES

Extinguishing Media

Suitable Extinguishing Media: Dry chemical powder, alcohol-resistant foam, carbon dioxide (CO2).

Unsuitable Extinguishing Media: Do not use a heavy water stream. Use of heavy stream of water may spread fire.

Gorilla Super Glue Gel SDS Page 2 of 7



Date Revised: 01/15/2020 **Date Issued:** 05/22/2015

Version: 1.3

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186

According to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Special Hazards Arising From the Substance or Mixture

Fire Hazard: Not flammable.

Explosion Hazard: Product is not explosive.

Reactivity: Rapid polymerization occurs upon contact with water or alkaline substances. As a result, heat is generated. Skin inflammation or burns may occur upon contact during this polymerization. May react with strong oxidizers, increasing risk of fire or explosion.

Advice for Firefighters

Precautionary Measures Fire: Exercise caution when fighting any chemical fire.

Firefighting Instructions: Do not allow run-off from fire fighting to enter drains or water courses.

Protection During Firefighting: Do not enter fire area without proper protective equipment, including respiratory protection.

Hazardous Combustion Products: Irritating organic vapors may be formed.

Reference to Other Sections

Refer to section 9 for flammability properties.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal Precautions, Protective Equipment and Emergency Procedures

General Measures: Do not get in eyes, on skin, or on clothing. Keep away from heat, hot surfaces, sparks, open flames, and other ignition sources. No smoking.

For Non-Emergency Personnel

Protective Equipment: Use appropriate personal protection equipment (PPE).

Emergency Procedures: Evacuate unnecessary personnel.

For Emergency Personnel

Protective Equipment: Equip cleanup crew with proper protection.

Emergency Procedures: Upon arrival at the scene, a first responder is expected to recognize the presence of dangerous goods, protect oneself and the public, secure the area, and call for the assistance of trained personnel as soon as conditions permit.

Environmental Precautions

Prevent entry to sewers and public waters.

Methods and Material for Containment and Cleaning Up

For Containment: Absorb and/or contain spill with inert material, then place in suitable container. Take up in non-combustible materials.

Methods for Cleaning Up: Clean up spills immediately and dispose of waste safely. Use only non-sparking tools.

Reference to Other Sections

See heading 8, Exposure Controls and Personal Protection. Concerning disposal elimination after cleaning, see item 13.

SECTION 7: HANDLING AND STORAGE

Precautions for Safe Handling

Hygiene Measures: Handle in accordance with good industrial hygiene and safety procedures. Wash hands and other exposed areas with mild soap and water before eating, drinking, or smoking and again when leaving work.

Conditions for Safe Storage, Including Any Incompatibilities

Storage Conditions: Store in a dry, cool and well-ventilated place. Keep container closed when not in use. Store away from heat and incompatible materials. Protect from moisture.

Incompatible Materials: Strong acids, strong bases, strong oxidizers. Water.

Storage Temperature: 5 - 25 °C (41 - 77 °F)

Specific End Use(s) Adhesive for metal, wood, ceramics, leather, paper, most plastics and more.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

For substances listed in section 3 that are not listed here, there are no established Exposure limits from the manufacturer, supplier, importer, or the appropriate advisory agency including: ACGIH (TLV), NIOSH (REL), OSHA (PEL), Canadian provincial governments, or the Mexican government.

Gorilla Super Glue Gel SDS Page 3 of 7

S.T.R.O.

Safety Data Sheet - Gorilla Super Glue Gel

Date Revised: 01/15/2020 **Date Issued:** 05/22/2015

Version: 1.3

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186

According to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Ethyl cyanoacrylate (7085-85-0)			
USA ACGIH	ACGIH TWA (ppm)	0.2 ppm	
Alberta	OEL TWA (mg/m³)	1 mg/m³	
Alberta	OEL TWA (ppm)	0.2 ppm	
British Columbia	OEL TWA (ppm)	0.2 ppm	
Manitoba	OEL TWA (ppm)	0.2 ppm	
Newfoundland & Labrador	OEL TWA (ppm)	0.2 ppm	
Nova Scotia	OEL TWA (ppm)	0.2 ppm	
Ontario	OEL TWA (ppm)	0.2 ppm	
Prince Edward Island	OEL TWA (ppm)	0.2 ppm	
Saskatchewan	OEL STEL (ppm)	0.6 ppm	
Saskatchewan	OEL TWA (ppm)	0.2 ppm	

Exposure Controls

Appropriate Engineering Controls: Emergency eye wash fountains and safety showers should be available in the immediate vicinity of any potential exposure. Provide sufficient ventilation to keep vapors below permissible exposure limit. Ensure all national/local regulations are observed.

Personal Protective Equipment: Protective clothing. Safety glasses. Gloves. Insufficient ventilation: wear respiratory protection.





Relative Vapor Density at 20 °C





Materials for Protective Clothing: Chemically resistant materials and fabrics. Wear fire/flame resistant/retardant clothing.

Hand Protection: Wear chemically resistant protective gloves.

Eye Protection: Chemical goggles or safety glasses.

Skin and Body Protection: Wear suitable protective clothing.

Respiratory Protection: If exposure limits are exceeded or irritation is experienced, approved respiratory protection should be worn.

Other Information: When using, do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Information on Basic Physical and Chemical Properties

Physical State : Liquid

Appearance : White Water / Straw colored

Odor Sharp, irritating **Odor Threshold** Not available Ηα Not applicable **Evaporation Rate** : Not available **Melting Point** Not available **Freezing Point** Not available **Boiling Point** > 100 °C (212 °F) **Flash Point** > 81 °C (177.8 °F) **Auto-ignition Temperature** Not available **Decomposition Temperature** Not available Flammability (solid, gas) Not available **Lower Flammable Limit** Not available **Upper Flammable Limit** Not available < 0.5 mm Hg **Vapor Pressure**

Gorilla Super Glue Gel SDS Page 4 of

Not available



Date Revised: 01/15/2020 **Date Issued:** 05/22/2015

Version: 1.3

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186

According to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Relative Density : 1.1 (water = 1)

Specific Gravity : 1.1

Solubility : Immiscible in water.

Partition Coefficient: N-Octanol/Water: Not availableViscosity: Not available

Explosion Data – Sensitivity to Mechanical Impact : Not expected to present an explosion hazard due to mechanical impact. Explosion Data – Sensitivity to Static Discharge : Not expected to present an explosion hazard due to static discharge.

VOC Content : < 20 g/l estimated (California SCAQMD Method 316B)

SECTION 10: STABILITY AND REACTIVITY

Reactivity: Rapid polymerization occurs upon contact with water or alkaline substances. As a result, heat is generated. Skin inflammation or burns may occur upon contact during this polymerization. May react with strong oxidizers, increasing risk of fire or explosion.

Chemical Stability: Stable under recommended handling and storage conditions (see section 7).

Possibility of Hazardous Reactions: Hazardous polymerization will not occur.

Conditions to Avoid: Direct sunlight. Extremely high or low temperatures.

Incompatible Materials: Strong acids, strong bases, strong oxidizers. Water.

Hazardous Decomposition Products: Carbon Oxides (CO and CO₂) and other irritating compounds.

SECTION 11: TOXICOLOGICAL INFORMATION

Information on Toxicological Effects - Product

Acute Toxicity: Not classified LD50 and LC50 Data: Not available

Skin Corrosion/Irritation: Causes skin irritation.

pH: Not applicable

Serious Eye Damage/Irritation: Causes serious eye irritation.

pH: Not applicable

Respiratory or Skin Sensitization: Not classified

Germ Cell Mutagenicity: Not classified

Teratogenicity: Not available **Carcinogenicity:** Not classified

Specific Target Organ Toxicity (Repeated Exposure): Not classified

Reproductive Toxicity: Not classified

Specific Target Organ Toxicity (Single Exposure): May cause respiratory irritation.

Aspiration Hazard: Not classified

Symptoms/Injuries After Inhalation: May cause respiratory irritation.

Symptoms/Injuries After Skin Contact: Causes skin irritation.

Symptoms/Injuries After Eye Contact: Causes serious eye irritation.

Symptoms/Injuries After Ingestion: Ingestion is likely to be harmful or have adverse effects.

Information on Toxicological Effects - Ingredient(s)

LD50 and LC50 Data: Estimated Oral LD50: >5000 mg/kg; Estimated Dermal LD50: >2000 mg/kg;

Estimated Inhalation LC50: Vapors may be irritating.

SECTION 12: ECOLOGICAL INFORMATION

Toxicity Not classified

Persistence and Degradability Not available

Bioaccumulative Potential Not available

Mobility in Soil Not available

Gorilla Super Glue Gel SDS Page 5 of 7



Date Revised: 01/15/2020 Date Issued: 05/22/2015

Version: 1.3

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186

According to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Other Adverse Effects

Other Information: Avoid release to the environment.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Recommendations: Dispose of waste material in accordance with all local, regional, national, provincial, territorial and international regulations.

SECTION 14: TRANSPORT INFORMATION

In Accordance with DOT Not regulated for transport In Accordance with IMDG Not regulated for transport In Accordance with IATA Not regulated for transport In Accordance with TDG Not regulated for transport

SECTION 15: REGULATORY INFORMATION

US Federal Regulations

Gorilla Super Glue Gel	
SARA Section 311/312 Hazard Classes	Immediate (acute) health hazard
Ethyl cyanoacrylate (7085-85-0)	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	

US State Regulations

Gorilla Super Glue Gel

California Prop 65: To the best of our knowledge, this product does not contain any of the listed chemicals, which the State of California has found to cause cancer, birth defects or reproductive harm.

Ethyl cyanoacrylate (7085-85-0)

U.S. - New Jersey - Right to Know Hazardous Substance List

Canadian Regulations

Canadian Negarations	
Gorilla Super Glue Gel	
WHMIS Classification	Class B Division 3 - Combustible Liquid
	Class D Division 2 Subdivision B - Toxic material causing other toxic effects





Ethyl cyanoacrylate (7085-85-0)

Listed on the Canadian DSL (Domestic Substances List)

WHMIS Classification Class B Division 3 - Combustible Liquid

Class D Division 2 Subdivision B - Toxic material causing other toxic effects

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations (CPR) and the SDS contains all of the information required by CPR.

SECTION 16: OTHER INFORMATION, INCLUDING DATE OF PREPARATION OR LAST REVISION

Revision Date : 01/15/2020

Other Information : This document has been prepared in accordance with the SDS requirements of the OSHA

Hazard Communication Standard 29 CFR 1910.1200.

GHS Full Text Phrases:

Eye Irrit. 2A	Serious eye damage/eye irritation Category 2A	
Flam. Liq. 4	Flammable liquids Category 4	
Skin Irrit. 2	Skin corrosion/irritation Category 2	

Gorilla Super Glue Gel SDS

GORILLA

Safety Data Sheet - Gorilla Super Glue Gel

Date Revised: 01/15/2020 **Date Issued:** 05/22/2015

Version: 1.3

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186

According to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

STOT SE 3	Specific target organ toxicity (single exposure) Category 3
H227	Combustible liquid
H315	Causes skin irritation
H319	Causes serious eye irritation
H335	May cause respiratory irritation

Party Responsible for the Preparation of This Document

The Gorilla Glue Company +1 513-271-3300

The information presented in this Safety Data Sheet was prepared by qualified personnel and to the best of our knowledge is true and accurate. The information and recommendations are furnished for this product with the understanding that the purchaser will independently determine the suitability of the product for this purpose. This data does not constitute a warranty, expressed or implied, statutory or otherwise, nor is it representation for which The Gorilla Glue Company assumes legal responsibility. The data is submitted for the user's information and consideration only. Any use of this product must be determined by the user to be in accordance with applicable federal, state, provincial and local laws and regulations.

North America GHS US 2012 & WHMIS 2 GG

Gorilla Super Glue Gel SDS Page 7 of 7