



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED. '19

REV	DATE	APP'D
1	7/31/80	KB
2	9/28/80	AF

MOD	4
CDR	BD
BY	39

REV	DATE	APP'D	DESCRIPTION
1	7/31/80	KB	REDRAWN
2	9/28/80	AF	ADDED -2 NPR 4832

589 615



1. CONNECTOR WILL ACCEPT (24) MULTIMATE SOCKET CONTACTS.
2. MAXIMUM INSULATION NOT TO EXCEED .150 DIA.
3. FRONT AND REAR FACE OF CONNECTOR.

06-JUL-93 12:59:30 /none/s0026a/d14023/eng25061/qr 4832

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES ARE TO BE HOLD TOLERANCES ON DIMENSIONS ON DIMENSIONS ON DIMENSIONS ON DIMENSIONS ON	DATE 7/31/80	NAME AMP
DESIGNED BY CHKD BY APP'D BY MATERIAL THERMOPLASTIC, BLACK	DATE 7-28-81	NAME AMP Incorporated Harrisburg, PA 17105-3608
FINISH BLACK	DATE 7-28-81	NAME AMP Incorporated Harrisburg, PA 17105-3608
APPLICATOR SPEC	DATE 7-28-81	NAME AMP Incorporated Harrisburg, PA 17105-3608
SCALE 2:1	DATE 7-28-81	NAME AMP Incorporated Harrisburg, PA 17105-3608

SMALL PACK	206837-2
STANDARD	206837-1
PACKAGING	PART NUMBER

CUSTOMER DRAWING