
# TTT I THURLBY THANDAR INSTRUMENTS

# QL Series High Performance Precision DC PSUs (Page 1)



- Advanced "next generation" dc power supply range
- Very high precision, very low noise, excellent dynamics
- Switchable remote sense provides perfect load regulation
- Advanced user interface with numeric and rotary control
- Multiple voltage/current ranges for increased flexibility
- Multiple non-volatile memories for power supply set-ups
- Comprehensive protection including OVP and OCP trips
- Compact bench footprint; modular width for rack mounting
- Auxilliary output of 5.0V, 3.3V or 2.7V (QL355T and TP)
- Bus programmable via GPIB, RS-232 or USB (P models)
- Duplicate power and sense terminals at rear (P models)

# Unmatched Precision, Unrivalled Performance

The QL series represents the 'next generation' of laboratory power supplies offering an unparalleled level of precision and performance.

Voltage and current are controlled using 16 bit DACs enabling voltages to be set to 1mV resolution even at full output. Indeed, the accuracy is sufficient for the PSU to be used as a calibration source for some hand-held DMMs.

The QL series uses pure linear technology and offers unrivalled performance in terms of regulation, output noise and dynamics. Line and load regulation are at the limit of measurement. Output noise is less than 350µV rms. Recovery time from transient current pulses is better than 50µs.

The QL series provides full remote sense capability via dedicated sense terminals. Remote sense is essential to maintain precise regulation at the load (two 0.03 Ohm connection leads will drop 300mV at 5 Amps). When remote sense is not required, internal local sensing can be selected at the touch of a button.

#### Multiple Ranges for Greater Flexibility

The QL series provides multiple ranges for increased current capability at lower voltages. The main range offers 0 to 35 volts at up to 3 Amps. The higher current range provides up to 5 Amps for voltages up to 15V. A further low current range provides enhanced current setting and measurement resolution of 0.1mA.

The product of voltage and current can be displayed at any time by pressing the VxA button. The power is displayed to a resolution of 0.01 Watts.

# Fast, Simple and Safe to use

The user interface of the QL series has been carefully designed to provide rapid control whilst guarding against any possibility of error.

Voltage and current setting can be performed either by direct numeric entry or, for applications where the voltage or current must be gradually changed, by using the quasi-analogue Jog control.

To enable the current limit to be set before connecting the load, the limit setting is displayed when the output is off. Pressing the View Limits key at any time provides a temporary display of the limit values allowing precise adjustment to also be made with the output on.

#### Setting Memories for Added Convenience

The QL series provided storage of up to 10 power supply sets-ups in non-volatile memory. Upon mains switch-off, the set-up of the PSU is saved and is automatically restored at switch-on.

### OVP and OCP Trips with 'Alarm' Output

The QL series provides fully adjustable over-voltage and over-current trips which can be used both as a fail-safe against accidental mis-setting and as a protection against inappropriate load conditions. In addition to turning the output off, a trip condition switches the rear panel alarm signal enabling other equipment to be controlled. For complete protection of the power supply, the trip will also be operated by over-temperature or excess voltage on the sense terminals.

# Triple Output Models QL355T and QL355TP

These triple output models have two main outputs plus one auxiliary output. The casing is twice the width of a single output model (two-thirds rack).

The QL355T and TP have two identical outputs which are both independent and isolated. Illuminated keys selects which output is to be adjusted and provide unambiguous indication.

In situations where the user wishes to set similar voltages or currents on both outputs, "linked" mode is available. When linked, all adjustments are applied to both outputs simultaneously.

Linked mode can provide tracking outputs and is particularly useful when the user wishes to wire the outputs in series or parallel to obtain higher voltages or currents. A "copy" function allows all of the settings of one output to be duplicated on the other prior to linking.

For even greater flexibility, the outputs can be linked when set to different voltages or currents allowing separate settings to be loaded into the linked-mode memories for simultaneous recall.

### Auxiliary output - QL355T and QL355TP

The QL355T and TP incorporate a third output intended for powering logic and other low voltage circuitry.

This output is fully isolated from the main outputs and provides a switchable voltage of 2.7, 3.3 or 5.0 volts at a current of up to one amp. An independent output on/off switch is provided which is bus controllable on the QL355TP.

Each output has its own illuminated dc on/off key providing completely independent control. For situations where power needs to be connected or disconnected from all three outputs together, master on/off keys are also provided.

#### **Programmable via GPIB, RS-232 or USB** (QL-P models)

Models with a P suffix incorporate a full bus interface enabling remote control and readback via either GPIB (IEEE-488), RS-232 or USB. On T models, the single interface address controls all three outputs.

The GPIB interface conforms fully with IEEE-488.2 as well as IEEE-488.1. The serial interface can be used as a conventional RS-232 interface or as part of a multi-instrument ARC system (Addressable RS-232 Chain).

USB support:

The QL bus interface incorporates a USB connection in addition to RS232 and GPIB. USB represents the future for medium speed PC connectivity and enables multiple devices to be connected. A Windows device driver is supplied which creates a virtual COM port, enabling USB to be used with applications that do not directly support it.

Fully isolated outputs for maximum flexibility:

Each output is fully floating and is opto-isolated from the bus interfaces. On triple output models the two main outputs can be linked in series or parallel to produce higher voltages or higher currents as required.

Rear terminals:

P versions incorporate output power and sense terminals on the rear panel in addition to as the front panel.

Simple and consistent control:

QL series supplies use simple and consistent command structures which make programming particularly easy regardless of which interface is used. A National Instruments LabWindows\* device driver is available.

High resolution control and readback:

All power supply settings can be controlled via the bus. Voltage and current can be set to a resolution of 1mV or 0.1mA for each main output. Actual voltage and current can be read back along with the power supply status. N.B. Control of the auxiliary output on T models is limited to output on-off and monitoring of overload status.

# QL Series High Performance Precision DC PSUs (Page 2)

# Compact design for bench or rack

The QL series are highly compact with a small footprint for bench use. Fold-away feet are incorporated which can be used to angle the front panel upwards. Single output models are one-third rack width, whilst triple output models are two thirds rack width.

A flexible rack mount tray is available which will mount one, two or three singles, one triple, or one triple plus one single. On P versions, rear terminals are provided for system use.

#### **Specifications**

MAIN OUTPUT(S)

QL355, QL355P, QL355T, QL355TP

Max. Output Power: 105 watts Output Ranges:

Range 1 - 0 to 35V, 0 to 3A Range 2 - 0 to 15V, 0 to 5A

Range 3 - 0 to 35V, 0 to 500.0mA

QL564, QL564P

Max. Output Power: 112 watts

Output Ranges:

Range 1 - 0 to 56V, 0 to 2A Range 2 - 0 to 25V, 0 to 4A Range 3 - 0 to 56V, 0 to 500.0mA

Voltage Setting: By floating point numeric entry or rotary jog wheel;

resolution 1mV.

Current Setting: By floating point numeric entry or rotary jog wheel;

resolution 1mA or 0.1mA depending on range Voltage - 0.03% ±5mV. Current 0.2% ±5mA/0.5mA Setting Accuracy:

Output Mode Operation in constant voltage or constant current modes

with automatic cross-over and mode indication by LEDs. DC Output Switch: Sets output voltage and current levels to zero when Off.

Output Terminals: 4mm terminals on 19mm (0.75") spacing.

Duplicate terminals on rear tag strip (P versions only) <0.01% of maximum output for 50% load change Load Regulation:

Line Regulation: <0.01% of maximum output for 10% line voltage change

Ripple and Noise: Typically <0.35mV rms Transient Response:

<20usec to within 15mV of setting for 90% load change

TempCo <±(50ppm+0.5mV)/°C (voltage)

Remote Sense: Eliminates up to 0.5V drop per lead. Remote sense operation selected from front panel and indicated by LED.

Sense Terminals: Recessed sprung sockets for direct insertion of wires Duplicate terminals on rear tag strip (P versions only).

**OUTPUT PROTECTION** 

Output Protection: Output will withstand forward voltages of up to 20V above rated output voltage. Reverse protection by diode clamp for

currents up to 3A.

The output will be shut down if any of the four trip conditions listed below occur. In addition to the output being set to Off, Fault Condition Trip:

an isolated rear panel signal is also activated.

Settable 1V to 40V (QL355) or 62V (QL564) in 0.1V steps

Over Voltage (OVP): Settable 0.1A to 5.5A (QL355) or 4.4A (QL564) in 0.01A Over Current (OCP):

Over Temperature: Monitors internal temperature rise to protect against excess

ambient temperature or blocked ventilation slots Monitors the voltage between the remote sense terminals

Sense Error: and output terminals to protect against mis-wiring. Trip Output Signal: Isolated open-collector output signal on rear panel

**METERING** 

Display Type: Dual digital meters per output using 14mm (0.56") high

brightness LEDs. 5 digit voltmeter, 4 digit current meter. Reading rate 4 per second.

Voltage meter shows set voltage when in CV mode and measured voltage when in CI mode. Meter Function:

Current meter shows measured current when in CV mode

and set current when in CI mode.
With the dc output switch set to Off, both meters show the set values (i.e. the limits). With the output On, either the Limits Display:

voltage meter or current meter will show a measured value (depending on the CV/CI mode). Pressing the Limits button will provide a temporary display of the set

Watts (VxA) Display: The voltage meter can be made to show the instantaneous calculated product of voltage and current. The

value displayed is equal to the equivalent power at the moment when the button is pressed and remains whilst

the button is held.

Meter Resolution: Voltage: 1mV (CV mode) or 10mV (CI mode)

Current: 1mA or 0.1mA depending on range Power: 0.01W or 0.001W depending on range

Voltage: 0.05% of reading ±10 mV (CI mode)
Current: 0.2% of reading ± 0.005A or 0.5mA (CV mode) Meter Accuracy:

Power: 0.3% of reading ± 0.05W or 0.005W

#### **SETTING MEMORIES**

10 (30 total on QL355T and TP) plus power-down store. Number of Stores:

Memory Type: Non-volatile using EEPROM.

Parameters Stored: Range, Set volts, Set current, OVP, OCP. Recall system:

Settings are previewed onto the displays before being

#### LINK & COPY - QL355T & TP

Each output can be controlled independently or can be linked. When linked, keyboard and jog wheel control operates on both outputs simultaneously.

Linked mode can be used to create tracking outputs, or for convenient series or parallel operation of the two outputs.

A Copy function is available which copies all of the settings for output one to output two (Range, Set volts, Set current, OVP, OCP).

Linked mode can also be used to store the settings for both outputs to a group of common memory stores when simultaneous recall is required.

(Note: Linked mode can be selected with differing voltage and current settings on the two outputs. However both outputs must be set to the same range.)

#### **AUXILIARY OUTPUT - QL355T & TP**

Switchable as 2.7V, 3.3V or 5.0V. Accuracy ±1%. Output Voltage: Output Current: >1.0 A maximum. LED indication of over-current. DC Output Switch: Sets output voltage level to zero when Off. Output Terminals: 4mm terminals on 19mm (0.75") spacing. Duplicate terminals at rear (P versions only)

Output will withstand up to 16 V forward voltage. Diode clamped for reverse voltages and 3 Amps reverse current. Output Protection:

Load Regulation: < 0.2% for 50% load change. Line Regulation: < 0.1% for 10% line change.

#### **BUS INTERFACES (P Suffix versions)**

Supplied with device driver for Win98 or above. USB:

Operates as a virtual COM port.

RS-232: Variable baud rate 19,200 max. Single instrument or

Addressable RS232 Chain (ARC) system. GPIR-Conforming with IEEE-488.1 and IEEE-488.2 N.B. All three interfaces incorporate full control, readback and status reporting.

From front panel (GPIB/RS232/USB). Bus Type Selection:

Address Selection: From front panel (1 to 31).

RS-232 only. From front panel (600 to 19200 baud). Baud Selection:

Setting Resolution: Voltage - 1mV, Current 0.1mA (0.01mA on 500mA range). Readback Resolution: Voltage - 10mV, Current 1mA (0.1mA on 500mA range). Accuracy:

See specifications under Outputs and Metering.

Remote Command Response Time:

Interface <80 ms (command processing time).

Output Voltage: Response time varies with range and load conditions. Typical time to settle to within 1% of the total excursion on

a 35V/3A range with full load is <25ms. With no load it is <7 ms for an upward change and <600ms for downward.

**GENERAL** 

230V or 115V ± 14% (internally adjustable). Power Requirements:

Installation category 11.

Environmental: Operating Range: 5°C to 40°C, 20% to 80% RH

Storage Range: -20°C to +60°C

141 x 171 x 300 mm (single); 282 x 171 x 300 mm (triple) Size and Weight: 5 kg (single); 10 kg (triple)

Designed and manufactured to comply with IEC1010-1. Full safety sockets available to special order. Electrical Safety:

Designed and manufactured to comply with EN61326.

Benchtop Operation: Folding legs are incorporated that can be used to angle the

front panel upwards when required.

19 inch 4U mount for up to three single output units or one Rack Mount Option:

triple plus one single. Blanking plates are available for un-

used sections.

Thurlby Thandar Instruments Ltd. operates a policy of continuous development and reserves the right to alter specifications without prior notice.

Designed and built in the EEC by:



Thurlby Thandar Instruments Ltd.

Glebe Road, Huntingdon. Cambs. PE29 7DR United Kingdom Tel: +44 (0)1480 412451 Fax: +44 (0)1480 450409

e-mail: sales@tti-test.com Web: http://www.tti-test.com