

Product Datasheet


Alkaline

LR6 (PPG mix grade)



LR6

Typical Dimensions









IEC Dimensions (mm)		
Dimension	Maximum	Minimum
A	50,5	
B		49,5
C		7,0
E	0,5	
F	5,5	
G		1,0
Ø	14,5	13,5

Specifications

Name	LR6 / M / AA / AM3 / MIGNON / MN1500 / 15A / 15AC
Made in	Poland
Type	Alkaline Foil
Nominal Voltage	1,5 Volt
Electrolyte	Potassium Hydroxide
Average weight	23,5 g
Storage temperature range	+10°C ~ +25°C
Operating temperature range	-20°C ~ +45°C
Average Impedance	+/- 105 m-Ohm @ 1kHz fresh
Heavy metals	No added mercury (Hg), Cadmium (Cd) or Lead (Pb)
Compliant to	IEC 60086 non dangerous goods regulation EU directive 2006/66/EC
Recommended cut off voltage	0,8V per cell

Typical discharge values

LR6



The information contained herein is believed to be correct. However no warranty is made, either expressed or implied regarding the accuracy or the results to be obtained from the use of such information. Test results are according to IEC conditions. Capacities of batteries are depending on drain, temperature and cut-off voltage. Data are subject to change without prior notification.