

Eaton DM1-123D0EB-S20S

Catalog Number: DM1-123D0EB-S20S

Eaton PowerXL DM1 series micro drive, Single-phase, 230 V, 3 A, Internal EMC filter, Internal brake chopper, Multi segment LCD display, IP20, STO SIL2 and ethernet I/P, Modbus TCP onboard

General specifications

Product Name	Catalog Number
Eaton PowerXL DM1 micro variable frequency drive	DM1-123D0EB-S20S
	UPC
	786689350208
Product Length/Depth	Product Height
11 in	12 in
Product Width	Product Weight
9.3 in	5 lb
Certifications	
UL Listed	



Product specifications

Max overload

200 %

High overload (CT) amps

3

Motor control modes

V/Hz

Open loop vector control

Conformal coated boards

Yes

Low overload (VT) kW

0.75

Ambient operating temperature range

-10 to 50 °C CT

-10 to 40 °C VT

Communications onboard

Modbus RTU

Modbus TCP

Ethernet/IP

BACnet IP

BACnet MS/TP

Bluetooth

Motor type

Induction

Induction motor

Permanent magnet motor (SPM/IPM)

Electromagnetic compatibility filter

Yes

Fuse size - max

30

Internal choke

No

User interface

Multi-segment

Brake chopper

Internal brake chopper

Input phases

Single-phase

Resources

Specifications and datasheets

[Eaton Specification Sheet - DM1-123D0EB-S20S](#)

High overload (CT) kW

0.37

Digital inputs

4

Output phases

Three-phase

Analog inputs

1

Mounting Type

DIN rail

Panel mount

Digital outputs

0

Low overload (VT) hp

1

Low overload (VT) amps

4.8

Internal line reactor

No

High overload (CT) hp

0.5

Frame size

FR1

Output frequency range

0-400 Hz

Series

DM1

Communications optional

CANopen

PROFIBUS

SmartWireDT

Relay outputs

2

Input voltage range

200-240 Vac

Input frequency range

50-60 Hz

Enclosure rating

IP00

Drive type

General purpose



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)