

# Single Channel Bench Top Power supply **multicomp** PRO

RoHS  
Compliant



## Features

- Low noise: the cooling fan is controlled by the radiator temperature.
- High-precision voltage and current output (see parameter table), and maximum resolution 0.1mA of current reading.
- Constant Voltage/Constant Current operation
- Output ON/OFF control
- Voltage, current and power display
- Digital panel control
- 4 pairs of saving/recalling panel settings
- Coarse and fine voltage/.current control
- Software calibration
- Keyboard LOCK function
- Over-Voltage and Over-Current Protections that can set parameters
- Reverse polarity protection
- Short circuit protection
- uA and power displays
- USB & RS232 for remote control

## Specification

MODEL	MP711005
Voltage Range	0-30V
Current Range	0-5A
<b>Load Regulation</b>	
Voltage	$\leq 0.01\% + 2\text{mV}$
Current	$\leq 0.1\% + 5\text{mA}$
<b>Line Regulation</b>	
Voltage	$\leq 0.01\% + 3\text{mV}$
Current	$\leq 0.1\% + 3\text{mA}$

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp** PRO

# Single Channel Bench Top Power supply **multicomp** PRO

<b>Setup Resolution</b>	
Voltage	10mV
Current	1mA
<b>Setup Accuracy (25°C to -5°C)</b>	
Voltage	≤0.5%+20mV
Current	≤0.5%+5mA
<b>Ripple (20-20m)</b>	
Voltage	≤2mVrms
Current	≤3mVrms
<b>Temperature Coefficient</b>	
Voltage	≤150ppm
Current	≤150ppm
<b>Read Back Accuracy</b>	
Voltage	10mV
Current	1mA
<b>Read Back Temperature Coefficient</b>	
Voltage	≤150ppm
Current	≤150ppm
<b>Reaction Time</b>	
Voltage Rise	≤100mS
Voltage Drop	≤100mS
<b>(10% rated load)</b>	
Dimensions	262mm × 110mm × 160mm
Weight	4.3kg

## Part Number Table

Description	Part Number
Single Channel Bench Top Power Supply, Programmable, 0 to 30V	MP711005

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 sg.element14.com/b/multicomp-pro

**multicomp** PRO