

Part Number : 502128000 Product Description : 2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 24-30 AWG, Reel Series Number : 50212 Status : Active Product Category : Crimp Terminals Packaging Alternative : 0502128100 (Bag)



Documents & Resources

Drawings 502128000_sd.pdf

3D Models and Design Files

3D Model 502128000_stp.zip

Specifications

Application Specification 510900001-000.pdf Packaging Specification SPK-50212-001-001.pdf Product Specification 510650000-PS-000.pdf Product Specification 510651000-PS-000.pdf Product Specification PS-51089-001-001.pdf Product Specification PS-51089-005-001.pdf Product Specification PS-51090-003-001.pdf Product Specification PS-51090-004-001.pdf Product Specification PS-51090-005-001.pdf Product Specification PS-51090-009-001.pdf Product Specification PS-51090-016-001.pdf Product Specification PS-51090-017-001.pdf Product Specification PS-51090-018-001.pdf Product Specification PS-51160-001-001.pdf Product Specification PS-51160-006-001.pdf Product Specification PS-52968-006-001.pdf Product Specification PS-52968-007-001.pdf Product Specification PS-53358-001-001.pdf Product Specification PS-53717-002-001.pdf Product Specification PS-54111-001-001.pdf Product Specification PS-54111-002-001.pdf

Product Specification PS-54452-006-001.pdf Product Specification PS-55533-004-001.pdf

Tooling Specifications

Application Tooling Specification 571753720ATP-E-000.pdf Application Tooling Specification 571753720ATS-000.pdf Application Tooling Specification 571753720ATP-J-000.pdf Application Tooling Specification 571753720ATS-J-000.pdf Crimp Specification CS-50212-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	®
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	50212

Description	2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 24- 30 AWG, Reel
Application	Automotive, Signal, Wire-to-Board
Product Family	Micro-Latch Wire-to-Board Connector System
Product Name	DuraClik,Mi II,Micro-Latch,Sherlock
UPC	800753644625

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	20.400/mg
Packaging Type	Reel
Plating min - Mating	0.900µm
Plating min - Termination	0.900µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.40mm max.
Wire Size (AWG)	24, 26, 28, 30
Wire Size mm ²	N/A

Use with Part(s)

Description	Part Number
DuraClik Single Row Receptacle Housings	502351
Micro-Latch Single Row Receptacle Housings	<u>51065</u>
Mi II Single Row Crimp Housings	<u>51089</u>
Mi II Single Row Crimp Housings	51090

Application Tooling

Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	0011030043
Hand Crimp Tool for 2.00mm Pitch Terminal, 24-30 AWG	0638190500
FineAdjust Applicator for 2.00mm Pitch Wire-to-Board Crimp Terminals, 24-30 AWG Wire, Insulation OD 1.10-1.30mm	<u>0639005200</u>
FineAdjust Applicator for 2.00mm Pitch Wire-to-Board Crimp Terminal, 24-30 AWG, Insulation OD 0.90-1.10mm	<u>0639046800</u>
T2 Terminator Die	0639105200

Application Tooling

Japan

Description	Part Number
Extraction Tool	0571056000
S-1 Applicator for Wire-to-Board Receptacle Terminal, for 24-30 AWG Twisted Wire	<u>0571753720</u>

This document was generated on Dec 16, 2023