




Part Number : [530470510](#)

Product Description : 1.25mm Pitch, PicoBlade PCB Header, Single Row, Vertical, Through Hole, Tin Plating, Friction Lock, 5 Circuits, Tray, 2.30mm PC Tail Length

Series Number : 53047

Status : Active

Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[Drawing 530470510_sd.pdf](#)

3D Models and Design Files

[2D Drawing DXF 530470510.dxf](#)

[2D Drawing DXF PDF 530470510.pdf](#)

[3D Model 530470510_stp.zip](#)

[3D Model PDF 530470510.pdf](#)

Specifications

[Application Specification 510210000-AS-000.pdf](#)

[Packaging Specification SPK-53047-001-001.pdf](#)

[Product Specification 510211010-PS-000.pdf](#)

[Product Specification 510211110-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	53047
Description	1.25mm Pitch, PicoBlade PCB Header, Single Row, Vertical, Through Hole, Tin Plating, Friction Lock, 5 Circuits, Tray, 2.30mm PC Tail Length
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Family	PicoBlade Connector System
Product Name	PicoBlade
UPC	800753750524

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Physical

Breakaway	No
Circuits (Loaded)	5

Circuits (maximum)	5
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	5.20mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	111.200/mg
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PC Tail Length	2.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.80mm
Pitch - Mating Interface	1.25mm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	<u>51021</u>

PicoBlade Female-to-PicoBlade Female Off-the-Shelf (OTS) Cable Assemblies	<u>15134</u>
---	--------------

This document was generated on Sep 04, 2023