



## Kvaser D-sub 9 pin 120 Ohm termination adapter



### Kvaser D-sub 9 pin 120 Ohm termination adapter

EAN: 73-30130-00801-4

Kvaser D-sub 9 pin 120 Ohm termination adapter is a CAN adaptor with a 9-pin male D-Sub connector at one end and a 9-pin female D-Sub socket at the other. Between CAN High (pin 7) and CAN Low (pin 2) there is a built-in 120 Ohm CAN terminating resistor.

This adapter provides quick and easy termination to any Kvaser high-speed CAN product. The Kvaser CAN termination adapter is used when there is a need to terminate a CAN node without internal termination or when no CAN node is connected to the bus. The Kvaser D-sub 9 pin 120 Ohm termination adapter has a 9-pin male D-Sub plug connector and a 9-pin female D-Sub socket. A 120 ohm terminating resistor sits between pins 2 and 7. Major Features 9-pin D-Sub male, 9-pin D-Sub female built-in 120 Ohm CAN terminating resistor CE & RoHS certified Warranty 2-Year Warranty. See our General Conditions and Policies for details. Register your product at [kvaser.com/getting-started](https://www.kvaser.com/getting-started) for an additional 1-year Warranty Extension. Support Free Technical Support on all products available by contacting

Kvaser  
Aminogatan 25 A SE 431 53 Mölndal SWEDEN  
Kvaser Europe AB  
Telephone: +46 31 886344  
Email: [sales@kvaser.com](mailto:sales@kvaser.com)  
<https://www.kvaser.com/>



## Kvaser D-sub 9 pin 120 Ohm termination adapter

support@kvaser.com. Software Documentation, software and drivers can be downloaded for free at [kvaser.com/downloads](http://kvaser.com/downloads). Kvaser CANLIB SDK is a free resource that includes everything you need to develop software for the Kvaser CAN interfaces. Includes full documentation and many program samples, written in C, C++, C#, Delphi, and Visual Basic. All Kvaser CAN interface boards share a common software API. Programs written for one interface type will run without modifications on the other interface types! J2534 Application Programming Interface available. RP1210A Application Programming Interface available. Online documentation in Windows HTML-Help and Adobe Acrobat format.



## Kvaser D-sub 9 pin 120 Ohm termination adapter

TECHNICAL DATA - KVASER D-SUB 9 PIN 120 OHM TERMINATION ADAPTER	
WIDTH (MM)	N/A
CURRENT CONSUMPTION	N/A
OPERATING TEMPERATURE RANGE (C)	-30 °C to +85 °C
ON-BOARD RX BUFFER	N/A
ON-BOARD BUFFER	N/A
WEIGHT (G)	N/A
CASING MATERIAL	N/A
ON-BOARD TX BUFFER	N/A
PROMOTIONAL_TEXT	9-pin male-to-female D-Sub connector with termination.
GALVANIC ISOLATION	N/A
RUGGED	N/A
CIRCUIT BOARD	No
LENGTH (MM)	N/A
PIN COUNT	N/A
SILENT MODE	N/A
SOUND	N/A
CLOCK SYNC	N/A
PRODUCT GROUPS	Accessory
NETWORK CHANNEL(S)	
ERROR FRAME GENERATION	N/A
# OF CAN CHANNELS	0
CERTIFICATIONS	CE,RoHS
PC INTERFACE	Cable
API, FREE	N/A
STATUS	Active

Kvaser  
Aminogatan 25 A SE 431 53 Mölndal SWEDEN  
Kvaser Europe AB  
Telephone: +46 31 886344  
Email: sales@kvaser.com  
<https://www.kvaser.com/>



## Kvaser D-sub 9 pin 120 Ohm termination adapter

ERROR COUNTERS READING	N/A
MAXIMUM BITRATE (KBPS)	N/A
CAN FD	No
HEIGHT (MM)	N/A
TIMESTAMP RESOLUTION (US)	N/A
ERROR FRAME DETECTION	N/A
CONNECTOR	DSUB 9
EMBEDDED SCRIPT	No
MSGRATE TX MAX	N/A
MINIMUM BITRATE (KBPS)	N/A
API, LICENCED	None
IP CLASS	N/A
OPERATING SYSTEM	Linux,Win 7,Win 10,Win 8
MSGRATE RX MAX	N/A
DATABASE DBC SUPPORT	No

The information herein is subject to change without notice