



DIFFERENTIAL PRESSURE TRANSMITTERS ± 0.25 , ± 1 , OR $\pm 2\%$ ACCURACY



One-Touch® Digital Push-Button Calibration Technology

CALIBRATION SERVICES AVAILABLE



The Series 616KD Differential Pressure Transmitters ± 0.25 , ± 1 , or $\pm 2\%$ Accuracy with One-Touch® digital push-button calibration technology are designed for simplicity, making them the ideal choice for installers and maintenance professionals. These instruments not only alleviate cumbersome turn pots typically found in most transmitters, but eliminate entirely the need to span the instruments during calibration. With a single digital push-button, both ZERO AND SPAN are calibrated properly, nothing else is required. No additional reference pressure sources or separate calibration devices are necessary.

BENEFITS/FEATURES

- Simple calibration push-button sets back zero and span, saving time installing and over the service life
- Cost effective and compact device suitable for OEM applications where space, simplicity, and value are key
- Ranges and accuracy selection cover a wide range of applications minimizing components and determining standardizing on design
- Optional 1/8" NPT process connection allows for use with metal barbed fittings or compression fittings for use with metal tubing
- Side mounted push button zero (-A and -B models only)

APPLICATIONS

- Air handlers
- Variable air volume
- Duct pressure
- Filter monitoring

MODEL CHART					
Example	616KD	-A	-12	-AT	616KD-A-12-AT
Series	616KD				Differential pressure transmitter
Accuracy		A B			0.25% FS accuracy 1.0% FS accuracy 2.0% FS accuracy
Range			00 01 02 03 04 05 06 07 08 10 11 12 13 14 15 50 51 57 52 53 54 55 56 58		0 to 1 in w.c. 0 to 2 in w.c. 0 to 3 in w.c. 0 to 5 in w.c. 0 to 10 in w.c. 0 to 15 in w.c. 0 to 20 in w.c. 0 to 25 in w.c. 0 to 40 in w.c. 0 to 250 Pa 0 to 500 Pa 0 to 750 Pa 0 to 1250 Pa 0 to 2500 Pa 0 to 5000 Pa 0 to ± 1 in w.c. 0 to ± 2 in w.c. 0 to ± 3 in w.c. 0 to ± 5 in w.c. 0 to ± 10 in w.c. 0 to ± 250 Pa 0 to ± 500 Pa 0 to ± 750 Pa 0 to ± 1250 Pa
Options				AT FC N NIST TC V	Aluminum tag Factory calibration 1/8" female NPT NIST certification Terminal cover Voltage output 0-5, 1-5, 0-10, 2-10 VDC (field selectable)

Note: 0.25% FS accuracy is not available in the following ranges 00, 01, 10, 11, 50, 51, 54, 55.

SPECIFICATIONS

Service: Air and non-combustible, compatible gases.
Wetted Materials: Consult factory.
Accuracy: 616KD-A: $\pm 0.25\%$ FS; 616KD-B: $\pm 1\%$ FS, 616KD: $\pm 2\%$ FS.
Stability: $\pm 1\%$ FS/year.
Temperature Limits: 0 to 140°F (-17.8 to 60°C).
Compensated Temperature Range: 20 to 122°F (-6.67 to 50°C).
Pressure Limits: 2 psig (ranges 5 in w.c. or lower); 5 psig (ranges 10 to 40 in w.c.).
Thermal Effect: 616KD-A: $\pm 0.02\%$ FS/°F; 616KD-B: $\pm 0.04\%$ FS/°F; 616KD: $\pm 0.06\%$ FS/°F, includes zero and span.
Power Requirements: 4-20 mA output: 10-35 VDC (2-wire) or 12-26 VAC (4-wire); 5 V output: 10-35 VDC (3-wire) or 12-26 VAC (4-wire); 10 V output: 13-35 VDC (3-wire) or 12-26 VAC (4-wire) for 616KD A and B. 16-36 VDC (2-wire or 3-wire): 20-28 VAC (3-wire) for 616KD.
Output Signal: 4-20 mA or option with field selectable 0-10, 0-5, 2-10, 1-5 V.
Zero and Span Adjustments: Push button.
Loop Resistance: 4-20 mA output (DC): 0 to 1250 Ω max. Rmax = 50 (VpsDC -10) Ω ; 4-20 mA output (AC): 0 to 1200 Ω max. Rmax = 50 (1.4 VpsAC -12) Ω ; Voltage output: 5 k Ω minimum.
Current Consumption: 24 mA max for 616KD A and B. 21 mA max for 616KD.
Electrical Connections: Screw-type terminal block.
Process Connections: Barbed, dual size to fit 1/8" and 3/16" (3 mm and 5 mm) ID rubber or vinyl tubing.
Enclosure Rating: NEMA 1 (IP20), tested to UL 2043 for plenum applications.
Mounting Orientation: Vertical with pressure connections pointing down.
Weight: 1.8 oz (51 g).
Compliance: CE.

ACCESSORIES

Model	Description
A-360	Aluminum DIN rail 1 m
A-618	Protective terminal cap



Optional NPT connection block



Side mount zero