



Main

| | |
|---------------------------|--|
| Range | Thalassa |
| Product name | Thalassa PLA |
| Enclosure type | Multi-purpose |
| Product or Component Type | Suitable enclosure |
| Version | PLA |
| Nominal height | 39.37 in (1000 mm) |
| Nominal width | 29.53 in (750 mm) |
| Nominal depth | 12.60 in (320 mm) |
| Enclosure mounting | Floor-standing |
| Device composition | 1 top part 1 bottom part 2 side part 1 rear panel 1 door |

Complementary

| | |
|-----------------------------|---|
| Body type | Sealed top and bottom part assembled with side parts |
| Door type | Solid front |
| Number of doors | 1 |
| Door opening side | Reversible 120 °) |
| Lock type | 4 points lock, 5 mm double-bar |
| Accessibility for operation | Rear Front |
| Removable parts | Door by hinges Rear panel by fixing element |
| Material | Polyester reinforced with fibreglass |
| Color | Gray RAL 7035) |
| Standards | UL 508 A IEC 62208 |
| NEMA Degree of Protection | NEMA 5 NEMA 1 NEMA 2 NEMA 3X NEMA 3 NEMA 3R NEMA 12 NEMA 3S NEMA 13 |
| Product Certifications | Veritas UL/CUL listed DNV Marine |
| Electrical Insulation Class | Class II |

Environment

| | |
|-------------------------------------|-----------------------------------|
| IP degree of protection | IP65 IEC 60529 completely sealed) |
| IK degree of protection | IK10 IEC 62262 plain door) |
| Fire resistance | 1760 °F (960 °C) IEC 62208 |
| Ambient Air Temperature for Storage | -31...194 °F (-35...90 °C) |

Ordering and shipping details

| | |
|-------------------|--|
| Category | 80034-ENCLOSURE SYSTEMS WALL MOUNT METAL |
| Discount Schedule | ES1 |
| GTIN | 3606480774478 |
| Returnability | No |
| Country of origin | ES |

Packing Units

| | |
|------------------------------|--------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 13.78 in (35.0 cm) |
| Package 1 Width | 30.31 in (77.0 cm) |
| Package 1 Length | 40.16 in (102.0 cm) |
| Package 1 Weight | 39.56 lb(US) (17.944 kg) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |