



Main

Range	Spacial
Accessory / separate part category	Enclosure accessory
Product or Component Type	Door
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting Location	Step slide Front side
Range compatibility	Spacial (Spacial CRN) Spacial (Spacial S3D) Spacial (Spacial S3X)
Device composition	1 door 4 fixing brackets 2 mounting uprights

Complementary

Material	Door sheet steel
Color	All faces Gray RAL 7035)
Surface Finish	Polyester powder
Lock type	Lock 3 mm double bar
Number of locks	1
Adjustment	Pitch 25 mm (on step slides)
Door type	Internal plain
Door opening side	Reversible
Maximum load	30 kg/m²
Height	Nominal 19.69 in (500 mm)
Width	Nominal 15.75 in (400 mm)
Product Weight	6.17 lb(US) (2.8 kg)






Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480168567
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	14.17 in (36.000 cm)
Package 1 Length	18.50 in (47.000 cm)
Package 1 Weight	5.65 lb(US) (2.561 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------