

# MCMFOW4 Series

## Precision Metal Film Fixed Resistors



### Scope:


This specification for approval relates to metal film fixed resistors.

### Ratings:

Type	MF
Rated Power	0.25W at 70°C
Maximum Working Voltage	250V
Maximum Overload Voltage	500V
Dielectric Withstanding Voltage	500V
Rated Ambient Temperature	70°C
Operating Temperature Range	- 55°C to + 155°C
Resistance Tolerance	±0.5%
Resistance Range	10Ω to 1MΩ

### Power Rating:

Resistors shall have a power rating based on continuous full load operation at an ambient temperature of 70°C. For temperature in excess of 70°C, the load shall be derated.



# MCMFOW4 Series

## Precision Metal Film Fixed Resistors



### Voltage rating:

Resistors shall have a rated direct-current (DC) continuous working voltage or an approximate sine-wave root-mean-square (RMS) alternating-current (AC) continuous working voltage at commercial line frequency and waveform corresponding to the power rating, as determined from the following formula :

$$RCWV = \sqrt{P \times R}$$

Where : RCWV = Rated DC or RMS AC continuous working voltage at commercial-line frequency and waveform (volt).

P = Power rating (watt)


R = Nominal resistance (ohm)

In no case shall the rated DC or RMS AC continuous working voltage be greater than the applicable maximum value.

### Nominal resistance :

Effective figures of nominal resistance shall be in accordance with E-96 series, and resistance tolerance.

### Construction:



No.	Name	Material
1	Basic Body	Rod type ceramics
2	Resistance Film	Metal film
3	End Cap	Steel (tin plated iron surface)
4	Lead Wire	Annealed copper wire coated with tin
5	Joint	By welding
6	Coating	Epoxy insulated resin (colour : sky blue)
7	Color Code	Epoxy resin

# MCMFOW4 Series

## Precision Metal Film Fixed Resistors



Characteristics	Limits	Test Methods (JIS C 5201-1)
DC resistance	Must be within the specified tolerance.	The limit of error of measuring apparatus shall not exceed allowable range or 0.5% of resistance tolerance.
Temperature coefficient	Within the temperature coefficient specified below : $\pm 50\text{PPM}/^{\circ}\text{C}$ maximum.	Natural resistance change per temperature degree centigrade $R2-R1/ R1 (t2-t1) \times 10^6$ (PPM/ $^{\circ}\text{C}$ ). R1 : Resistance value at room temperature (t1). R2 : Resistance value at room temperature plus 100 $^{\circ}\text{C}$ (t2).
Short time overload	Resistance change rate is $\pm(0.5\% + 0.05\Omega)$ maximum with no evidence of mechanical damage.	Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds.
Dielectric withstanding voltage	No evidence of flashover mechanical damage, arcing or insulation break down.	Resistors shall be clamped in the trough of a 90 $^{\circ}$ metallic V-block and shall be tested at AC potential respectively.
Pulse overload	Resistance change rate is $\pm(1\% + 0.05\Omega)$ maximum with no evidence of mechanical damage.	Resistance change after 10,000 cycles 1 second "on", 25 seconds "off" at 4 times RCWV.
Terminal strength	No evidence of mechanical damage.	<b>Direct load</b> : Resistance to a 2.5kgs direct load for 10 seconds in the direction of the longitudinal axis of the terminal leads. <b>Twist test</b> : Terminal leads shall be bent through 90 $^{\circ}$ at point of about 6mm from the body of the resistor and shall be rotated through 360 $^{\circ}$ about the original axis of the bent terminal in alternating direction for a total of 3 rotations.
Resistance to soldering heat	Resistance change rate is $\pm(1\% + 0.05\Omega)$ maximum with no evidence of mechanical damage.	Permanent resistance change when leads immersed to 3.2 to 4.8 mm from the body in 350 $^{\circ}\text{C} \pm 10^{\circ}\text{C}$ solder for 3 $\pm 0.5$ seconds.
Solderability	95% coverage minimum	The area covered with a new, smooth, clean, shiny and continuous surface free from concentrated pinholes. Test temperature of solder : 245 $^{\circ}\text{C} \pm 3^{\circ}\text{C}$ . Dwell time in solder : 2 to 3 seconds.
Resistance to solvent	No deterioration of protective coatings and markings.	Specimens shall be immersed in bath of trichroethane completely for 3 minutes with ultrasonic.


# MCMFOW4 Series

## Precision Metal Film Fixed Resistors



Characteristics	Limits	Test Methods (JIS C 5201-1)															
Temperature cycling	Resistance change rate is $\pm(1\% + 0.05\Omega)$ maximum with no evidence of mechanical damage.	Resistance change after continuous 5 cycles for duty shown below:															
		<table border="1"> <thead> <tr> <th>Step</th> <th>Temperature</th> <th>Time</th> </tr> </thead> <tbody> <tr> <td>1</td> <td><math>-55^{\circ}\text{C} \pm 3^{\circ}\text{C}</math></td> <td>30 minutes</td> </tr> <tr> <td>2</td> <td>Room temperature</td> <td>10 to 15 minutes</td> </tr> <tr> <td>3</td> <td><math>+155^{\circ}\text{C} \pm 2^{\circ}\text{C}</math></td> <td>30 minutes</td> </tr> <tr> <td>4</td> <td>Room temperature</td> <td>10 to 15 minutes</td> </tr> </tbody> </table>	Step	Temperature	Time	1	$-55^{\circ}\text{C} \pm 3^{\circ}\text{C}$	30 minutes	2	Room temperature	10 to 15 minutes	3	$+155^{\circ}\text{C} \pm 2^{\circ}\text{C}$	30 minutes	4	Room temperature	10 to 15 minutes
		Step	Temperature	Time													
		1	$-55^{\circ}\text{C} \pm 3^{\circ}\text{C}$	30 minutes													
		2	Room temperature	10 to 15 minutes													
3	$+155^{\circ}\text{C} \pm 2^{\circ}\text{C}$	30 minutes															
4	Room temperature	10 to 15 minutes															
Load life in humidity	<table border="1"> <thead> <tr> <th>Resistance Value</th> <th><math>\Delta R/R</math></th> </tr> </thead> <tbody> <tr> <td>Normal type</td> <td><math>\pm 1.5\%</math></td> </tr> </tbody> </table>	Resistance Value	$\Delta R/R$	Normal type	$\pm 1.5\%$	Resistance change after 1000 hours (1.5 hours "on", 0.5 hour "off") at RCWV in a humidity test chamber controlled at $40^{\circ}\text{C} \pm 2^{\circ}\text{C}$ and 90 to 95% relative humidity.											
	Resistance Value	$\Delta R/R$															
Normal type	$\pm 1.5\%$																
Load life	<table border="1"> <thead> <tr> <th>Resistance Value</th> <th><math>\Delta R/R</math></th> </tr> </thead> <tbody> <tr> <td>Normal type</td> <td><math>\pm 1.5\%</math></td> </tr> </tbody> </table>	Resistance Value	$\Delta R/R$	Normal type	$\pm 1.5\%$	Permanent resistance change after 1000 hours operating at RCWV with duty cycle of (1.5 hours "on", 0.5 hour "off") at $70^{\circ}\text{C} \pm 2^{\circ}\text{C}$ ambient.											
	Resistance Value	$\Delta R/R$															
Normal type	$\pm 1.5\%$																

### Dimensions:




Dimensions : Millimetres

Type	Power Rating	D (Maximum)	L (Maximum)	d $\pm 0.05$	H $\pm 3$
MF	1/4 W	2.5	6.8	0.54	28

Dimensions : Millimetres

### Painting method:


Welding point, terminal and lead wire, is permissible to be exposed without the outer coated cover. The extent should be within 1/2 of the arc angle.



### Marking :

#### Resistor :

Resistors shall be marked with color coding colors shall be in accordance with JIS C 0802.



# MCMFOW4 Series

## Precision Metal Film Fixed Resistors



### Resistance Preferred Value Range

E6	E12	E24	E96	E6	E12	E24	E96	E6	E12	E24	E96
10	10	10	10.0				21.5				46.4
			10.2	22	22	22	22.1	47	47	47	47.5
			10.5				22.6				48.7
			10.7				23.2				49.9
		11	11.0				23.7			51	51.1
			11.3			24	24.3				52.3
			11.5				24.9				53.6
			11.8				25.5				54.9
	12	12	12.1				26.1		56	56	56.2
			12.4				27.7				57.6
			12.7		27	27	27.4				59.0
		13	13.0				28.0				60.4
			13.3				28.7			62	61.9
			13.7				29.4				63.4
			14.0			30	30.1				64.9
			14.3				30.9				66.5
			14.7				31.6	68	68	68	68.1
			15.0				32.4				69.8
15	15	15	15.4	33	33	33	33.2				71.5
			15.8				34.0				73.2
		16	16.2				34.8			75	75.0
			16.5				35.7				76.8
			16.9			36	36.5				78.7
			17.4				37.4				80.6
			17.8				38.3		82	82	82.5
	18	18	18.2		39	39	39.2				84.5
			18.7				40.2				86.6
			19.1				41.2				88.7
			19.6				42.2			91	90.9
		20	20.0			43	43.2				93.1
			20.5				44.2				95.3
			21.0				45.3				97.6

Above values in accordance with IEC Publication 63 (1963) and BS2488



# MCMFOW4 Series


## Precision Metal Film Fixed Resistors



### Part Number Table

Description	Part Number
Resistor, 100K , 0.25W 0.5% 50PPM	MCMFOW4DF1003A50

### Part Number Explanation:



- Product Type** : MF = Metal Film Fixed Resistor.  
**Special Feature** : 0 = Standard Product.  
**Wattage** : W4 = 1/4W.  
**Tolerance** : D =  $\pm 0.5\%$ .  
**PPM Requirement** : F =  $\pm 50\text{PPM}$ .  
**Ohmic Value** : Where R = Ohms =  $\Omega$ .  
K = Kiloohms =  $\text{K}\Omega$ .  
M = Megaohms =  $\text{M}\Omega$ .  
And replaces the decimal point.  
eg: 1R5 =  $1.5\Omega$ .  
4K7 =  $4.7\text{K}\Omega$ .  
6M8 =  $6.8\text{M}\Omega$ .
- Parking Type** : A = Tape/Box.  
**Packing Quantity** : 5 = 5000pcs.  
**Addition Information** : 0 = PT-52mm.

### Stocked Values

Tolerance	Wattage (W)	Preferred Value Range	Range Value
5%	0.25	E24	10R - 1M



# MCMFOW4 Series

## Precision Metal Film Fixed Resistors



### Notes:

### International Sales Offices:



**AUSTRALIA - Farnell**  
Tel No: ++61 1300 361 005  
Fax No: ++61 1300 361 225



**FINLAND - Farnell**  
Tel No: ++358 9 560 7780  
Fax No: ++358 9 345 5411



**ITALY - Farnell**  
Tel No: ++39 02 93 995 200  
Fax No: ++39 02 93 995 300



**SPAIN - Farnell**  
Tel No: 901 20 20 80  
Fax No: 901 20 20 90



**AUSTRIA - Farnell**  
Tel No: ++43 662 2180 680  
Fax No: ++43 662 2180 670



**FRANCE - Farnell**  
Tel No: ++33 474 68 99 99  
Fax No: ++33 474 68 99 90



**MALAYSIA - Farnell-Newark**  
Tel No: ++60 3 7873 8000  
Fax No: ++60 3 7873 7000



**SWEDEN - Farnell**  
Tel No: ++46 8 730 50 00  
Fax No: ++46 8 83 52 62



**BELGIUM - Farnell**  
Tel No: ++32 3 475 2810  
Fax No: ++32 3 227 3648



**GERMANY - Farnell**  
Tel No: ++49 89 61 39 39 39  
Fax No: ++49 89 613 59 01



**NETHERLANDS - Farnell**  
Tel No: ++31 30 241 7373  
Fax No: ++31 30 241 7333



**SWITZERLAND - Farnell**  
Tel No: ++44 204 64 64  
Fax No: ++44 204 64 54



**BRAZIL - Farnell-Newark**  
Tel No: ++55 11 4066 9400  
Fax No: ++55 11 4066 9410



**HONG KONG - Farnell-Newark**  
Tel No: ++852 2268 9888  
Fax No: ++852 2268 9899



**NEW ZEALAND - Farnell**  
Tel No: 0800 90 80 80  
Fax No: 0800 90 80 81



**UK - Farnell**  
Tel No: ++44 8701 200 200  
Fax No: ++44 8701 200 201



**CHINA - Farnell-Newark**  
Tel No: ++86 10 6238 5152  
Fax No: ++86 10 6238 5022



**HUNGARY - Farnell**  
Tel No: ++44 870 1200 208  
Fax No: ++44 870 1200 209



**NORWAY - Farnell**  
Tel No: 800 146 70  
Fax No: 800 146 76



**UK - CPC**  
++44 8701 202 530  
++44 8701 202 531



**CZECH REPUBLIC - Farnell**  
Tel No: ++44 870 1200 208  
Fax No: ++44 870 1200 209



**INDIA - Farnell**  
Tel No: ++44 870 1200 208  
Fax No: ++44 870 1200 209



**PORTUGAL - Farnell**  
Tel No: ++34 93 475 8804  
Fax No: ++34 93 474 5288



**USA - Newark**  
Tel No: 800 463 9275



**DENMARK - Farnell**  
Tel No: ++45 44 53 66 44  
Fax No: ++45 44 53 66 06



**IRELAND - Farnell**  
Tel No: ++353 1 830 9277  
Fax No: ++353 1 830 9016



**RUSSIA - Farnell**  
Tel No: ++44 870 1200 208  
Fax No: ++44 870 1200 209



**EXPORT - Farnell**  
Tel No: ++44 8701 200 208  
Fax No: ++44 8701 200 209

For enquiries from all other markets



**ESTONIA - Farnell**  
Tel No: ++358 9 560 7780  
Fax No: ++358 9 345 5411



**ISRAEL - Farnell**  
Tel No: ++180 937 0015  
Fax No: ++180 937 0014



**SINGAPORE - Farnell-Newark**  
Tel No: ++65 6788 0200  
Fax No: ++65 6788 0300

<http://www.farnell.com>  
<http://www.newark.com>  
<http://www.cpc.co.uk>

**Disclaimer** This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.

