




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts > Contact Tab: Component-to-Wire



Contact Type: **Receptacle**

Connector System: **Component-to-Wire**

Wire Size: **26.67 mm²**

Contact Mating Area Plating Material: **Silver**

[All Contact Tab: Component-to-Wire \(2\)](#)

Features

Product Type Features

Connector System	Component-to-Wire
Connector & Contact Terminates To	Wire & Cable

Contact Features

Contact Type	Receptacle
Contact Mating Area Plating Material	Silver
Contact Current Rating (Max)	100 A

Dimensions

Wire Size	26.67 mm ²
-----------	-----------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features



Packaging Method	Reel & Box
------------------	------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2351981-2 DYNAMIC D8000 REC HSG 2P	 TE Part # 2376202-1 Auxiliary Tool for D8000 REC CONTACT
---	---

Also in the Series | Dynamic 8000 Series



PCB Headers & Receptacles(1)




Wire-to-Board Connector Assemblies & Housings(2)



Wire-to-Board Connector Contacts(2)

Customers Also Bought




TE Part #1743164-2
3POS MQS REC




TE Part #1-1630186-3
HSA50 R50 5%



TE Part #1-2351981-2
Housing Receptacle: Wire-to-Board



TE Part #5-103960-5
4X6 MTE RCPT SR LATCH .100CL




TE Part #5532600-2
CONN SEC II 25 POS 100 C/L RA



TE Part #1982295-1
ELCON MINI 2P RA HEADER, W /CODING



TE Part #52263-5
TERMINAL R PG 8 10



TE Part #2317659-9
AV25 DPM 3A MOVING RING POWER R&G 12V FL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2373747-5_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2373747-5_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2373747-5_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English



Product Environmental Compliance

Product Compliance

English

Product Compliance

English