#### AK7

Request Samples 🕥

Check Inventory

7.0 x 5.0 x 1.8 mm RoHS/RoHS II Compliant MSL Level = 1

#### Features

- 3rd overtone solution
- Ultra-Low jitter: 75 fs typ RMS (100fs MAX, F= 156.25MHz LVPECL); spurs included
- Frequency range: 100MHz to 220MHz
- Lowest in-class power consumption (16mA Typ LVDS)
- ± 20ppm & ± 25ppm stability (-40 to +85°C) options available (dependent on frequency)
- 3.3V, 2.5V, 1.8V Vdd supply
- LVPECL, LVDS, & HCSL differential output options
- Output enable standard

#### **Key Electrical Specifications**

#### Applications

- Networking & communications
- Gigabit Ethernet
- Fibre Channel
- SONET/SDH
- RF systems, base stations (BTS)
- Datacenter
- PCI Express
- Test & measurement

Parameters		Min.	Typ.	Max.	Unit	Notes
Frequency Range		100		220	MHz	
Standard Available Frequencies		100 122.88 125 148.5 156.25 200 212.5		MHz	Contact Abracon for availability of frequencies not listed	
		2.97	3.3	3.63		Option "A"
Supply Voltage (Vdd) [Note 1]		2.37	2.5	2.62	V	Option "B"
		1.71	1.8	1.89		Option "C"
	LVPECL		30	50		@ 220MHz; @ Vdd=3.3V
Supply Current (Idd)	LVDS		16	27	mA	@ 220MHz; @ Vdd=3.3V
	HCSL		17	30		@ 220MHz; @ Vdd=3.3V
Operating Temperature Range		-20		+70	°C	Option "D"
Operating Temperature Kange	2	-40		+85	C	Option "F" or "Q"
Storage Temperature		-55		+150	°C	
Frequency Accuracy (Initial Set-Tolerance) [Note 3] at time of shipment (Pre-Reflow) @ +25°C		-10	<±5	+10	ppm	Relative to carrier frequency
		-15		+15		Option "D" (-20°C to +70°C)
Frequency Stability over <sup>[Note 2</sup> Operating Temperature Range		-20		+20	ppm	Option "Q" (-40°C to +85°C)
Operating Temperature Range		-25		+25		Option "F" (-40°C to +85°C)
Aging over 20 Year Product Life [Note 4]		-15		+15	ppm	
All-Inclusive Frequency Accuracy (Total Stability) over 20 Year Product Life [Notes 4, 5]		-40		+40		Option "D" (-20°C to +70°C)
		-45		+45	ppm	Option "Q" (-40°C to +85°C)
		-50		+50		Option "F" (-40°C to +85°C)



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 

AK7

Request Samples 🕥

Check Inventory

7.0 x 5.0 x 1.8 mm RoHS/RoHS II Compliant MSL Level = 1

Parameters		Min.	Тур.	Max.	Unit	Notes
Rise (Tr) / Fall (Tf) Time 20% to 80% V <sub>peak to peak</sub>	LVPECL		0.2	0.4	ns	@ Vdd=3.3V, $R_L$ =50 $\Omega$
			0.3	0.6		(a) Vdd=2.5V, $R_L$ =50 $\Omega$
	LVDS		0.15	0.4		(a) Vdd=3.3V, $R_L$ =100 $\Omega$
			0.15	0.4		(a) Vdd=2.5V, $R_L$ =100 $\Omega$
			0.3	0.5		(a) Vdd=1.8V, $R_L$ =100 $\Omega$
	HCSL		0.3	0.5		(a) Vdd=3.3V, $R_L$ =50 $\Omega$ to GND
			0.3	0.5		(a) Vdd=2.5V, $R_L$ =50 $\Omega$ to GND
			0.3	0.6		@ Vdd=1.8V, $R_L$ =50 $\Omega$ to GND
Duty Cycle		45		55	%	
Start-up Time [Note 2]			< 2	5.0	ms	

Note 1: Supply voltage (Vdd) = 1.8V option not available with LVPECL output

Note 2: Relative to initial measured frequency @ +25°C

Note 3: Option Q only available in select frequencies. Please contact Abracon for availability

Note 4: Relative to post-reflow frequency

Note 5: Includes temperature stability, initial frequency accuracy, load pulling, power supply variation, and 20-year aging



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 

AK7

Request Samples 🕥

Check Inventory

7.0 x 5.0 x 1.8 mm RoHS/RoHS II Compliant MSL Level = 1

Parameters			Min.	Тур.	Max.	Unit	Notes
	LVPECL	V <sub>OH</sub>	V <sub>dd</sub> -1.03		V <sub>dd</sub> -0.88		$R_L=50\Omega$ to $V_{dd}=2.0V$
Differential	LVFECL	V <sub>OL</sub>	V <sub>dd</sub> -1.85		V <sub>dd</sub> -1.60		$K_{L} = 30$ S2 to V dd = 2.0 V
Differential Output High Voltage (V <sub>OH</sub> )	LVDS	V <sub>OH</sub>		1.40	1.60	V	$R_L=100\Omega$ between
Output Low Voltage ( $V_{OL}$ )	LVDS	V <sub>OL</sub>	0.90	1.10			both outputs
Output Low Voltage (VOL)	HCSL	V <sub>OH</sub>	0.40	0.74	0.85		$R_L=50\Omega$ to ground
	ICSL	V <sub>OL</sub>	-0.15	0.00	0.15		on each output
	·		0.595	0.750	0.930		LVPECL
Output Voltage Swing			0.250	0.350	0.450	V	LVDS
			0.620	0.700	0.780		HCSL
Output Enable & Disable Con	trol		0.7*(V <sub>dd</sub> )			v	Output Enable or No Connect
Output Enable & Disable Con	101				0.3*(V <sub>dd</sub> )	v	Output Disable (High Impedance)
Output Enable Time				< 1	5.0	ms	
Output Disable Time					0.2	μs	
Output Disable Current Consumption					< 10	μΑ	$OE \le 0.3V$
	@ 200 MHz	LVPECL		70	95	fsec	@ Vdd=3.3V
RMS Phase Jitter [Note 6, 7, 8]				80	105		@ Vdd=2.5V
@ +25°C		LVDS		125	150		@ Vdd=3.3V
				150	175		@ Vdd=2.5V
(12kHz- 20MHz BW)		HCSL		120	145		@ Vdd=3.3V
				135	160		@ Vdd=2.5V
		LVPECL		75	100	fsec	@ Vdd=3.3V
	@ 156.25 MHz			80	105		@ Vdd=2.5V
		LVDS		90	115		@ Vdd=3.3V
				80	105		@ Vdd=2.5V
		HCSL		110	135		@ Vdd=3.3V
				115	140		@ Vdd=2.5V
		LVDECI		115	140		@ Vdd=3.3V
		LVPECL		95	120	fsec	@ Vdd=2.5V
		LUDC		125	150		@ Vdd=3.3V
	@ 148.5 MHz	LVDS		120	145		@ Vdd=2.5V
		HCSL		130	155		@ Vdd=3.3V
				135	160		@ Vdd=2.5V
				115	140		@ Vdd=1.8V

Note 6: Guaranteed by characterization; RMS Phase Jitter specifications are inclusive of any spurs

Note 7: Phase jitter measured with Keysight E5052B Signal Source Analyzer

Note 8: Refer to the next section for phase noise test setup and representative phase noise plots



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 

AK7

Request Samples 🕥

Check Inventory

7.0 x 5.0 x 1.8 mm RoHS/RoHS II Compliant MSL Level = 1

Parameters				Тур.	Max.	Unit	Notes			
		LVPECL		100	125		@ Vdd=3.3V			
RMS Phase Jitter [Note 6, 7, 8]		LVFECL		100	125	fsec	@ Vdd=2.5V			
@ +25°C		LVDS		150	175		@ Vdd=3.3V			
	@ 125 MHz			110	135		@ Vdd=2.5V			
(12kHz- 20MHz BW)				140	165		@ Vdd=1.8V			
				135	160		@ Vdd=3.3V			
		HCSL		140	165	1	@ Vdd=2.5V			
				135	160		@ Vdd=1.8V			
	@ 122.99 MIL-	LVPECL		150	175		@ Vdd=3.3V			
				155	180		@ Vdd=2.5V			
							130	155		@ Vdd=3.3V
		LVDS		115	140	fsec	@ Vdd=2.5V			
	@ 122.00 WIIIZ			165	190		@ Vdd=1.8V			
				135	160		@ Vdd=3.3V			
		HCSL		140	165		@ Vdd=2.5V			
				125	150		@ Vdd=1.8V			
		LVDS		155	180		@ Vdd=2.5V			
	@ 100 MHz			145	170		@ Vdd=3.3V			
				HCSL	HCSL		120	145		@ Vdd=2.5V
				155	180		@ Vdd=1.8V			

### Phase Noise Test Setup

- Keysight E5052B Signal Source Analyzer
- Integration Bandwidth = 12kHz to 20MHz
- Spurious Activity (entire plot trace) = Not omitted (Normalized in dBc/Hz)
- Specifed Spur Omission Function = Not enabled
- IF Gain = 20dB
- Correlation = 5
- Average = 3

Note 6: Guaranteed by characterization; RMS phase jitter specifications are inclusive of any spurs Note 7: RMS phase jitter measured with Keysight E5052B Signal Source Analyzer Note 8: Refer to next section for phase noise test setup and representative phase noise plots



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 

AK7


Request Samples 🕥

Check Inventory

7.0 x 5.0 x 1.8 mm RoHS/RoHS II Compliant MSL Level = 1


Representative Phase Noise Plots @ +25°C [Note 9]

F=156.2500MHz | V<sub>dd</sub>=3.3V | LVPECL RMS Phase Jitter = 69 fsec F=156.2500MHz | V<sub>dd</sub>=2.5V | LVPECL RMS Phase Jitter = 77 fsec



F=156.2500MHz | V<sub>dd</sub>=3.3V | LVDS RMS Phase Jitter = 88 fsec

F=156.2500MHz | V<sub>dd</sub>=2.5V | LVDS RMS Phase Jitter = 79 fsec




Note 9: Contact Abracon for phase noise plots at alternative supply voltage (V<sub>dd</sub>) & differential output formats



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 





5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 

AK7

Request Samples 🕥


Check Inventory

ESD Sensitive (Pb)


7.0 x 5.0 x 1.8 mm RoHS/RoHS II Compliant MSL Level = 1

F=100.0000MHz | V<sub>dd</sub>=3.3V | HCSL RMS Phase Jitter = 131 fsec





#### F=148.5000MHz | V<sub>dd</sub>=3.3V | LVPECL RMS Phase Jitter = 114 fsec




Note 9: Contact Abracon for phase noise plots at alternative supply voltage (V<sub>dd</sub>) & differential output formats



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 



AK7PAF1-156.2500T

Note 10: Contact Abracon for non-standard part number configurations and/or requests with carrier frequency callouts up to 5 & 6 digit accuracy after the decimal



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 

AK7


Request Samples 🕥

Check Inventory


ESD Sensitive


7.0 x 5.0 x 1.8 mm RoHS/RoHS II Compliant MSL Level = 1

**Typical Frequency vs. Temperature Characteristics** 



#### **Differential Output Waveform**






Note 11: Recommended test circuit images are representative of when the OE Function is located on Pin 1; when the OE Function is located on Pin 2, then Pin 1=No Connect & Pin 2=OE or No Connect.



÷

5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 



### AK7

Request Samples 🕥

Check Inventory

7.0 x 5.0 x 1.8 mm RoHS/RoHS II Compliant MSL Level = 1

#### **Reflow Profile [JEDEC J-STD-020]**




Table 1								
	SnPb Eutectic Process Classification Temperatures (T <sub>c</sub> )							
Package Thickness	Volume mm <sup>3</sup> <350	Volume mm³ <u>≥</u> 350						
<2.5 mm	235 °C	220 °C						
<u>&gt;</u> 2.5 mm	220 °C	220 °C						

Table 2

#### Pb-Free Process Classification Temperatures (T<sub>c</sub>)

Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> 350-2000	Volume mm <sup>3</sup> >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T <sub>smin</sub> )	100°C	150°C
Temperature maximum (T <sub>smax</sub> )	150°C	200°C
Time (T <sub>smin</sub> to T <sub>smax</sub> ) (t <sub>s</sub> )	60 - 120 sec.	60 - 120 sec.
Average ramp-up rate (T <sub>smax</sub> to T <sub>P</sub> )	3°C/sec. max	3°C/sec. max
Liquidous temperature (T <sub>L</sub> )	183°C	217°C
Time at liquidous (t <sub>L</sub> )	60 - 150 sec.	60 - 150 sec.
Peak package body temperature (T <sub>P</sub> )*	see Table 1	see Table 2
Time $(t_p)^{**}$ within 5°C of the specified classification temperature $(T_c)$	20 sec.	30 sec.
Ramp-down rate (T <sub>p</sub> to T <sub>smax</sub> )	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max


\*Tolerance for peak profile temperature (T<sub>P</sub>) is defined as a supplier minimum and a user maximum.

\*\*Tolerance for time at peak profile temperature (tp) is defined as supplier minimum and a user maximum.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 



are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 06-17-19** 

