


CUSTOMER DRAWING



Product Name				Product Dimensions				Cable Dimensions				
20 AWG	22 AWG	24 AWG	26 AWG	A±1.75 (A±0.07)	Ø B min	Ø C min	H min	Ø E max	Ø F min	Ø G min	Ø D max	J±0.5 (J±0.02)
S02-01-R CS9376	S02-06-R CS9376	S02-11-R CS9376	S02-16-R CS9376	16.5 (0.650)	1.90 (0.075)	2.65 (0.105)	8.25 (0.325)	2.65 (0.105)	0.90 (0.035)	0.50 (0.020)	1.90 (0.075)	7.5 (0.295)
S02-02-R CS9376	S02-07-R CS9376	S02-12-R CS9376	S02-17-R CS9376	16.5 (0.650)	2.65 (0.105)	3.68 (0.145)	8.25 (0.325)	3.68 (0.145)	1.40 (0.055)	0.75 (0.030)	2.65 (0.105)	7.5 (0.295)
S02-03-R CS9376	S02-08-R CS9376	S02-13-R CS9376	S02-18-R CS9376	16.5 (0.650)	4.30 (0.170)	5.08 (0.200)	8.25 (0.325)	5.08 (0.200)	2.15 (0.085)	1.25 (0.050)	4.30 (0.170)	7.5 (0.295)
S02-04-R CS9376	S02-09-R CS9376	S02-14-R CS9376	S02-19-R CS9376	19.1 (0.750)	5.95 (0.235)	6.45 (0.255)	8.25 (0.325)	6.45 (0.255)	3.30 (0.130)	1.80 (0.070)	5.95 (0.235)	7.5 (0.295)
S02-05-R CS9376	S02-10-R CS9376	S02-15-R CS9376	S02-20-R CS9376	19.1 (0.750)	7.00 (0.275)	7.60 (0.300)	8.25 (0.325)	7.60 (0.300)	4.30 (0.170)	2.50 (0.100)	7.00 (0.275)	7.5 (0.295)


MATERIALS

- INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked polyvinylidene fluoride.
- SOLDER PREFORM WITH FLUX AND THERMAL INDICATOR:
 - SOLDER: TYPE Sn63 per ANSI-J-STD-006.
 - FLUX: TYPE ROL1 per ANSI-J-STD-004.
 - THERMAL INDICATOR: Color change: violet to colorless.
- MELTABLE RING: Environment resistant thermoplastic. Color: blue.
- GROUND LEAD: Raychem 55A0111 in accordance with MIL-W-22759/32-AA-90 lead gauge per table.

APPLICATION

- These parts are designed to provide an environment resistant shield termination on cables meeting the following criteria:
 - Dimensions: Per table. Jacket rating: 125°C.
 - Shield plating: Tin or silver. Jacket material: consult TE Connectivity.
- When installed per Raychem process standard RCPS-100-70, assemblies will meet requirements of Raychem Specification RT-1404.

For best results, prepare the cable as shown:



		Raychem DEVICES	TITLE: SOLDERSLEEVE* SHIELD TERMINATOR, IMMERSION RESISTANT	
Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]			DOCUMENT NO.: S02-XX-RCS9376	
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A ROUGHNESS IN MICRON	TE Connectivity reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.	REV : A2	DATE : 27OCT2023
PREPARED BY: M. PRASANTH	CAGE CODE: 06090	ECN: ECN-23-234831	SCALE: NTS	SIZE: A SHEET: 1 of 1