

Product data sheet

Specifications



Wall mounted polyester enclosure, Thalassa PLM, plain door, with bakelite plate, 1056x852x350mm, IP66, IK10, RAL 7035

NSYPLM108BG

Product availability : Stock - Normally stocked in distribution facility

Main

Range	Thalassa
Product name	Thalassa PLM
Device short name	PLM
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	41.57 in (1056 mm)
Nominal width	33.54 in (852 mm)
Nominal depth	13.78 in (350 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 door 1 lock 1 mounting plate
Door type	Solid
Lock type	4 points lock, handle with 5 mm double bar insert

Complementary

Number of locks	1
Mounting plate description	Plain bakelite
Accessibility for operation	Front
Removable parts	Door by hinges Mounting plate by fixing element
Material	polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	NEMA classification 13 NEMA classification 4X IEC 62208
Product Certifications	UL
Electrical Insulation Class	Class II

Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature for Operation	-40...176 °F (-40...80 °C)

Ordering and shipping details

80034-ENCLOSURE SYSTEMS WALL MOUNT METAL	
Discount Schedule	ES1
GTIN	3606480776410
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	44.69 in (113.5 cm)
Package 1 Width	15.16 in (38.5 cm)
Package 1 Length	34.45 in (87.5 cm)
Package 1 Weight	80.91 lb(US) (36.7 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)