



DIMENSIONS:	
A	3.125" ± 0.063
B	3.436" ± 0.125
C	3.796" ± 0.063
D	2.500" ± 0.063
E	2.188" ± 0.063
F	2.876" ± 0.063
G	0.203" X 0.400" ± 0.015



NOTE: ALL LEADS 15.0" LONG MIN. STRIP 0.5".

ELECTRICAL DATA:			
TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 240V, 50Hz, BRN - BLU	2.5mA	Max.
Sec. N.L.V	@ 240V, 50Hz, BRN - BLU		
	BRN - RED = RED - BLU =	120.0V	±2%
	BLK - GRN/YEL =	11.02V	±2%
POLARITY	BRN, BLK	ADDITIVE	
DCR	@ 20°C, BRN - RED =	102.1 Ω	±20%
	@ 20°C, RED - BLU =	111.9 Ω	±20%
	@ 20°C, BLK - GRN/YEL =	0.590 Ω	±20%
HIPOT	PRIMARY - SECONDARY	2500V, 60Hz, 1 SEC	

REV.#	REVISION	DATE	HAMMOND MANUFACTURING™			
0	RELEASED.	C.I. 03/12/21	ELECTRONIC DIVISION			
			52 RANKIN PLACE,			
			WATERLOO, ONTARIO, N2J 3Z5			
			PH # (519) 886-6181			
			FAX # (519) 886-9540			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: OUTPUT TRANSFORMER	DWG. NO. 1750TY
			DATE: 03/12/21	APP'D. BY:		
				DIMENSIONS: IN(X) MM()		