



80-Series Diagonal cutters Tapered and relieved head, 8146-8158

These cutters are made from high performance ball bearing steel, black oxidised. Numerically controlled machine grinding guarantees edge angle accuracy and contact which increases the tools reliability and consistency.


Precision induction hardened edges, 63-65 HRC. Handles in synthetic material and come with return spring.






The cutting capacity that is given is for copper wire!

These Tapered and Relieved Head cutters are ideal for use in confined spaces and for rework.

"CO" standard handle shape in conductive material.

"DS" slip-on handle in dissipative material.



		 731415+		A mm	B mm	C mm	D F mmmm		
8146		0051076	10	110.0	10.0	10.0	6 0.8 0.2-1.0	Micro	46
8147		0051083	10	110.0	10.0	10.0	6 0.8 0.1-1.0	Flush	46
8147 DS		0051946	10	110.0	10.0	10.0	6 0.8 0.1-1.0	Flush	46
8148		0051090	10	110.0	10.0	10.0	6 0.8 0.1-0.8	Ultra	45
8148 CO		0051656	10	110.0	10.0	10.0	6 0.8 0.1-0.8	Ultra	45
8148 DS		0051953	10	110.0	10.0	10.0	6 0.8 0.1-0.8	Ultra	45
8156		0051212	10	112.5	12.5	12.5	6 1.0 0.3-1.25	Micro	49
8156 DS		0112142	1	112.5	12.5	12.5	6 1.0 0.3-1.25	Micro	49
8157		0052127	10	112.5	12.5	12.5	6 1.0 0.2-1.25	Flush	49
8158		0052134	10	112.5	12.5	12.5	6 1.0 0.2-1.0	Ultra	49