

Changeoverswitches, T5B, 63 A, surface mounting, 1 contact unit(s),
Contacts: 2, 60 °, maintained, With 0 (Off) position, 1-0-2, Design number
8210

Part no. **T5B-1-8210/14**
207432

General specifications		
Product name		Eaton Moeller® series T5B Changeover switch
Part no.		T5B-1-8210/14
EAN		4015082074326
Product Length/Depth		240 millimetre
Product height		162 millimetre
Product width		160 millimetre
Product weight		1.039 kilogram
Certifications		CSA-C22.2 No. 94 UL 60947-4-1 IEC/EN 60947-3 UL File No.: E36332 UL Category Control No.: NLRV CSA File No.: 012528 UL IEC/EN 60204 IEC/EN 60947 CSA VDE 0660 CE CSA Class No.: 3211-05 CSA-C22.2 No. 60947-4-1-14
Product Tradename		T5B
Product Type		Changeover switch
Product Sub Type		None
Catalog Notes		Rated Short-time Withstand Current (Icw) for a time of 1 second
Features & Functions		
Enclosure material		Plastic
Features		Complete device in housing
Fitted with:		Black thumb grip and front plate 0 (off) position
Inscription		1-0-2
Number of poles		1
General information		
Degree of protection		NEMA 1 NEMA 12 IP65
Degree of protection (front side)		IP65 NEMA 12
Lifespan, mechanical		500,000 Operations
Model		Reverser
Mounting method		Surface mounting
Mounting position		As required
Number of contact units		1
Operating frequency		1200 Operations/h
Overvoltage category		III
Pollution degree		3
Rated impulse withstand voltage (Uimp)		6000 V AC
Safe isolation		440 V AC, Between the contacts, According to EN 61140
Safety parameter (EN ISO 13849-1)		B10d values as per EN ISO 13849-1, table C.1
Shock resistance		15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
Suitable for		Branch circuits, suitable as motor disconnect, (UL/CSA) Ground mounting
Switching angle		60 °

Type		Changeover switch
Climatic environmental conditions		
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		40 °C
Ambient operating temperature (enclosed) - min		-25 °C
Ambient operating temperature (enclosed) - max		40 °C
Climatic proofing		Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Terminal capacities		
Terminal capacity (flexible with ferrule)		1 x (1 - 25) mm ² , ferrules to DIN 46228 2 x (1.5 - 10) mm ² , ferrule to DIN 46228
Terminal capacity (solid/flexible with ferrule AWG)		12 - 4
Terminal capacity (solid/stranded)		2 x (2.5 - 16) mm ² 1 x (2.5 - 35) mm ²
Screw size		M6, Terminal screw
Tightening torque		4 Nm, Screw terminals 35.4 lb-in, Screw terminals
Electrical rating		
Rated breaking capacity at 220/230 V (cos phi to IEC 60947-3)		520 A
Rated breaking capacity at 400/415 V (cos phi to IEC 60947-3)		600 A
Rated breaking capacity at 500 V (cos phi to IEC 60947-3)		480 A
Rated breaking capacity at 660/690 V (cos phi to IEC 60947-3)		340 A
Rated operational current (Ie)		57.2 A at AC-3, 500 V star-delta 29.4 A at AC-3, 690 V star-delta 63 A at AC-3, 230 V star-delta 63 A at AC-3, 400 V star-delta
Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V		51 A
Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V		41 A
Rated operational current (Ie) at AC-3, 500 V		33 A
Rated operational current (Ie) at AC-3, 660 V, 690 V		17 A
Rated operational current (Ie) at AC-21, 440 V		63 A
Rated operational current (Ie) at AC-23A, 230 V		63 A
Rated operational current (Ie) at AC-23A, 400 V, 415 V		63 A
Rated operational current (Ie) at AC-23A, 500 V		33 A
Rated operational current (Ie) at AC-23A, 690 V		23.8 A
Rated operational current (Ie) at DC-1, load-break switches I/r = 1 ms		63 A
Rated operational current (Ie) at DC-13, control switches L/R = 50 ms		25 A
Rated operational current (Ie) at DC-23A, 24 V		50 A
Rated operational current (Ie) at DC-23A, 48 V		50 A
Rated operational current (Ie) at DC-23A, 60 V		50 A
Rated operational current (Ie) at DC-23A, 120 V		25 A
Rated operational current (Ie) at DC-23A, 240 V		20 A
Rated operational power at AC-3, 380/400 V, 50 Hz		22 kW
Rated operational power at AC-3, 415 V, 50 Hz		22 kW
Rated operational power at AC-3, 690 V, 50 Hz		15 kW
Rated operational power at AC-23A, 220/230 V, 50 Hz		18.5 kW
Rated operational power at AC-23A, 400 V, 50 Hz		30 kW
Rated operational power at AC-23A, 500 V, 50 Hz		22 kW
Rated operational power at AC-23A, 690 V, 50 Hz		22 kW
Rated operational power star-delta at 220/230 V, 50 Hz		18.5 kW
Rated operational power star-delta at 380/400 V, 50 Hz		30 kW
Rated operational power star-delta at 500 V, 50 Hz		37 kW
Rated operational power star-delta at 690 V, 50 Hz		22 kW
Rated operational voltage (Ue) at AC - max		690 V
Rated uninterrupted current (Iu)		63 A
Uninterrupted current		Rated uninterrupted current Iu is specified for max. cross-section.
Short-circuit rating		

Rated conditional short-circuit current (Iq)	2 kA
Rated short-time withstand current (Icw)	1,3 kA, Contacts, 1 second
Short-circuit current rating (high fault)	10 kA, SCCR (UL/CSA) 100 A, Class J, max. Fuse, SCCR (UL/CSA)
Short-circuit protection rating	80 A gG/gL, Fuse, Contacts
Switching capacity	
Load rating	2 x I# (with intermittent operation class 12, 25 % duty factor) 1.3 x I# (with intermittent operation class 12, 60 % duty factor) 1.6 x I# (with intermittent operation class 12, 40 % duty factor)
Number of contacts in series at DC-23A, 24 V	1
Number of contacts in series at DC-23A, 48 V	2
Number of contacts in series at DC-23A, 60 V	3
Number of contacts in series at DC-23A, 120 V	3
Number of contacts in series at DC-23A, 240 V	6
Switching capacity (main contacts, general use)	63 A, Rated uninterrupted current max. (UL/CSA)
Rated making capacity up to 690 V (cos phi to IEC/EN 60947-3)	800 A
Voltage per contact pair in series	60 V
Motor rating	
Assigned motor power at 115/120 V, 60 Hz, 1-phase	3 HP
Assigned motor power at 200/208 V, 60 Hz, 1-phase	7.5 HP
Assigned motor power at 200/208 V, 60 Hz, 3-phase	15 HP
Assigned motor power at 230/240 V, 60 Hz, 1-phase	10 HP
Assigned motor power at 230/240 V, 60 Hz, 3-phase	15 HP
Assigned motor power at 460/480 V, 60 Hz, 3-phase	40 HP
Assigned motor power at 575/600 V, 60 Hz, 3-phase	40 HP
Contacts	
Control circuit reliability	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
Number of auxiliary contacts (change-over contacts)	0
Number of auxiliary contacts (normally closed contacts)	0
Number of auxiliary contacts (normally open contacts)	0
Number of contacts	2
Actuator	
Actuator function	With 0 (Off) position Maintained
Actuator type	Short thumb-grip
Design verification	
Equipment heat dissipation, current-dependent Pvid	0 W
Heat dissipation capacity Pdis	0 W
Heat dissipation per pole, current-dependent Pvid	4.5 W
Rated operational current for specified heat dissipation (In)	63 A
Static heat dissipation, non-current-dependent Pvs	0 W
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	UV resistance only in connection with protective shield.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of assemblies	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Off-load switch (EC001105)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Changeover switch (ecl@ss10.0.1-27-37-14-05 [AKF062013])

Model		Reverser
Number of poles		1
With zero (off) position		Yes
With retraction in 0-position		No
Rated permanent current I _u	A	63
Rated operation current I _e at AC-3, 400 V	A	41
Rated operation power at AC-3, 400 V	kW	22
Degree of protection (IP), front side		IP65
Degree of protection (NEMA), front side		12
Number of auxiliary contacts as normally closed contact		0
Number of auxiliary contacts as normally open contact		0
Number of auxiliary contacts as change-over contact		0
Suitable for floor mounting		Yes
Suitable for front mounting		No
Suitable for distribution board installation		No
Suitable for intermediate mounting		No
Complete device in housing		Yes
Material housing		Plastic
Type of control element		Short thumb-grip
Type of electrical connection of main circuit		Screw connection