

**Control circuit switches, TM, 10 A, flush mounting, Contacts: 3, STOP function, With black rotary handle and locking ring, Lockable in the 0 (Off) position**

**Part no. TM-2-8292/E/SVB-SW  
210955**

<b>General specifications</b>	
Product name	Eaton Moeller® series TM Accessory Control circuit isolator
Part no.	TM-2-8292/E/SVB-SW
EAN	4015082109554
Product Length/Depth	89 millimetre
Product height	48 millimetre
Product width	30 millimetre
Product weight	0.059 kilogram
Certifications	CSA UL File No.: E36332 IEC/EN 60947-5-1 CE UL report applies to both US and Canada CSA-C22.2 No. 94 UL 508 IEC/EN 60947 Certified by UL for use in Canada UL UL Category Control No.: NLRV VDE 0660 CSA-C22.2 No. 14-05 IEC/EN 60947-3
Product Tradename	TM
Product Type	Accessory
Product Sub Type	Control circuit isolator
Catalog Notes	up to 250 V AC per contact
<b>Features &amp; Functions</b>	
Features	Version as main switch
Fitted with:	Black rotary handle and locking ring
Functions	STOP function Interlockable
Locking facility	Lockable in the 0 (Off) position
Number of poles	3
<b>General information</b>	
Degree of protection	NEMA 12
Degree of protection (front side)	IP65
Lifespan, mechanical	1,000,000 Operations
Mounting method	Flush mounting
Mounting position	As required
Number of contact units	2
Operating frequency	1200 Operations/h
Overvoltage category	III
Pollution degree	3
Rated impulse withstand voltage (Uimp)	4000 V AC
Suitable for	Front mounting 4-hole
Switching angle	90 °
Type	Control circuit switch
<b>Climatic environmental conditions</b>	
Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	50 °C
Climatic proofing	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>Terminal capacities</b>	

Terminal capacity		2 x 1.5 mm <sup>2</sup> , flexible 2 x 1.0 mm <sup>2</sup> , flexible with ferrules to DIN 46228 2 x 1,5 mm <sup>2</sup> , solid or stranded 1 x 1.5 mm <sup>2</sup> , flexible 1 x 1.5 mm <sup>2</sup> , solid or stranded 1 x 1.0 mm <sup>2</sup> , flexible with ferrules to DIN 46228 14 AWG, solid or flexible with ferrule
Screw size		M2.5, Terminal screw
Tightening torque		0.4 Nm, Screw terminals 3.5 lb-in, Screw terminals
<b>Electrical rating</b>		
Rated operational power at AC-3, 380/400 V, 50 Hz		0 kW
Rated operational power at AC-23A, 400 V, 50 Hz		3 kW
Rated operational voltage (Ue) at AC - max		500 V
Rated uninterrupted current (Iu)		10 A
Uninterrupted current		Rated uninterrupted current Iu is specified for max. cross-section.
<b>Short-circuit rating</b>		
Rated conditional short-circuit current (Iq)		0 kA
Rated short-time withstand current (Icw)		0 kA
Short-circuit protection rating		10 A gG/gL, Fuse, Contacts
<b>Switching capacity</b>		
Switching capacity (main contacts, general use)		10 A, Rated uninterrupted current max. (UL/CSA)
Switching capacity (auxiliary contacts, general use)		10A, IU, (UL/CSA)
Switching capacity (auxiliary contacts, pilot duty)		A300 (UL/CSA)
<b>Motor rating</b>		
Assigned motor power at 115/120 V, 60 Hz, 1-phase		0.33 HP
Assigned motor power at 115/120 V, 60 Hz, 3-phase		0.75 HP
Assigned motor power at 230/240 V, 60 Hz, 1-phase		0.75 HP
Assigned motor power at 230/240 V, 60 Hz, 3-phase		1 HP
Assigned motor power at 277 V, 60 Hz, 1-phase		0.75 HP
<b>Contacts</b>		
Control circuit reliability		1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
Number of auxiliary contacts (change-over contacts)		0
Number of auxiliary contacts (normally closed contacts)		0
Number of auxiliary contacts (normally open contacts)		0
<b>Actuator</b>		
Actuator color		Black
Actuator type		Door coupling rotary drive
<b>Design verification</b>		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdiss		0 W
Heat dissipation per pole, current-dependent Pvid		0.15 W
Rated operational current for specified heat dissipation (In)		10 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		UV resistance only in connection with protective shield.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Switch disconnecter (EC000216)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Switch disconnecter (ecl@ss10.0.1-27-37-14-03 [AKF060013])

Version as main switch		Yes
Version as maintenance-/service switch		No
Version as safety switch		No
Version as emergency stop installation		No
Version as reversing switch		No
Number of switches		1
Max. rated operation voltage U <sub>e</sub> AC	V	500
Rated operating voltage	V	500 - 500
Rated permanent current I <sub>u</sub>	A	10
Rated permanent current at AC-23, 400 V	A	6.6
Rated permanent current at AC-21, 400 V	A	0
Rated operation power at AC-3, 400 V	kW	0
Rated short-time withstand current I <sub>cw</sub>	kA	0
Rated operation power at AC-23, 400 V	kW	3
Switching power at 400 V	kW	0
Conditioned rated short-circuit current I <sub>q</sub>	kA	0
Number of poles		3
Number of auxiliary contacts as normally closed contact		0
Number of auxiliary contacts as normally open contact		0
Number of auxiliary contacts as change-over contact		0
Motor drive optional		No
Motor drive integrated		No
Voltage release optional		No
Device construction		Built-in device fixed built-in technique
Suitable for floor mounting		No
Suitable for front mounting 4-hole		Yes
Suitable for front mounting centre		No
Suitable for distribution board installation		No
Suitable for intermediate mounting		No
Colour control element		Black
Type of control element		Door coupling rotary drive
Interlockable		Yes
Type of electrical connection of main circuit		Screw connection
Degree of protection (IP), front side		IP65
Degree of protection (NEMA)		12