

16 SPEED GENERAL DUTY BENCH DRILL

CATALOGUE ENTRY

55 D16/16 16 SPEED GENERAL DUTY BENCH DRILL

No-volt switch.

Sixteen speed bench drill complete with 16mm capacity chuck, ideal for the home and maintenance workshop. Powered by a 350W motor for an efficient smooth running operation. It has an adjustable circular tilting table complete with a rise and fall rack and pinion. Fitted with a BS approved non-rewireable 3 pin moulded plug and cable. Carton packed.

Specification:

Drilling capacity	... 16mm
Chuck capacity	... 16mm
Collar diameter	... 60mm
Spindle taper	... MT2
Speeds (rpm)	... 16 (210-3340)
Swing	... 323mm
Spindle travel	... 80mm
Column diameter	... 71mm
Table diameter	... 310mm
Base size	... 420 x 250mm
Motor	... 350W
Height	... 960mm
Nett/gross weight	... 54/56kg

Stock No.	Description	Euro each	GBP £ each
36389	230V Drill	N/a	N/a
65964	Chuck Guard	N/a	N/a
65970	Geared Chuck	N/a	N/a



DRAPER BULLETS

these need to be kept to a minimum, in order of priority.

- 16mm chuck capacity
- 0-45° tilting table
- Motor; 350W - 230VAC
- Height; 960mm

Stock No.	Chk Digit	Description	FARNELL CODE
36389	6	230V 16 SPEED GENERAL DUTY BENCH DRILL	7140745
65964	7	Chuck Guard	Ex Stock
65970	8	Geared Chuck	Ex Stock

BRAND:	DRAPER	BARCODED	YES
--------	---------------	----------	------------