

Changeover switches, TM, 10 A, flush mounting, 3 contact unit(s),
Contacts: 6, 60 °, maintained, With 0 (Off) position, 1-0-2, Design number
8212



Part no. **TM-3-8212/E**
010807

General specifications		
Product name		Eaton Moeller® series TM Changeover switch
Part no.		TM-3-8212/E
EAN		4015080108078
Product Length/Depth		86 millimetre
Product height		30 millimetre
Product width		30 millimetre
Product weight		0.05 kilogram
Certifications		UL 508 Certified by UL for use in Canada VDE 0660 UL File No.: E36332 CSA UL IEC/EN 60947-5-1 CSA-C22.2 No. 94 UL report applies to both US and Canada CE UL Category Control No.: NLRV IEC/EN 60947 IEC/EN 60947-3 CSA-C22.2 No. 14-05
Product Tradename		TM
Product Type		Changeover switch
Product Sub Type		None
Features & Functions		
Enclosure material		Plastic
Fitted with:		0 (off) position Black thumb grip and front plate
Inscription		1-0-2
Number of poles		3
General information		
Degree of protection		IP65
Degree of protection (front side)		IP65 NEMA 12
Lifespan, mechanical		1,000,000 Operations
Model		Reverser
Mounting method		Flush mounting
Mounting position		As required
Number of contact units		3
Operating frequency		1200 Operations/h
Overvoltage category		III
Pollution degree		3
Rated impulse withstand voltage (Uimp)		4000 V AC
Suitable for		Front mounting
Switching angle		60 °
Type		Changeover switch
Climatic environmental conditions		
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		50 °C
Climatic proofing		Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
Terminal capacities		

Terminal capacity (flexible with ferrule)		2 x 1.0 mm ² , ferrules to DIN 46228 1 x 1.0 mm ² , ferrules to DIN 46228
Terminal capacity (flexible)		2 x 1.5 mm ² 1 x 1.5 mm ²
Terminal capacity (solid/flexible with ferrule AWG)		14
Terminal capacity (solid/stranded)		2 x 1,5 mm ² 1 x 1.5 mm ²
Screw size		M2.5, Terminal screw
Tightening torque		0.4 Nm, Screw terminals 3.5 lb-in, Screw terminals
Electrical rating		
Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V		0 A
Rated operational power at AC-3, 380/400 V, 50 Hz		3.3 kW
Rated operational power at AC-23A, 400 V, 50 Hz		3 kW
Rated operational voltage (Ue) at AC - max		500 V
Rated uninterrupted current (Iu)		10 A
Uninterrupted current		Rated uninterrupted current Iu is specified for max. cross-section.
Short-circuit rating		
Short-circuit protection rating		10 A gG/gL, Fuse, Contacts
Switching capacity		
Switching capacity (main contacts, general use)		10 A, Rated uninterrupted current max. (UL/CSA)
Switching capacity (auxiliary contacts, general use)		10A, IU, (UL/CSA)
Switching capacity (auxiliary contacts, pilot duty)		A300 (UL/CSA)
Motor rating		
Assigned motor power at 115/120 V, 60 Hz, 1-phase		0.33 HP
Assigned motor power at 115/120 V, 60 Hz, 3-phase		0.75 HP
Assigned motor power at 230/240 V, 60 Hz, 1-phase		0.75 HP
Assigned motor power at 230/240 V, 60 Hz, 3-phase		1 HP
Assigned motor power at 277 V, 60 Hz, 1-phase		0.75 HP
Contacts		
Control circuit reliability		1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
Number of auxiliary contacts (change-over contacts)		0
Number of auxiliary contacts (normally closed contacts)		0
Number of auxiliary contacts (normally open contacts)		0
Number of contacts		6
Actuator		
Actuator function		Maintained With 0 (Off) position
Actuator type		Short thumb-grip
Design verification		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdis		0 W
Heat dissipation per pole, current-dependent Pvid		0.15 W
Rated operational current for specified heat dissipation (In)		10 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		UV resistance only in connection with protective shield.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Off-load switch (EC001105)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Changeover switch (ecl@ss10.0.1-27-37-14-05 [AKF062013])

Model		Reverser
Number of poles		3
With zero (off) position		Yes
With retraction in 0-position		No
Rated permanent current I _u	A	10
Rated operation current I _e at AC-3, 400 V	A	0
Rated operation power at AC-3, 400 V	kW	3.3
Degree of protection (IP), front side		IP65
Degree of protection (NEMA), front side		12
Number of auxiliary contacts as normally closed contact		0
Number of auxiliary contacts as normally open contact		0
Number of auxiliary contacts as change-over contact		0
Suitable for floor mounting		No
Suitable for front mounting		Yes
Suitable for distribution board installation		No
Suitable for intermediate mounting		No
Complete device in housing		No
Material housing		Plastic
Type of control element		Short thumb-grip
Type of electrical connection of main circuit		Screw connection